



• Specifications

Items	Characteristics	
Temperature range	-55 to +105°C	
Rated voltage range	2.5 to 25Vdc	
Capacitance range	6.8 to 1,500μF	
Capacitance tolerance	±20% [M] (at 20°C, 120Hz)	
Tangent of loss angle	Less than or equal to the value of Standard Ratings (at 20°C, 120Hz)	
Leakage current	Less than or equal to the value of Standard Ratings (at 20°C, after 2 minutes)	
ESR	Less than or equal to the value of Standard Ratings	
Characteristics of impedance	$Z_{+105^{\circ}\text{C}}/Z_{+20^{\circ}\text{C}} \leq 1.25, Z_{-55^{\circ}\text{C}}/Z_{+20^{\circ}\text{C}} \leq 1.25$ at 100kHz	
Endurance	105°C, 2,000 hrs at rated voltage	
	Appearance	No significant damage
	Capacitance change	Within±20% of the initial value
	Tangent of loss angle (tanδ)	≤150% of the initial specified value
	ESR(mΩ)	≤150% of the initial specified value
	Leakage current	≤The initial specified value
Damp Heat (Steady State)	60°C, 90 to 95% RH, 1,000 hrs, No-applied Voltage	
	Appearance	No significant damage
	Capacitance change	Within±20% of the initial value
	Tangent of loss angle (tanδ)	≤150% of the initial specified value
	ESR(mΩ)	≤150% of the initial specified value
	Leakage current	≤The initial specified value
Resistance to soldering heat	VPS (230°C, 75s)	
	Appearance	No significant damage
	Capacitance change	Within±10% of the initial value
	Tangent of loss angle (tanδ)	≤130% of the initial specified value
	ESR(mΩ)	≤130% of the initial specified value
	Leakage current	≤The initial specified value


*In case of some problems for measured values, measure after applying rated voltage for 120 minutes at 105°C

• Size List

(unit: mm)

μF	RV (SV)	2.5 (2.9)	4 (4.6)	6.3 (7.2)	10 (11.5)	16 (18.4)	20 (23.0)	25 (28.7)
6.8								6.3×5.9
10							5×5.9	8×6.9
15						5×5.9		
22						5×5.9	6.3×5.9	10×7.9
27							6.3×5.9	
33					5×5.9		8×6.9	8×11.9
39		5×5.9				6.3×5.9		
47			5×5.9	6.3×5.9	6.3×5.9	8×6.9		
56				6.3×5.9	8×6.9	10×7.9		10×12.6
68		5×5.9						10×7.9
82				6.3×5.9		8×6.9		
100				6.3×5.9		10×7.9	8×11.9	8×11.9
120				6.3×5.9	8×6.9			
150		6.3×5.9			8×6.9 10×7.9	10×7.9	10×12.6	10×12.6
180						8×11.9 10×7.9		
220	6.3×5.9			8×6.9 10×7.9				
270					10×7.9			
330		8×6.9	10×7.9	8×11.9 10×7.9	10×12.6			
470	8×6.9			8×11.9 10×7.9	10×12.6			
560		8×11.9						
680	8×11.9	10×7.9						
820				10×12.6				
1000				10×12.6				
1200		10×12.6						
1500	10×12.6							

• Marking and Dimensions




(unit: mm)

Size	ØD±0.5	L+0.1-0.4	W±0.2	H±0.2	C±0.2	R	P±0.2
5×5.9	5.0	5.9	5.3	5.3	6.0	0.6~0.8	1.4
6.3×5.9	6.3	5.9	6.6	6.6	7.3	0.6~0.8	2.1
8×6.9	8.0	6.9	8.3	8.3	9.0	0.6~0.8	3.2
10×7.9	10.0	7.9	10.3	10.3	11.0	0.6~0.8	4.6
8×11.9	8.0	11.9	8.3	8.3	9.0	0.8~1.1	3.2
10×12.6	10.0	12.6	10.3	10.3	11.0	0.8~1.1	4.6

• Recommended Land Pattern Dimension of PCB

(unit: mm)



Size	a	b	c
5×5.9	1.4	7.4	1.6
6.3×5.9	2.1	9.1	1.6
8×6.9	2.8	11.1	1.9
10×7.9	4.3	13.1	1.9
8×11.9	2.8	11.1	1.9
10×12.6	4.3	13.1	1.9

• Standard Ratings

Rated Voltage [Vdc]	Rated Capacitance [µF]	Size ØD x L [mm]	ESR (20°C, 100kHz) [mΩ] [max.]	Rated Ripple Current (105°C, 100kHz) [mA rms]	Tangent of Loss Angel [max]	Leakage Current [µA, max]	Part Number
2.5	220	6.3 x 5.9	23	2390	0.1	110	2VS220MC6
	470	8 x 6.9	23	3300	0.1	235	2VS470MD7
	680	8 x 11.9	13	4520	0.1	340	2VS680MD12
	1500	10 x 12.6	12	5440	0.1	750	2VS1500ME12
4	39	5 x 5.9	70	1100	0.1	78	4VS39MB6
	68	5 x 5.9	60	1400	0.1	136	4VS68MB6
	150	6.3 x 5.9	40	1810	0.1	120	4VS150MC6
	330	8 x 6.9	35	2560	0.1	264	4VS330MD7
	560	8 x 11.9	13	4520	0.1	448	4VS560MD12
	680	10 x 7.9	25	3700	0.1	544	4VS680ME8
	1200	10 x 12.6	12	5440	0.1	960	4VS1200ME12
	47	5 x 5.9	70	1100	0.1	148	6VS47MB6
6.3	82	6.3 x 5.9	45	1700	0.1	103	6VS82MC6
	100	6.3 x 5.9	40	1810	0.1	126	6VS100MC6
	120	6.3 x 5.9	40	1810	0.1	151	6VS120MC6
	220	8 x 6.9	35	2560	0.1	277	6VS220MD7
	220	10 x 7.9	25	3700	0.1	277	6VS220ME8
	330	10 x 7.9	25	3700	0.1	416	6VS330ME8
	470	10 x 7.9	25	3700	0.1	592	6VS470ME8
	470	8 x 11.9	15	4210	0.1	592	6VS470MD12
	820	10 x 12.6	12	5440	0.1	1033	6VS820ME12
	1000	10 x 12.6	12	5440	0.1	1260	6VS1000ME12
10	33	5 x 5.9	70	1100	0.1	165	10VS33MB6
	47	6.3 x 5.9	50	1620	0.1	94	10VS47MC6
	56	6.3 x 5.9	45	1700	0.1	112	10VS56MC6
	120	8 x 6.9	35	2560	0.1	240	10VS120MD7
	150	8 x 6.9	35	2560	0.1	300	10VS150MD7
	150	10 x 7.9	30	3020	0.1	300	10VS150ME8
	270	10 x 7.9	25	3700	0.1	540	10VS270ME8
	330	8 x 11.9	17	3950	0.1	660	10VS330MD12
	330	10 x 7.9	25	3700	0.1	660	10VS330ME8
	560	10 x 12.6	13	5230	0.1	1120	10VS560ME12
16	15	5 x 5.9	120	1020	0.1	120	10VS15MB6
	22	5 x 5.9	90	1060	0.1	176	10VS22MB6
	39	6.3 x 5.9	50	1620	0.1	125	16VS39MC6
	47	6.3 x 5.9	50	1620	0.1	150	16VS47MC6
	56	8 x 6.9	45	1890	0.1	179	16VS56MD7
	82	8 x 6.9	40	2120	0.1	262	16VS82MD7
	100	10 x 7.9	35	2670	0.1	320	16VS100ME8
	150	10 x 7.9	30	3020	0.1	480	16VS150ME8
	180	8 x 11.9	20	3640	0.1	576	16VS180MD12
	180	10 x 7.9	30	3020	0.1	576	16VS180ME8
	330	10 x 12.6	16	4720	0.1	1056	16VS330ME12
470	10 x 12.6	16	4720	0.1	1504	16VS470ME12	
20	10	5 x 5.9	120	1020	0.1	100	20VS10MB6
	22	6.3 x 5.9	60	1450	0.1	88	20VS22MC6
	27	6.3 x 5.9	60	1450	0.1	108	20VS27MC6
	33	8 x 6.9	45	1890	0.1	132	20VS33MD7
	47	8 x 6.9	45	1890	0.1	188	20VS47MD7
	56	10 x 7.9	40	2400	0.1	224	20VS56ME8
	68	10 x 7.9	40	2400	0.1	272	20VS68ME8
	100	8 x 11.9	24	3320	0.1	400	20VS100MD12
	150	10 x 12.6	20	4320	0.1	600	20VS150ME12
25	6.8	6.3 x 5.9	80	1200	0.1	85	25VS6R8MC6
	10	8 x 6.9	60	1500	0.1	125	25VS10MD7
	22	10 x 7.9	50	2000	0.1	275	25VS22ME8
	33	8 x 11.9	30	2980	0.1	413	25VS33MD12
	56	10 x 12.6	28	3800	0.1	700	25VS56ME12
	100	8 x 11.9	30	3320	0.1	500	25VS100MD12
150	10 x 12.6	25	3800	0.1	750	25VS150ME12	

Conductive Polymer Hybrid Aluminum Electrolytic Capacitors Radial Lead Type

Conductive Polymer Hybrid Aluminum Electrolytic Capacitors SMD Lead Type

Conductive Polymer Aluminum Electrolytic Capacitors Radial Lead Type

Conductive Polymer Aluminum Electrolytic Capacitors SMD Lead Type