




PEC PRECISION PRODUCTS

Round and Square End Protractors




Features:

Used for drawing radial lines, transferring angles and setting bevels
 Made of tempered steel with satin chrome finish
 Measures Angles from 0 - 180°
 Features 6" arm and knurled thumb lock nut
 Blade secured firmly by lock nut at any angle
 Head measures 3-5/16" x 2"
 Accuracy ± 1/2°

Order Code	Description
5180	Round End Protractor
5170	Square End Protractor


Depth Gauge Protractors



Specification as above but with graduated rule.

Order Code	Description
5191	Square End with rule 32nds/1mm
5192	Square End metric only rule 0.5 / 1mm
5193	Round End rule 32nds/1mm
5194	Round End metric only rule 0.5 / 1mm

Linear Universal Bevel Protractor




Features:

Dial face and vernier in satin chrome
 Magnifier for easy reading of vernier scale
 Protractor dial graduated 360 x 1 degree
 Vernier scale reads to 5 minutes of arc
 Blades bevelled at 45 degrees on one end and 60 degrees on the other
 Protractor accepts 6" and 12" blades

Order Code	Description
51-550-012	Protractor with 6" and 12" blades

Linear Universal Precision Protractor



This special protractor is extremely versatile and due to its clever design is capable of measuring both internal and external angles.

Features:

Outer Angle range 0 - 180°
 Inner angle range 40 - 180°
 Protractor scale graduated 320 x 1 degree
 Vernier scale reads in 2 minute divisions
 Blade length is 150mm
 Blades are made from alloy steel, hardened and ground
 Scales are stainless steel with a satin chrome finish
 Indicating accuracy ± 2 minutes

Order Code	Description
51-500-000	Universal Precision Protractor