




PLASTI-GRIP

TE Internal #: 52465
Spring Spade Terminal, 16 – 14 AWG, #10 Stud, 4.82 mm [.19 in]
Stud Diameter, Closed Barrel, Straight, Tin Plating, Partially
Insulated, PLASTI-GRIP

[View on TE.com >](#)

Terminals & Splices > Spade Terminals



Spade Terminal Type: **Spring Spade Terminal**
Wire Size: **2050 – 5180 CMA**
Stud Size: **#10**

Features

Product Type Features

Terminal Features	Inspection Slot
Stud Size	#10
Sealable	No
Wire Insulation Support Retention Type	Insulation Support

Electrical Characteristics

Voltage Rating	600 V
----------------	-------

Body Features

Insulation Sleeve Color	Blue
Stripe Color	Blue

Contact Features

Spade Terminal Type	Spring Spade Terminal
Barrel Type	Closed
Terminal Orientation	Straight
Terminal Plating Material	Tin

Mechanical Attachment

Wire Insulation Support	With
-------------------------	------

Dimensions

Wire Size	2050 – 5180 CMA
Stud Diameter	4.82 mm [.19 in]
Tongue Thickness	.84 mm [.033 in]
Product Length	25.83 mm [1.017 in]
Compatible Insulation Diameter (Max)	4.9 mm [.193 in]
Compatible Insulation Diameter Range	3 – 4.9 mm [.118 – .193 in]

Usage Conditions

Insulation Option	Partially Insulated
-------------------	---------------------

Operation/Application

Compatible With Wire Base Material	Copper
Compatible With Wire Plating Material	Tin

Industry Standards

Government Qualified Terminal	No
-------------------------------	----

Packaging Features

Packaging Quantity	1000
Packaging Method	Loose Piece

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer



This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 58423-1
DIE, RBY IS9252

TE Part # 58433-3
PRO CR ASSY, RBY IS9252

TE Part # 169404
CERTI-LOK DIE

TE Part # 59824-1
TETRA-CRIMP PIDG PG FASTON 22-10 ASSY

TE Part # 169400
CERTI-LOK FRAME W/O DIES

TE Part # 47387
DAHT PG PIDG 20-14 ASSY

TE Part # 59250
T-HEAD PIDG 26-14 ASSY

Also in the Series | PLASTI-GRIP

Compression Connectors(3)

Crimp Wire Pins, Tabs & Ferrules(20)


Ring Terminals(310)

Spade Terminals(159)



Splices(45)

Customers Also Bought



TE Part #6-215882-4
64 WAY GREY MK II RECP



TE Part #1609078-1
6ESRM-P=F6990



TE Part #234478-E
SRCA 1,27 12 M 1 SMD 137 E1 094 *
GURT *



TE Part #5745783-5
25 MSFL RCPT RA 318 (SL,FM)



TE Part #5103308-7
A/L LOW PRO HDR 34P VERT BLACK



TE Part #5207661-3
RCPT ASSY,37P,HDP-20,CN



TE Part #350829-1
12P UMNL HDR ASSY PC 94VO



TE Part #420356-000
RMW-35/12-1200/ADH-0



TE Part #52291-1
TERMINAL R PG 8 3/8



TE Part #5554990-1
MJ,TE,6P

Documents

Product Drawings

TERMINAL,PG SPR SPD 16-14 10

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_52465_N.2d_dxf.zip



English

Customer View Model

[ENG_CVM_CVM_52465_N.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_52465_N.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

[Application Specification](#)

English

Agency Approvals

[UL Report](#)

English

[UL Report](#)

English