


# Palm/Foot Switches

## Range: Control Stations

Order Code: SFP-EAL-2A1B-RD



### DESCRIPTION

Latching palm/foot switch, Red Button. Push to stop/start - twist to reset

### CONTROL STATIONS FEATURES

- Customised control station service available - please ask for details.
- Insulation resistance - >100MOhm @ 500VDC
- Enclosures sealed up to IP66
- Dust & waterproof for short-term submersion
- 2 contact blocks fitted as standard
- Different voltage ratings are available
- Contact material - Silver Bifurcated and serrated
- Operating Temperature -20 to +50°C
- Contact rating - AC12 Resistive / AC15 Electromagnetic - 240V (3A) / 415V (1.5A)
- Mechanical life - 1 million operations
- Contact Block UL and TUV rated

*Features may vary by product throughout the range.*

*Subject to technical modification without notice.*

*Typographical and other errors do not justify claim for damages.*

## SPECIFICATION

Base Colour	Yellow/Black
Base Style	Standard base
Depth (mm)	102.5
Enclosure Material	ABS-UL94-HB
Height (mm)	85
IP Rating	IP66
Lid Colour	Yellow
Min Temperature Rating °C	-20
Max Temperature Rating °C	50
Number of Switches	1
Size (mm)	85x85x102.5
Switch 1 Style	Red push button non-illuminated
Switch 1 Substyle	Palm/foot
Width (mm)	85