


KAM03AR70G104K#

(0201, 4.0V, X7R, 0.1 μ F, +/-10%, AEC-Q200, Sn Term)
Multilayer Ceramic Chip Capacitor Datasheet



DIMENSIONS



	millimetres	inches
L	0.6 $\pm$ 0.03	0.024 $\pm$ 0.002
W	0.3 $\pm$ 0.03	0.012 $\pm$ 0.002
T max.	0.33	0.014
t	0.1 to 0.2	0.004 to 0.008


*Inch is for reference only.

BASIC SPECIFICATIONS


Item	Spec.	Conditions
Rated Voltage	4.0V	
Capacitance	0.1 μ F	1kHz, 0.5Vrms
Capacitance Tolerance	+/-10%	
DF Max	10 %	1kHz, 0.5Vrms
IR Min	500 M Ω	4.0Vdc, t=60s
DWV	10 Vdc	I $\leq$ 50mA, t $\leq$ 5 s

Case Size EIA (JIS)	0201(0603)
Operating Temperature	-55°C to +125°C
Dielectric	X7R
Grade	AEC-Q200
RoHS Compliant	Yes
Termination	Sn
Packaging	T&R 7in (180mm) & T&R 13in (330mm)

ELECTRICAL CHARACTERISTICS



ELECTRICAL CHARACTERISTICS



KAM03AR70G104K#

(0201, 4.0V, X7R, 0.1μF, +/-10%, AEC-Q200, Sn Term)
Multilayer Ceramic Chip Capacitor Datasheet



PART NUMBER INFORMATION

K	A	M	03	A	R7	0G	104	K	#	□□□□
1.	2.	3.	4.	5.	6.	7.	8.	9.	10.	11.
1.Symbol KAVX		5.Thickness See catalog for list of codes			8.Capacitance Capacitance expressed in pF 2 significant digits + No. of zeros For Values < 10pF Letter R denotes decimal point Example R50 0.5pF 1R0 1pF 100 10pF 101 100pF 103 10nF 105 1μF 107 100μF			10.Packing T&R 180mm(7in) H T U Y V P Q T&R 330mm(13in) M L N K S W Waffle X		
2.Grade G General A Automotive (AEC-Q200) M Medical		6.Dielectric CG C0G CH C0H R5 X5R S6 X6S T6 X6T R7 X7R S7 X7S T7 X7T R8 X8R L8 X8L G8 X8G V5 Y5V K7 X7R(KAVX)			9.Tolerance A +/-0.05pF B +/-0.1pF C +/-0.25pF D +/-0.5pF F +/-1% G +/-2% J +/-5% K +/-10% M +/-20% Z +80/-20%			11.Option See catalog for optional codes		
3.Requirement M Standard U Hi-Q E ESD T Low Profile L Low Inductance A Low Inductance (LGA) F Flexiterm® S Flexisafe Q Ultra Low ESR N 3term		7.Voltage Multiplier Base 0 1x A 1 1 10x N 1.5 2 100x C 1.6 3 1000x D 2 E 2.5 U 3 V 3.5 G 4 H 5 J 6.3 Example 1E = 25V (10 x 2.5)								
4.Size 02 01005 03 0201 05 0402 15 0603 21 0805 31 1206 32 1210 42 1808 43 1812 44 1825 55 2220 56 2225 91 3640										

Please check catalog for part number availability

NOTICE: Specifications are subject to change without notice. All statements, information and data given herein are believed to be accurate and reliable, but are presented without guarantee or responsibility of any kind, expressed or implied. Specifications are typical and may not apply to all applications.