

# Radial Leaded PTC Resettable Fuse **multicomp**PRO

RoHS  
Compliant



## Applications

Line Voltage Power Supply, Transformer and Appliances

## Features

- Low hold current, solid state, Radial leaded product ideal for up to 265V AC/DC.
- Operation Current from 0.05A to 2A
- Maximum Voltage 240V AC/DC
- Maximum Interrupt Voltage 265V AC/DC
- Temperature range: -40°C to +85°C for MC011373 to MC011380  
-20°C to +85°C for MC011381 to MC011385
- Approval: UL Approved

## Electrical Characteristics (23°C)

| Part Number | Hold Current       | Trip Current       | Max. Time to trip       | Max. Current         | Rated Voltage              | Max. Int. Voltage            | Typ. Power         | Resistance       |                   |
|-------------|--------------------|--------------------|-------------------------|----------------------|----------------------------|------------------------------|--------------------|------------------|-------------------|
|             | I <sub>H</sub> , A | I <sub>T</sub> , A | at 5×I <sub>H</sub> , S | I <sub>MAX</sub> , A | V <sub>MAX</sub> , V AC/DC | V <sub>I-MAX</sub> , V AC/DC | P <sub>d</sub> , W | R <sub>MIN</sub> | R <sub>1MAX</sub> |
| MC011373    | 0.05               | 0.12               | 15                      | 1                    | 240                        | 265                          | 0.7                | 18.5             | 65                |
| MC011374    | 0.08               | 0.19               | 15                      | 1.2                  | 240                        | 265                          | 0.8                | 7.4              | 26                |
| MC011375    | 0.12               | 0.3                | 15                      | 1.2                  | 240                        | 265                          | 1                  | 3                | 12                |
| MC011376    | 0.16               | 0.37               | 15                      | 2                    | 240                        | 265                          | 1.4                | 2.5              | 7.8               |
| MC011377    | 0.25               | 0.56               | 18.5                    | 3.5                  | 240                        | 265                          | 1.5                | 1.3              | 3.8               |
| MC011378    | 0.33               | 0.74               | 21                      | 4.5                  | 240                        | 265                          | 1.7                | 0.83             | 2.6               |
| MC011379    | 0.4                | 0.9                | 24                      | 5.5                  | 240                        | 265                          | 2                  | 0.6              | 1.9               |
| MC011380    | 0.55               | 1.25               | 26                      | 7                    | 240                        | 265                          | 3.4                | 0.45             | 1.45              |
| MC011381    | 0.75               | 1.5                | 18                      | 7.5                  | 240                        | 265                          | 2.6                | 0.32             | 0.84              |
| MC011382    | 1                  | 2                  | 21                      | 10                   | 240                        | 265                          | 2.9                | 0.22             | 0.58              |
| MC011383    | 1.25               | 2.5                | 23                      | 12.5                 | 240                        | 265                          | 3.3                | 0.17             | 0.44              |
| MC011384    | 1.5                | 3                  | 23                      | 15                   | 240                        | 265                          | 3.7                | 0.12             | 0.32              |
| MC011385    | 2                  | 4                  | 28                      | 20                   | 240                        | 265                          | 4.5                | 0.09             | 0.22              |

**I<sub>H</sub>** = Hold current-maximum current at which the device will not trip at 23°C still air.

**I<sub>T</sub>** = Trip current-minimum current at which the device will always trip at 23°C still air.

**V<sub>MAX</sub>** = Maximum voltage device can withstand without damage at its rated current.

**I<sub>MAX</sub>** = Maximum fault current device can withstand without damage at rated voltage (V max).

**P<sub>d</sub>** = Typical power dissipated from device when in the tripped state in 23°C still air environment.

**R<sub>MIN</sub>** = Minimum device resistance at 23°C.

**R<sub>1MAX</sub>** = Maximum device resistance at 23°C 1 hour after tripping.

Newark.com/multicomp-pro  
Farnell.com/multicomp-pro  
sg.element14.com/b/multicomp-pro


**multicomp**PRO

# Radial Leaded PTC Resettable Fuse **multicomp**PRO

## Physical Specifications

|                           |                                                                                                                                                                                                                                                                      |
|---------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Lead Material             | : MC011373, MC011374, MC011375 & MC011376 - Electrolytic tin plated copper, 24AWG.<br>MC011377, MC011378 & MC011379 - Electrolytic tin plated copper, 22AWG.<br>MC011380, MC011381, MC011382, MC011383, MC011384 & MC011385 - Electrolytic tin plated copper, 20AWG. |
| Soldering Characteristics | : MIL-STD-202, Method 208E.                                                                                                                                                                                                                                          |
| Insulating Coating        | : Flame retardant epoxy, meets UL-94V-0 requirement.                                                                                                                                                                                                                 |

## Dimensions




| Part Number | Figure | A       | B       | C       | D       | E       | F       |
|-------------|--------|---------|---------|---------|---------|---------|---------|
|             |        | Maximum | Maximum | Typical | Minimum | Maximum | Typical |
| MC011373    | 1      | 8.3     | 10.7    | 5.1     | 7.6     | 3.8     | 1.6     |
| MC011374    | 1      | 8.3     | 10.7    | 5.1     | 7.6     | 3.8     | 1.6     |
| MC011375    | 1      | 8.3     | 10.7    | 5.1     | 7.6     | 3.8     | 1.6     |
| MC011376    | 1      | 9.9     | 12.5    | 5.1     | 7.6     | 3.8     | 1.6     |
| MC011377    | 2      | 9.6     | 17.4    | 5.1     | 7.6     | 3.8     | 1.8     |
| MC011378    | 2      | 11.4    | 16.5    | 5.1     | 7.6     | 3.8     | 1.8     |
| MC011379    | 2      | 11.5    | 19.5    | 5.1     | 7.6     | 3.8     | 1.8     |
| MC011380    | 3      | 14      | 21.7    | 5.1     | 7.6     | 4.1     | 1.9     |
| MC011381    | 3      | 11.5    | 23.4    | 5.1     | 7.6     | 4.8     | 1.9     |
| MC011382    | 4      | 18.7    | 24.4    | 10.2    | 7.6     | 5.1     | 1.9     |
| MC011383    | 4      | 21.2    | 27.4    | 10.2    | 7.6     | 5.3     | 1.9     |
| MC011384    | 4      | 23.4    | 30.9    | 10.2    | 7.6     | 5.3     | 1.9     |
| MC011385    | 3      | 24.9    | 33.8    | 10.2    | 7.6     | 6.1     | 1.9     |

Dimensions : Millimetres


# Radial Leaded PTC Resettable Fuse **multicomp**PRO

## Thermal Derating Curve



**A:** MC011373  
MC011374  
MC011375  
MC011376  
MC011377  
MC011378  
MC011379  
MC011380  
**B:** MC011381  
MC011382  
MC011383  
MC011384  
MC011385

## Typical Time-To-Trip at 23°C



**A** = MC011373  
**B** = MC011374  
**C** = MC011375  
**D** = MC011376  
**E** = MC011377  
**F** = MC011378  
**G** = MC011379  
**H** = MC011380  
**I** = MC011381  
**J** = MC011382  
**K** = MC011383  
**L** = MC011384  
**M** = MC011385

## Part Number Table

| Description                                          | Part Number |
|------------------------------------------------------|-------------|
| PTC Resettable Fuse, 0.05A, 240V AC/DC, Through Hole | MC011373    |
| PTC Resettable Fuse, 0.08A, 240V AC/DC, Through Hole | MC011374    |
| PTC Resettable Fuse, 0.12A, 240V AC/DC, Through Hole | MC011375    |
| PTC Resettable Fuse, 0.16A, 240V AC/DC, Through Hole | MC011376    |
| PTC Resettable Fuse, 0.25A, 240V AC/DC, Through Hole | MC011377    |
| PTC Resettable Fuse, 0.33A, 240V AC/DC, Through Hole | MC011378    |
| PTC Resettable Fuse, 0.4A, 240V AC/DC, Through Hole  | MC011379    |
| PTC Resettable Fuse, 0.55A, 240V AC/DC, Through Hole | MC011380    |
| PTC Resettable Fuse, 0.75A, 240V AC/DC, Through Hole | MC011381    |
| PTC Resettable Fuse, 1A, 240V AC/DC, Through Hole    | MC011382    |
| PTC Resettable Fuse, 1.25A, 240V AC/DC, Through Hole | MC011383    |
| PTC Resettable Fuse, 1.5A, 240V AC/DC, Through Hole  | MC011384    |
| PTC Resettable Fuse, 2A, 240V AC/DC, Through Hole    | MC011385    |

**Important Notice :** This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro  
Farnell.com/multicomp-pro  
sg.element14.com/b/multicomp-pro

**multicomp**PRO