

RoHS
Compliant



Specifications

Applications : Rechargeable battery packs, Lithium cell and battery packs
 Product Features : Low profile, Solid state
 Operation Current : 1.2A to 4.2A
 Maximum Voltage : 15V to 30VDC
 Temperature Range : -40°C to 85°C
 UL and TUV Approved

Electrical Characteristics (23°C)

Part Number	Hold Current	Trip Current	Max. Time to Trip	Rated Voltage	Max. Current	Typ. Power	Resistance		
							R _{MIN}	R _{MAX}	R _{1MAX}
	I _H , A	I _T , A	at 5 × I _H , S	V _{MAX} , V _{DC}	I _{MAX} , A	P _d , W	Ω	Ω	Ω
MP008048	1.2	2.7	5	15	100	1.2	0.085	0.16	0.22
MP008049	1.75	3.8				1.5	0.05	0.09	0.12
MP008050	2	4.4	4	30		1.9	0.03	0.06	0.1
MP008051	3.5	6.3	3			2.5	0.017	0.031	0.05
MP008052	4.2	7.6	6			2.9	0.012	0.024	0.04

I_H=Hold current-maximum current at which the device will not trip at 23°C still air.

I_T=Trip current-minimum current at which the device will always trip at 23°C still air.

V_{MAX}=Maximum voltage device can withstand without damage at its rated current.

I_{MAX}= Maximum fault current device can withstand without damage at rated voltage (V_{MAX}).

P_d=Typical power dissipated from device when in tripped state in 23°C still air environment.

R_{MIN}=Minimum device resistance at 23°C.

R_{1MAX}=Maximum device resistance at 23°C, 1 hour after tripping .

Physical specifications:

Lead material:0.13mm nominal thickness, quarter-hard nickel.

Insulating material: Polyester tape.

Production Dimensions (millimeter)




Top view

Part Number	A		B		C		D		F	
	Min	Max	Min	Max	Min	Max	Min	Max	Min	Max
MP008048	19.9	22.1	4.9	5.2	0.6	1.0	5.5	7.5	3.9	4.1
MP008049	20.9	23.1	4.9	5.2	0.6	1.0	4.1	5.5	3.9	4.1
MP008050	21.3	23.4	10.2	11.0	0.5	1.1	5.0	7.6	4.8	5.4
MP008051	28.4	31.8	13.0	13.5	0.5	1.1	6.3	8.9	5.9	6.1
MP008052	30.6	32.4	12.9	13.6	0.5	1.1	5.0	7.5	5.9	6.1

Thermal Derating Curve


FSR Series



Axial Leaded PTC Resettable Fuse **multicomp**PRO

Typical Time-To-Trip at 23°C

- A = MP008048
- B = MP008049
- C = MP008050
- D = MP008051
- E = MP008052



Material Specification

Lead material: 0.13 mm nominal thickness, quarter-hard nickel
 Insulating material: Polyester tape

Part Number Table

Description	Part Number
PTC Resettable Fuse, 1.2A, Axial Leaded	MP008048
PTC Resettable Fuse, 1.75A, Axial Leaded	MP008049
PTC Resettable Fuse, 2A, Axial Leaded	MP008050
PTC Resettable Fuse, 3.5A, Axial Leaded	MP008051
PTC Resettable Fuse, 4.2A, Axial Leaded	MP008052

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro
 Farnell.com/multicomp-pro
 sg.element14.com/b/multicomp-pro

multicompPRO