



SUPERSEAL 1.0mm

TE Internal #: 8-2388688-5  
Vertical, Cable-to-Board, 34 Position, 4 Rows, 3mm [.118in]  
Centerline, Silver (Ag), Sealable, Printed Circuit Board, SUPERSEAL 1.0mm

[View on TE.com >](#)

Connectors > Automotive Connectors > Automotive Headers > SUPERSEAL 1.0 Connector Headers



PCB Mount Orientation: **Vertical**  
Termination Method to PCB: **Through Hole - Solder**  
Sealable: **Yes**  
Connector & Contact Terminates To: **Printed Circuit Board**  
Contact Current Rating (Max): **15 A**

[All SUPERSEAL 1.0 Connector Headers \(39\)](#)

Features

Product Type Features

|                                   |                       |
|-----------------------------------|-----------------------|
| Sealable                          | Yes                   |
| Connector & Contact Terminates To | Printed Circuit Board |

Configuration Features

|                       |          |
|-----------------------|----------|
| PCB Mount Orientation | Vertical |
|-----------------------|----------|

Body Features

|                       |       |
|-----------------------|-------|
| Primary Product Color | Black |
|-----------------------|-------|

Contact Features

|                              |      |
|------------------------------|------|
| Contact Current Rating (Max) | 15 A |
|------------------------------|------|

Termination Features

|                           |                       |
|---------------------------|-----------------------|
| Termination Method to PCB | Through Hole - Solder |
|---------------------------|-----------------------|

Usage Conditions

|                             |                            |
|-----------------------------|----------------------------|
| Operating Temperature Range | -40 – 125 °C[-40 – 257 °F] |
|-----------------------------|----------------------------|



Product Compliance

For compliance documentation, visit the product page on [TE.com](#)>

|                                               |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                   |
|-----------------------------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| EU RoHS Directive 2011/65/EU                  | Compliant                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                         |
| EU ELV Directive 2000/53/EC                   | Compliant with Exemptions                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                         |
| China RoHS 2 Directive MIIT Order No 32, 2016 | No Restricted Materials Above Threshold                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                           |
| EU REACH Regulation (EC) No. 1907/2006        | Current ECHA Candidate List: JAN 2025 (247)<br>Candidate List Declared Against: JAN 2025 (247)<br>SVHC > Threshold:<br>Dodecamethylcyclohexasiloxane (D6) (.71% in 20106398984)<br>Decamethylcyclopentasiloxane (D5) (.71% in 20106398984)<br>Pb (2.75% in 27042497947)<br><b>Article Safe Usage Statements:</b><br>Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location. |
| Halogen Content                               | Not Low Halogen - contains Br or Cl > 900 ppm.                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                    |
| Solder Process Capability                     | Not reviewed for solder process capability                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                        |





Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE’s information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) ‘Guidance on requirements for substances in articles’(Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of ‘complex object’, the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA “Guidance on requirements for substances in articles” (June 2017, version 4.0) and will be updating its statements accordingly.


Compatible Parts



Also in the Series | **SUPERSEAL 1.0mm**



Customers Also Bought





Documents

Product Drawings

SUPERSEAL 34P HDR VER COD 1 W/GEAR

English

CAD Files

3D PDF

3D

Customer View Model

ENG\_CVM\_CVM\_8-2388688-5\_A.3d\_stp.zip

English

Customer View Model

ENG\_CVM\_CVM\_8-2388688-5\_A.2d\_dxf.zip

English

Customer View Model

ENG\_CVM\_CVM\_8-2388688-5\_A.3d\_igs.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Product Specification

English