



Figure similar

SIMATIC S7-1200, Digital I/O SM 1223, 16 DI/16 DO, 16 DI 24 V DC, Sink/Source, 16 DO, relay 2 A

General information	
Product type designation	SM 1223, DI 16x24 V DC, DQ 16x relay
Supply voltage	
Rated value (DC)	24 V
permissible range, lower limit (DC)	20.4 V
permissible range, upper limit (DC)	28.8 V
Input current	
from backplane bus 5 V DC, max.	180 mA
Digital inputs	
• from load voltage L+ (without load), max.	4 mA/input 11 mA/relay
output voltage / header	
supply voltage of the transmitters / header	
• present	Yes
Power loss	
Power loss, typ.	10 W
Digital inputs	
Number of digital inputs	16
• in groups of	2
Input characteristic curve in accordance with IEC 61131, type 1	Yes
Number of simultaneously controllable inputs	
all mounting positions	
— up to 40 °C, max.	16
horizontal installation	
— up to 40 °C, max.	16
— up to 50 °C, max.	16
vertical installation	
— up to 40 °C, max.	16
Input voltage	
• Type of input voltage	DC
• Rated value (DC)	24 V
• for signal "0"	5 V DC at 1 mA
• for signal "1"	15 V DC at 2.5 mA
Input current	
• for signal "0", max. (permissible quiescent current)	1 mA
• for signal "1", min.	2.5 mA
• for signal "1", typ.	4 mA
Input delay (for rated value of input voltage)	
for standard inputs	
— parameterizable	Yes; 0.2 ms, 0.4 ms, 0.8 ms, 1.6 ms, 3.2 ms, 6.4 ms and 12.8 ms, selectable in

	groups of four
for interrupt inputs	
— parameterizable	Yes
Cable length	
• shielded, max.	500 m
• unshielded, max.	300 m
Digital outputs	
Number of digital outputs	16
• in groups of	4
Short-circuit protection	No; to be provided externally
Switching capacity of the outputs	
• with resistive load, max.	2 A
• on lamp load, max.	30 W with DC, 200 W with AC
Output voltage	
• Rated value (DC)	5 V DC to 30 V DC
• Rated value (AC)	5 V AC to 250 V AC
Output current	
• for signal "1" rated value	2 A
• for signal "1" permissible range, max.	2 A
Output delay with resistive load	
• "0" to "1", max.	10 ms
• "1" to "0", max.	10 ms
Total current of the outputs (per group)	
horizontal installation	
— up to 50 °C, max.	8 A; Current per mass
Relay outputs	
• Number of relay outputs	16
• Rated supply voltage of relay coil L+ (DC)	24 V
• Number of operating cycles, max.	mechanically 10 million, at rated load voltage 100 000
Switching capacity of contacts	
— with inductive load, max.	2 A
— on lamp load, max.	30 W with DC, 200 W with AC
— with resistive load, max.	2 A
Cable length	
• shielded, max.	500 m
• unshielded, max.	150 m
Interrupts/diagnostics/status information	
Alarms	
• Diagnostic alarm	Yes
Diagnostics indication LED	
• for status of the inputs	Yes
• for status of the outputs	Yes
Potential separation	
Potential separation digital inputs	
• between the channels, in groups of	2
Potential separation digital outputs	
• between the channels	Relays
• between the channels, in groups of	4
• between the channels and backplane bus	1 500 V AC for 1 minute
Permissible potential difference	
between different circuits	750 V AC for 1 minute
Degree and class of protection	
IP degree of protection	IP20
Standards, approvals, certificates	
CE mark	Yes
CSA approval	Yes
UL approval	Yes
cULus	Yes
FM approval	Yes
RCM (formerly C-TICK)	Yes

KC approval	Yes		
Marine approval	Yes		
Ecological footprint			
• environmental product declaration	Yes		
Global warming potential			
— global warming potential, (total) [CO2 eq]	123 kg		
— global warming potential, (during production) [CO2 eq]	12.1 kg		
— global warming potential, (during operation) [CO2 eq]	111 kg		
— global warming potential, (after end of life cycle) [CO2 eq]	-0.434 kg		
Ambient conditions			
Free fall			
• Fall height, max.	0.3 m; five times, in product package		
Ambient temperature during operation			
• min.	-20 °C		
• max.	60 °C; Number of simultaneously activated outputs: 8 (no adjacent points) at 60 °C horizontal or 50 °C vertical, 16 at 55 °C horizontal or 45 °C vertical		
• horizontal installation, min.	-20 °C		
• horizontal installation, max.	60 °C		
• vertical installation, min.	-20 °C		
• vertical installation, max.	50 °C		
• permissible temperature change	5°C to 55°C, 3°C / minute		
Ambient temperature during storage/transportation			
• min.	-40 °C		
• max.	70 °C		
Air pressure acc. to IEC 60068-2-13			
• Storage/transport, min.	660 hPa		
• Storage/transport, max.	1 080 hPa		
Relative humidity			
• Operation at 25 °C without condensation, max.	95 %		
connection method			
required front connector	Yes		
Mechanics/material			
Enclosure material (front)			
• Plastic	Yes		
Dimensions			
Width	70 mm		
Height	100 mm		
Depth	75 mm		
Weights			
Weight, approx.	350 g		
Classifications			
		Version	Classification
	eClass	14	27-24-22-04
	eClass	12	27-24-22-04
	eClass	9.1	27-24-22-04
	eClass	9	27-24-22-04
	eClass	8	27-24-22-04
	eClass	7.1	27-24-22-04
	eClass	6	27-24-22-04
	ETIM	10	EC001419
	ETIM	9	EC001419
	ETIM	8	EC001419
	ETIM	7	EC001419
	IDEA	4	3566
	UNSPSC	15	32-15-17-05

Approvals / Certificates

General Product Approval	Test Certificates
--------------------------	-------------------



[Type Test Certificates/Test Report](#)

Test Certificates	Maritime application	other
-------------------	----------------------	-------

[Special Test Certificate](#)



[Confirmation](#)



Environment



[Environmental Confirmations](#)

last modified:

4/6/2025