



The MSA range of eye protection has been designed to protect workers from immediate and long-term dangers. Our products have been designed to provide the ideal balance between fit, comfort, protection and style. High strength, lightweight materials are used to provide robustness for frames and lenses whilst the latest technology delivers hard coating, anti scratch lenses and anti fog properties.

MSA offers spectacles, goggles and welding helmets for a variety of work applications that involve an immediate risk of impact from flying debris, chemical splash, dust, sparks and glare.

In addition, all MSA spectacles offer 100% protection from harmful UV rays to protect against long-term cumulative eye damage.

MSA
100% UV
EYE PROTECTION

Eye Protection

MSA Premium Eyewear Range

Interceptor

- Full Polycarbonate Semi Rimless Frame
- Curved Rubber Temple Tips
- Wide Rubber Nose Bridge
- Panoscopic Tilt 8 Base Polycarbonate Curve Lens
- 100% UV 380 (Clear Lens) or 100% UV 400 (Smoke and Mirror Lenses)
- Anti-Fog / Anti-Scratch lens (Non Mirror Lenses Only)
- 100% Distortion Free
- Certified to AS/NZS 1337 Medium Velocity Impact



Blue Frame Clear
C-Max Lens
765707CF



Blue Frame Clear
C-Max Lens
765707SF



Blue Frame
Blue Mirror
Hard Coat Lens
765707BM

Bronx

- Encased tough polycarbonate frame
- 3 point length adjustable arm
- Large paddle styled rubber temple tips
- Anti scratch/anti fog lens coating
- Certified to AS/NZS 1337 Medium Velocity Impact



Clear
765013C



Smoke
765013S



Amber
765013A

Boxa

- C-Max™ UV 400 coated lenses
- Feather weight 28gms
- Sleek and smooth finish
- Eye cupping 10 base curve lenses
- Tough all polycarb construction UV400
- Rubber insert temple tips
- Certified to AS/NZS 1337 Medium Velocity Impact
- Moulded Nose Bridge
- Anti-Scratch, Anti-Fog Lens



Amber
765014A



Clear
765014C



Smoke
765014M



Smoke
765014S

Refer page 67 for Mini-Boxa

Shape Shifter

- Advanced Anti-Fog Coating (Clear, Amber and Smoke)
- RX Adaptable (for prescription lens)
- UV 400 Polycarbonate Lenses
- Hard Coated
- Certified to AS/NZS 1337 Medium Velocity Impact
- Standard item
(includes non-vented foam insert and nose bridge insert)



Clear
765870CF



Smoke
765870SF



Amber
765870AF



Blue Mirror
765870BM



Silver Mirror w/shields
765870SM

Part No.	Description
765871	Non-vented Foam Insert
765872	Semi-vented Closed Cell Foam Insert
765877	Nose Bridge Insert (supports smaller nose bridge size)
765873	Adjustable Nose Bridge RX Adaptor
765874	2 Function LED Temple Arms
765875	Adjustable Elastic Strap
766373	Non-vented Foam Insert RX

RX-1

- Functional and practical RX insert
- RX Adaptor made of stainless steel construction
- Suitable for prescription lenses including High Index Lenses
- Rubber insert temple tips
- Certified to AS/NZS 1337 Medium Velocity Impact



765015C Clear Lens
Gunmetal Frame with
RX Adaptor



765015FC
Frame Only
Clear Lens



765015S
Smoke Lens Gunmetal
Frame with RX Adaptor



765015FS
Frame Only
Smoke Lens

Eye Protection

Milan

The Milan range of European Styled spectacles offer superior safety and are designed for today's fashion. The Milan allows you to feel and, look good while remaining safe at work.

As well as being AS/NZS standards certified, the lenses are Anti-fog. The Anti-fog lenses are available in Smoke, Light Gold and Clear.

What more could you ask for in a safety spectacle - stylish, fashionable and safe.

SAFETY HAS NEVER LOOKED SO GOOD!!!



Clear
765929CF



Smoke
765929SF



Lite Gold Anti-fog
765929LF

Torin

High quality black fashion frame with matt metal finishes delivers a classy safety spectacle that just wants to be worn. The anti scratch/anti fog lens delivers superb optics for excellent vision with medium velocity impact and UV400 protection.

The low profile side arms ensure a comfortable fit and the fitted nosebridge eliminates annoying slippage.

Certified to AS/NZS1337, the Torin eyewear range is available in smoke anti fog, lite gold anti fog and blue mirror lenses that are also anti scratch to provide long lasting protection.



Blue Mirror
766318BM



Smoke
766318SF



Lite Gold Anti-fog
766318LF

Grayz

Cool and stylish wrap around design with a funky edge styling sets this spectacle apart from the rest. The light weight frame provides a face hugging fit and a high base curve that delivers exceptional panoramic vision and safety. The co-injection side arms have great flexibility to fit all head sizes and deliver superb all day comfort.

Certified to AS/NZS1337, the Grayz is available in clear anti fog, smoke anti fog, lite gold anti fog and blue mirror lenses that are also anti scratch to provide long lasting protection.



Blue Mirror
766317BM



Smoke
766317SF



Lite Gold Anti-fog
766317LF



Clear
766317CF

- Certified to AS/NZS 1337 Medium Velocity Impact

Ideal for use indoor and outdoors.

100% UV protection, lightweight and comfortable.

- Popular Wrap Around Style - Wide Vision Lens

- Lightweight Frame - Blue Mirror Lens for
Maximum Glare Protection

AS/NZS 1337 Lic1502
SAI Global

Each Arctic Gold comes in its own protective, soft carry pouch that doubles as a cleaning cloth.

- Lightweight for All Day Comfort - Wraparound styling for maximum protection - 100% UV 400 Protection
- Anti Fog Coating for Humid Environments

Anti-Fog Clear Lens for Indoor Protection, Smoke Lens for
Outdoor Protection, Lite-Gold Lens for Indoor/Outdoor
Protection and Gold Mirror Lens for Glare Protection

Eye Protection

Nullarbor

- Stylish wraparound design
- Wide vision hard coated lens
- Robust nylon frame
- Certified to AS/NZS 1337 Medium Velocity Impact



Quality protection in a stylish wrap around look and scratch resistant lens.

The polycarbonate scratch resistant lenses offer 100% UV protection with wide vision and built in side impact protection.

- Popular Wrap Around Style - Lightweight Frame with soft feel temple ends

Clear Lens for Indoor Protection, Smoke Lens for Outdoor Protection and Blue Mirror Lens for Glare Protection. Lite Gold Lens for Indoor/Outdoor Protection. Optional Anti-Fog coating available on Clear Lens and Lite Gold.

Refer page 67 for Mini-Nullarbor

Discovery

- Wraparound lenses
- Adjustable length side arms
- Hard coat anti scratch lens
- Certified to AS/NZS 1337 Medium Velocity Impact



Platinum

- High quality nickel silver frame
- Stainless steel sidearms tipped in natural rubber
- Industrial wide-vision with non-removable sideshields
- Ideal for use with prescription lenses
- Certified to AS/NZS 1337 Medium Velocity Impact



Clear w/shields
229305



Smoke w/shields
229306



Silver Mirror w/shields
229307

Stylish metal framed spectacle featuring a high quality nickel silver frame with stainless steel sidearms tipped in natural rubber to ensure a firm grip. Available with a choice of three scratch resistant lens styles: Clear, smoke and silver mirror.

All models feature 100% UV protection.
Frame suitable for fitting prescription lenses.



Glacier

- Available in 3 frame colours: Champagne, Smoke & Blue
- Certified to AS/NZS 1337 Medium Velocity Impact
- Hard coat anti scratch lens
- Soft feel frame
- Stylish wraparound coverage



Smoke Frame
Smoke 228007SS



Smoke Frame
Lite Gold 228007SL



Smoke Frame
Lite Blue 228007SB



Champagne Frame
Smoke 228007CS



Champagne Frame
Orange 228007CO



Champagne Frame
Lite Gold 228007CL



Champagne Frame
Clear 228007CC



Supervue

- Wraparound style with rolled edges
- Optimum visibility, comfort & protection
- Side vents provide superior ventilation
- Internal space allows prescriptive glasses to be worn underneath
- Certified to AS/NZS 1337 Medium Velocity Impact



Clear
225228





FlexiPlus Protective Goggles

- Certified to AS/NZS 1337 Medium Velocity Impact



Foam bound
Clear Anti-fog unvented
29206CFV

Goggles

Scope Goggle

- Low Profile Design
- Light Weight Frosted Grey PVC Frame
- Indirect Vented Frame
- 2mm Anti-Fog Anti-Scratch Coated Lens
- 25mm Elastic Strap
- Certified to AS/NZS 1337 Medium Velocity Impact



Clear
765927CF

Velocity Goggle

- Extremely Low Profile Design
- Co Injected PC / Rubber Frame
- Indirect Vented Frame
- 2mm Anti-Fog Anti-Scratch Coated Clear Lens
- 25mm Elastic Strap
- Certified to AS/NZS 1337 Splash Proof



Clear
765928CF

FlexiFold Goggle

- Flexible, face hugging goggle with adjustable strap
- Scratch resistant anti-fog polycarbonate lens
- Dust/waterproof sponge cupping
- Open/close side ventilation
- Ideal smoke protective goggle for bushfire fighting
- Certified to AS/NZS 1337 Medium Velocity Impact



Clear
228028CL



Smoke
228028SM



FlexiWeld Goggles

- Certified to AS/NZS 1337 Medium Velocity Impact

Two models – Shade 5 for Gas Welding and Shade 3 for Welder's Assistants.

Stylish soft-frame welding goggles designed to comfortably fit most facial contours. Roomy design allows for wearing over most prescription eyewear.

One piece polycarbonate, scratch resistant lens. Protects against welding and chemical splatter and UV rays, while permitting unobstructed viewing.



Shade 3
229405



Shade 5
229406

Flashmaster 'Flip-Up' Welding Goggles

- Dual Purpose Goggle
- Ideal for gas welding, chipping & grinding
- Easy replacement welding filter & protective cover lenses

Description	Part No.
Cover lens Clear Polycarbonate	220038
Cover lens Clear CR39	220038CR
Welding Lens Shade 4	220321
Welding Lens Shade 5	220322
Welding Lens Shade 6	220323



220343

Flashmaster Welding Helmet

- Ideal for electrical welding
- Made from polypropylene to combine strength, lightweight, and chemical resistance
- Fitted with Shade 10 welding lens
- Replaceable CR39 cover lens protecting filter
- Impact resistant clear polycarbonate backing lens
- Adjustable head diameter, height & faceshield angle
- Padded cloth headband for added comfort

Description	Part No.
Cover lens Clear Polycarbonate	220035
Cover lens Clear CR39	220035CR
Cover lens Clear Glass	220316
Welding Lens Shade 8	220324
Welding Lens Shade 9	220325
Welding Lens Shade 10	220326
Welding Lens Shade 11	220327
Welding Lens Shade 12	220328
Welding Lens Shade 13	225491
Welding Lens Shade 14	220628



221681