



## Capacitance Range (X5R)

Dielectric	X5R					
	0805			1206		
Size						
Rated Voltage (V dc)	6.3 (V)	10 (V)	16 (V)	6.3 (V)	10 (V)	16 (V)
0.22 (224)	-	-	-	-	-	-
1µF (105)	-	T	T	-	T	T
1.5µF (154)	-			-		
2.2 (225)	T	-	-			
3.3 (335)	-	-	-			
4.7 (475)	T	-	-	-	-	-
6.8 (685)	-	-	-	-	-	-
10µF (106)	-	-	-	T	J	-
2.2µF (226)	-	-	-	-	-	-

## Capacitance Range (Y5V)

Dielectric	Y5V				
	0805		1206		
Size					
Rated Voltage (V dc)	10 (V)	16 (V)	6.3 (V)	10 (V)	16 (V)
0.22 (224)	-	-	-	-	-
1µF (105)	-	-	-	-	-
1.5µF (154)	-	-	-	-	-
2.2 (225)	-	T	-	-	-
3.3 (335)	T	-	-	-	-
4.7 (475)		-	-	-	T
6.8 (685)	-	-	-	T	-
10µF (106)	-	-	-		J
2.2µF (226)	-	-	-	-	-

## Dimensions Table

Size [Inch (mm)]	Thickness (mm)/Symbol	
0805 (2012)	0.95	T
1206 (3216)		
	1.25	J

Dimensions : Inches (Millimetres)

## Dimensions

Size [Inch (mm)]	L (mm)	W (mm)	M <sub>B</sub> (mm)
0805 (2012)	2.00 ±0.15	1.25 ±0.10	0.50 ±0.20
	2.00 ±0.20	1.25 ±0.20	
1206 (3216)	3.20 ±0.15	1.60 ±0.15	0.60 ±0.20
	3.20 ±0.20	1.60 ±0.20	
		1.60 + 0.30/-0.10	

Dimensions : Inches (Millimetres)

## Specification Table

Description	Dielectric	Size [Inch (mm)]	Capacitance	Tolerance	Rated Voltage (V dc)	Part Number
MLCC, 0805, X5R, 6.3V, 2.2µF	X5R	0805 (2012)	2.2µF	±10%	6.3	MCCA000591
MLCC, 0805, X5R, 6.3V, 4.7µF		0805 (2012)	4.7µF	±10%, ±20%		MCCA000592
MLCC, 0805, X5R, 6.3V, 10µF		0805 (2012)	10µF	±20%		MCCA000593
MLCC, 0805, X5R, 10V, 2.2µF	Y5V	0805 (2012)	2.2µF	±10%, ±20%	10	MCCA000594
MLCC, 0805, Y5V, 10V, 4.7µF		1206 (3216)	4.7µF	-20/ +80%		MCCA000595
MLCC, 0805, X5R, 16V, 1µF	X5R	0805 (2012)	1µF	±10%	16	MCCA000596
MLCC, 0805, Y5V, 16V, 2.2µF	Y5V	0805 (2012)	2.2µF	-20/80%		MCCA000597
MLCC, 0805, X5R, 16V, 2.2µF	X5R	0805 (2012)	2.2µF	±10%, ±20%		MCCA000598
MLCC, 0805, Y5V, 16V, 4.7µF	Y5V	0805 (2012)	4.7µF	-20/80%		MCCA000599

Dimensions : Inches (Millimetres)

## Specification Table

Description	Dielectric	Size [Inch (mm)]	Capacitance	Tolerance	Rated Voltage (V dc)	Part Number
MLCC, 1206, X5R, 6.3V, 10 $\mu$ F	X5R	1206 (3216)	10 $\mu$ F	$\pm$ 20%	6.3	MCCA000600
MLCC, 1206, X5R, 10V, 2.2 $\mu$ F		0805 (2012)	2.2 $\mu$ F	$\pm$ 10%, $\pm$ 20%	10	MCCA000601
MLCC, 1206, Y5V, 10V, 10 $\mu$ F	Y5V	1206 (3216)	10 $\mu$ F	-20/ +80%		10
MLCC, 1206, Y5V, 10V, 22 $\mu$ F		1206 (3216)	22 $\mu$ F	-20/80%	MCCA000604	

1. This series product is suited to reflow soldering process only.

Dimensions : Inches (Millimetres)

**Disclaimer** This data sheet and its contents (the "Information") belong to the Premier Farnell Group (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. SPC Multicomp is the registered trademark of the Group. © Premier Farnell plc 2009.