


Number of contacts


**max. 32**



**Female connectors**

Identification	Number of contacts	Part No.	Drawing	Dimensions in mm
Female connector for crimp contacts Order contacts separately	32	09 04 032 3213		
			<p>Shell housing 09 03 096 0501 page 94</p>	

Contact arrangement View from termination side



Identification	Wire gauge	Part No.	Performance levels according to DIN 41 612, explanations page 10	Special	
		2	1		
Female crimp contacts					
	Bandoliered contacts (approx. 2500 pieces)	1	09 06 000 6484	09 06 000 6474	09 06 000 6424
		2	09 06 000 6481	09 06 000 6471	09 06 000 6421
	3	09 06 000 6482	09 06 000 6472	09 06 000 6422	
Bandoliered contacts (approx. 300 pieces)	1	09 06 000 9484	09 06 000 9474	please check change-over to performance level 1 or 2	09 06 000 9421
	2	09 06 000 9481	09 06 000 9471		09 06 000 9422
	3	09 06 000 9482	09 06 000 9472		09 06 000 9421
Individual contacts	1	09 06 000 8484	09 06 000 8474	09 06 000 6434	
	2	09 06 000 8481	09 06 000 8471	09 06 000 6431	
	3	09 06 000 8482	09 06 000 8472	09 06 000 6432	
Female contacts with solder lugs (lockable)	-			09 06 000 6420	

Wire gauge	Insulation Ø
mm <sup>2</sup>	mm
1 0.09 - 0.25	28 - 24 0.7 - 1.5
2 0.14 - 0.56	26 - 20 0.8 - 2.0
3 0.5 - 1.5	20 - 16 1.6 - 2.8

3.5 + 0.5 mm of insulation is stripped from the wires to be crimped  
Crimping tools page 91

