

Kemtron

TE Internal #: 2420726-1

Oriented Wire EMI Gasket, Conductive Sheet, Fluorosilicone Binding, Rectangular, 2.4 mm [.094 in] Thick, 1 m [3.28 ft] Length, Kemtron 450 Series

[View on TE.com >](#)



Gasket Type: **Oriented Wire EMI Gasket**
Finished Type: **Conductive Sheet**
Binding Material: **Fluorosilicone**
Gasket Shape: **Rectangular**
Product Thickness: **2.4 mm [.094 in]**

[All Oriented Wire EMI Gasket \(28\)](#)

Features

Product Type Features

Finished Type	Conductive Sheet
Binding Material	Fluorosilicone
Gasket Wire Material Type	Nickel-Copper Alloy
Closing Force	102 N/cm²

Electrical Characteristics

Resistance to Petroleum	Yes
-------------------------	-----

Body Features

Gasket Type	Oriented Wire EMI Gasket
Gasket Shape	Rectangular

Dimensions

Product Thickness	2.4 mm[.094 in]
Product Length	1 m[3.28 ft]
Product Width	150 mm[5.905 in]



Usage Conditions

Operating Temperature Range	-67 – 392 °C[-76 – 392 °F]
-----------------------------	----------------------------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2023 (233) Does not contain REACH SVHC
Halogen Content	Low Bromine/Chlorine - Br and Cl < 900 ppm per homogenous material. Also BFR /CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



Customers Also Bought




TE Part #DT06-2S
PLG, 2P, GRY, N



TE Part #CAT-D487-W416
Wedgelocks: DEUTSCH DT



TE Part #DT04-2P
REC, 2P, GRY, N



TE Part #CAT-D48-ST273
DEUTSCH Solid Contacts



TE Part #114017-ZZ
SEALING PLUG, SIZE 12/16, WHT



TE Part #281934-2
SINGLE WIRE SEAL



TE Part #CAT-AM71-CH8172
AMP SUPERSEAL 1.5MM,
CONNECTOR HOUSING

Documents

Product Drawings

Mon Wire 50 Sh Fsil 150x1000x2.4mm Sheet

English

Datasheets & Catalog Pages

Performance Materials brochure

English

Oriented Wire In Silicone And Fluorosilicone Rubber

English

Product Specifications

Application Specification

English