



Sensors > Temperature Sensors > NTC Sensors > NTC Thermistors > Precision Glass Thermistors - 55000



NTC Sensor Type: **Glass Encapsulated NTC Thermistor**

Lead Wire Length: **65 mm [2.559 in]**

Resistance (at 25°C): **10 kΩ**

β-Value(25/85): **3978 K**

Tolerance β-Value: **±0.4 %**

[All Precision Glass Thermistors - 55000 \(19\)](#)

Features

Product Type Features

NTC Sensor Type	Glass Encapsulated NTC Thermistor
Tolerance β-Value	±0.4 %

Electrical Characteristics

β-Value(25/85)	3978 K
----------------	--------

Dimensions

Lead Wire Length	65 mm[2.559 in]
------------------	-----------------

Usage Conditions

Resistance (at 25°C)	10 kΩ
Operating Temperature Range	-55 – 150 °C[-67 – 302 °F]
Operating Temperature (Max)	150 °C[302 °F]

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Out of Scope
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold



EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 11029675-00
55004-BP GEM THERM

Also in the Series | MEAS 55000




NTC Thermistors(19)

Customers Also Bought



TE Part #GA10K3MCD1
MCD PROBE, 10K OHMS,+/- 0.2C @ 25C



TE Part #31088
BUDGET R 22-16COMM 22-18MIL 2



TE Part #34120
TERMINAL,SOLIS R 16-14 6



TE Part #794269-1
02P UMNL INTERFACE SEAL




TE Part #794821-1
08P MINI UMNL PLUG HSG



TE Part #794894-1
02P MINI UMNL PLUGS WIRE HOLES




TE Part #794896-1
2 CIR MINI UMNL RND WIRE HOLES



TE Part #1586359-2
02P MINIMUMNL GANG WIRE SEAL DR



TE Part #1586359-8
08P MINIMUMNL GANG WIRE SEAL DR



TE Part #GA15K3MBD8
MBD9-PROBE

Documents

Datasheets & Catalog Pages

Model 55000 Series Datasheet

English

Model 55036 Datasheet

English