


Metal Oxide Varistor Disk type

Ordering code: **SIOV- S25K550E4R12**
Preliminary

SIOV nomenclature

S	=	Disk type
25	=	Rated disk diameter
K	=	Tolerance of V_V at 1mA : $\pm 10\%$
550	=	Max. AC voltage
E4	=	High-Energy series
R12	=	Customized lead spacing

Figure: Dimensions given in Millimeters (mm)




Electrical data:

Maximum Ratings (85°C):


Max. operating AC voltage		V_{RMS}	=	550V
Max. operating DC voltage		V_{DC}	=	745V
Surge current (8/20 μ s)	1 time	I_{max}	=	20000A
Energy absorption (2ms)	1 time	W_{max}	=	940J
Average power dissipation		P_{max}	=	1,0W

Characteristics (25°C):


Varistor voltage at 1mA		V_V	=	$910V \pm 10\%$
Clamping voltage at 150A (8/20 μ s)		$V_{C,max}$	=	1500V
Typ. capacitance at 1 kHz		C	=	680pF


				File: S25K550E4R12_C.DO C	DATA SHEET VARISTOR SIOV- S25K550E4R12	
C	-	29.05.01			B72....*-7600 (Preliminary)	Bl./Page 2
Ausg. Issue	Mitteilung Info No.	Datum Date	Name Sign			

V/I Characteristic:



Derating:




				File: S25K550E4R12_C.DO C	DATA SHEET VARISTOR SIOV- S25K550E4R12	
C	-	29.05.01				
Ausg. Issue	Mitteilung Info No.	Datum Date	Name Sign		B72....*-7600 (Preliminary)	

Reliability Data:


	Characteristics	Test Methods/Description	Specifications
E L E C T R I C A L	Varistor Voltage	The voltage between two terminals with the specified measuring current applied is called V_V (1 mA _{DC} @ 0.2 - 2 s).	To meet the specified value.
	Clamping Voltage	The maximum voltage between two terminals with the specified standard impulse current (8/20µs) illustrated below applied.	To meet the specified value.
	Surge current derating, 8/20 µs	100 surge currents (8/20 µs), unipolar, interval 30 s, amplitude corresponding to derating curve for 20 µs	$ \Delta V/V (1 \text{ mA}) \leq 10 \%$ (measured in direction of surge current) No visible damage
	Surge current derating, 2 ms	100 surge currents (2ms), unipolar, interval 120s, amplitude corresponding to derating curve for 2ms	$ \Delta V/V (1 \text{ mA}) \leq 10 \%$ (measured in direction of surge current) No visible damage

				File: S25K550E4R12_C.DOC	DATA SHEET VARISTOR SIOV- S25K550E4R12	
C	-	29.05.01			B72....*-7600 (Preliminary)	BI/Page 4
Ausg. Issue	Mitteilung Info No.	Datum Date	Name Sign			

	Characteristics	Test Methods/Description	Specifications							
M	Tensile strength	After gradually applying the force specified below and keeping the unit fixed for 10 seconds, the terminal shall be visually examined for any damage.	$\Delta V/V$ (1 mA) $\leq 5\%$ No break of solder joint, no wire break							
		<table border="1"> <thead> <tr> <th>Terminal diameter</th> <th>Force</th> </tr> </thead> <tbody> <tr> <td>0.5 mm</td> <td>5 N</td> </tr> <tr> <td>0.6 mm</td> <td>10 N</td> </tr> <tr> <td>0.8 mm</td> <td>10 N</td> </tr> <tr> <td>1.0 mm</td> <td>20 N</td> </tr> </tbody> </table>		Terminal diameter	Force	0.5 mm	5 N	0.6 mm	10 N	0.8 mm
Terminal diameter	Force									
0.5 mm	5 N									
0.6 mm	10 N									
0.8 mm	10 N									
1.0 mm	20 N									
E C H	Vibration	After repeatedly applying a single harmonic vibration according to the table below. Thereafter, the unit shall be visually examined. frequency range: 10 55 Hz amplitude: 0.75 mm or 98 m/s ² duration: 6 h (3 x 2 h) pulse: sine wave	$\Delta V/V$ (1 mA) $\leq 5\%$ No visible damage							
A N I C A L	Solderability	After dipping the terminals to a depth of approximately 3 mm from the body in a soldering bath of 235°C for 5 seconds, the terminals shall be visually examined.	The inspection shall be carried out under adequate light with normal eyesight or with the assistance of a magnifier capable of giving a magnification of 4 times to 10 times. The dipped surface shall be covered with a smooth and bright solder coating with no more than small amounts of scattered imperfections such as pinholes or un-wetted or de-wetted areas. These imperfections shall not be concentrated in one area.							


				File: S25K550E4R12_C.DO C	DATA SHEET VARISTOR SIOV- S25K550E4R12	
C	-	29.05.01			B72....*-7600 (Preliminary)	Bl./Page 5
Ausg. Issue	Mitteilung Info No.	Datum Date	Name Sign			

	Characteristics	Test Methods/Description	Specifications
M E C H A N I C A L	Resistance to soldering heat	Each lead shall be dipped into a solder bath having a temperature of $260 \pm 5^\circ\text{C}$ to a point 2.0 to 2.5 mm from the body of the unit, be held there for 10 ± 1 s and then be stored at room temperature and normal humidity for 1 to 2 hours. The change of V_v and mechanical damages shall be examined.	$ \Delta V/V (1 \text{ mA}) \leq 5 \%$ No visible damage
	Electric strength	2500 V_{RMS} , 10 s The varistor is placed in a container holding 1.6 ± 0.2 mm diameter metal balls such that only the terminations of the varistor are protruding. The specified voltage shall be applied between both terminals of the specimen connected together and the electrode inserted between the metal balls.	No breakdown

				File: S25K550E4R12_C.DOC	DATA SHEET VARISTOR SIOV- S25K550E4R12	
C	-	29.05.01			B72....*-7600 (Preliminary)	Bl./Page 6
Ausg. Issue	Mitteilung Info No.	Datum Date	Name Sign			

	Characteristics	Test Methods/Description	Specifications												
E N V I R O N M E N T A L	Max. AC operating voltage	After being continuously applied the maximum allowable voltage at $85 \pm 2^\circ\text{C}$ for 1000 hours, the specimen shall be stored at room temperature and normal humidity for 1 to 2 hours. Thereafter, the change of V_v shall be measured.	$ \Delta V/V (1 \text{ mA}) \leq 10 \%$												
	Damp heat, steady state	The specimen shall be subjected to $40 \pm 2^\circ\text{C}$, 90 to 95 % r.H. for 56 days without load and then stored at room temperature and normal humidity for 1 to 2 hours. Thereafter, the change of V_v shall be measured.	$ \Delta V/V (1 \text{ mA}) \leq 10 \%$												
	Climatic sequence	The specimen shall be subjected to: a) dry heat at $+85^\circ\text{C}$, 16 h b) damp heat, 1st cycle: 55°C , 93 % r.H., 24 h c) cold, -40°C , 2 h d) damp heat, additional 5 cycles: 55°C , 93 % r.H., 24 h/cycle Then the specimen shall be stored at room temperature and normal humidity for 1 to 2 hours. Thereafter, the change of V_v shall be measured.	$ \Delta V/V (1 \text{ mA}) \leq 10 \%$												
	Fast temperature cycling	The temperature cycle shown below shall be repeated 5 times. Then the specimen shall be stored at room temperature and normal humidity for 1 to 2 hours. The change of V_v and mechanical damage shall be examined.	$ \Delta V/V (1 \text{ mA}) \leq 5 \%$ No visible damage												
		<table border="1"> <thead> <tr> <th>Step</th> <th>Temperature ($^\circ\text{C}$)</th> <th>Period (min.)</th> </tr> </thead> <tbody> <tr> <td>1</td> <td>-40 ± 3</td> <td>30 ± 3</td> </tr> <tr> <td>2</td> <td>transition time</td> <td>< 10 s</td> </tr> <tr> <td>3</td> <td>85 ± 2</td> <td>30 ± 3</td> </tr> </tbody> </table>	Step	Temperature ($^\circ\text{C}$)	Period (min.)	1	-40 ± 3	30 ± 3	2	transition time	< 10 s	3	85 ± 2	30 ± 3	
Step	Temperature ($^\circ\text{C}$)	Period (min.)													
1	-40 ± 3	30 ± 3													
2	transition time	< 10 s													
3	85 ± 2	30 ± 3													

Note: More details can be found in the data book 'SIOV Metal Oxide Varistors', Ordering No. EPC: 62002-7600

				File: S25K550E4R12_C.DO C	DATA SHEET VARISTOR SIOV- S25K550E4R12	
C	-	29.05.01			B72....*-7600 (Preliminary)	Bl./Page 7
Ausg. Issue	Mitteilung Info No.	Datum Date	Name Sign			