



Wire & Cable > Wire & Cable Accessories > Cable Ties



Cable Tie Style: **Standard**
Packaging Method: **Bag**
Tensile Strength: **130 Newton**
Product Length: **140 mm [5.5 in]**

Features

Product Type Features

Cable Tie Style	Standard
Tensile Strength	130 Newton

Body Features

Primary Product Color	Black
Primary Product Material	Polyamide 6.6 GF

Dimensions

Compatible Cable Bundle Diameter Range	35 mm[1.37 in]
Product Length	140 mm[5.5 in]
Product Width	3.6 mm[.141 in]
Product Thickness	1.2 mm[.047 in]

Packaging Features

Packaging Method	Bag
Packaging Quantity	1000

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold



EU REACH Regulation (EC) No. 1907/2006

Current ECHA Candidate List: JAN 2025 (247)
Candidate List Declared Against: JAN 2025 (247)
Does not contain REACH SVHC

Halogen Content

Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free

Solder Process Capability

Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>




Compatible Parts

 TE Part # EC6497-000 13611443	 TE Part # 0628890001 CM-SCE-1/2-4H-2L	 TE Part # 823954-000 CM-SCE-TP-2.5K-1/4-4H-9	 TE Part # EC6523-000 13611904
 TE Part # EC6541-000 13611922	 TE Part # EC6406-000 13611101	 TE Part # EC6546-000 13611927	 TE Part # EC6494-000 13611440



 TE Part # EC6543-000 13611924	 TE Part # EC6550-000 13611931	 TE Part # EC6481-000 13611427	 TE Part # EC6409-000 13611202
 TE Part # EC6498-000 13611444	 TE Part # EC6535-000 13611916	 TE Part # EC6471-000 13611417	 TE Part # EC6526-000 13611907
 TE Part # EC6457-000 13611403	 TE Part # EC6484-000 13611430	 TE Part # EC6538-000 13611919	 TE Part # EC6548-000 13611929

Customers Also Bought

 TE Part #2-100693-2 MOUNTING BASE,BLACK	 TE Part #1-1563844-3 MCON 9.5,CONTACT	 TE Part #2272162-1 MCON WIRE DRESS, 4P, STRAIGHT	 TE Part #CAT-M8793-CH8172 MQS, CONNECTOR HOUSING
 TE Part #2401461-1 30POS,HYBRID,TAB HSG ASSY,SLD, COD A	 TE Part #1274412-1 SMB PCB RIGHT ANGLE JACK	 TE Part #2294663-1 6P MQS SHEILD ASSY WITH CPA	 TE Part #2310000-1 10POS,MQS,REC HSG ASSY,UNSLD, COD A



Documents

Product Drawings

CABLE TY 140X3.6 BLACK

English

Datasheets & Catalog Pages

CABLE TIES

English

Agency Approvals

Agency Approval Document

English