



Material Safety Data Sheet

Copyright, 2007, 3M Company. All rights reserved. Copying and/or downloading of this information for the purpose of properly utilizing 3M products is allowed provided that: (1) the information is copied in full with no changes unless prior written agreement is obtained from 3M, and (2) neither the copy nor the original is resold or otherwise distributed with the intention of earning a profit thereon.

SECTION 1: PRODUCT AND COMPANY IDENTIFICATION

PRODUCT NAME: EG4 SEALANT FOR SERIES 1 & SERIES 2 SCOTCHLOK CONNECTORS
MANUFACTURER: 3M
DIVISION: Communication Markets Division
ADDRESS: 3M Center
 St. Paul, MN 55144-1000

EMERGENCY PHONE: 1-800-364-3577 or (651) 737-6501 (24 hours)

Issue Date: 08/28/2007
Supersedes Date: 01/11/2007

Document Group: 16-2710-8

Product Use:

Intended Use: EG4 SEALANT FOR SERIES 1 & SERIES 2 SCOTCHLOK CONNECTORS
 Specific Use: SEALANT

SECTION 2: INGREDIENTS

<u>Ingredient</u>	<u>C.A.S. No.</u>	<u>% by Wt</u>
SEALANT	Trade Secret	100

SECTION 3: HAZARDS IDENTIFICATION

3.1 EMERGENCY OVERVIEW

Specific Physical Form: Viscous MITS data
Odor, Color, Grade: Clear, water white paste, bland odor
General Physical Form: Solid
Immediate health, physical, and environmental hazards: environmental hazard.

The environmental properties of this product present a low environmental hazard.

3.2 POTENTIAL HEALTH EFFECTS

Eye Contact:
 Mild Eye Irritation: Signs/symptoms may include redness, pain, and tearing.

Skin Contact:

Mild Skin Irritation: Signs/symptoms may include localized redness, swelling, and itching.

Inhalation:

No health effects are expected.

Ingestion:

Gastrointestinal Irritation: Signs/symptoms may include abdominal pain, nausea, diarrhea and vomiting.

3.3 POTENTIAL ENVIRONMENTAL EFFECTS

This substance does not leach metals or other RCRA (Resource Conservation and Recovery Act) listed TCLP (Toxic Characteristic Leaching Procedure) hazardous substances at concentrations that would make the product a hazardous waste.

SECTION 4: FIRST AID MEASURES

4.1 FIRST AID PROCEDURES

The following first aid recommendations are based on an assumption that appropriate personal and industrial hygiene practices are followed.

Eye Contact: Flush eyes with large amounts of water. If signs/symptoms persist, get medical attention.

Skin Contact: Wash affected area with soap and water. If signs/symptoms develop, get medical attention.

Inhalation: No need for first aid is anticipated.

If Swallowed: Do not induce vomiting. Give victim two glasses of water. Never give anything by mouth to an unconscious person. Get immediate medical attention.

SECTION 5: FIRE FIGHTING MEASURES

5.1 FLAMMABLE PROPERTIES

Autoignition temperature	<i>No Data Available</i>
Flash Point	<i>Not Applicable</i>
Flammable Limits - LEL	<i>No Data Available</i>
Flammable Limits - UEL	<i>No Data Available</i>
OSHA Flammability Classification:	Not Determined

5.2 EXTINGUISHING MEDIA

Ordinary combustible material. Use fire extinguishers with class A extinguishing agents (e.g., water, foam). Use fire extinguishers with class B extinguishing agents (e.g., dry chemical, carbon dioxide).

5.3 PROTECTION OF FIRE FIGHTERS

Special Fire Fighting Procedures: Wear full protective equipment (Bunker Gear) and a self-contained breathing apparatus (SCBA).

Unusual Fire and Explosion Hazards: Not applicable.

Note: See STABILITY AND REACTIVITY (SECTION 10) for hazardous combustion and thermal decomposition information.

SECTION 6: ACCIDENTAL RELEASE MEASURES

Accidental Release Measures: Evacuate unprotected and untrained personnel from hazard area. The spill should be cleaned up by qualified personnel. Collect as much of the spilled material as possible. Place in a closed container approved for transportation by appropriate authorities.

In the event of a release of this material, the user should determine if the release qualifies as reportable according to local, state, and federal regulations.

SECTION 7: HANDLING AND STORAGE

7.1 HANDLING

Do not eat, drink or smoke when using this product. Wash exposed areas thoroughly with soap and water. Avoid prolonged or repeated skin contact. Keep out of the reach of children. For industrial or professional use only.

7.2 STORAGE

Store under normal warehouse conditions.

SECTION 8: EXPOSURE CONTROLS/PERSONAL PROTECTION

8.1 ENGINEERING CONTROLS

Not applicable.

8.2 PERSONAL PROTECTIVE EQUIPMENT (PPE)

8.2.1 Eye/Face Protection

Avoid eye contact.

The following eye protection(s) are recommended: Safety Glasses with side shields.

8.2.2 Skin Protection

Gloves not normally required. Avoid prolonged or repeated skin contact.

8.2.3 Respiratory Protection

Under normal use conditions, airborne exposures are not expected to be significant enough to require respiratory protection.

8.2.4 Prevention of Swallowing

Do not eat, drink or smoke when using this product. Wash exposed areas thoroughly with soap and water.

8.3 EXPOSURE GUIDELINES

None Established

SECTION 9: PHYSICAL AND CHEMICAL PROPERTIES

Specific Physical Form:	Viscous MITS data
Odor, Color, Grade:	Clear, water white paste, bland odor
General Physical Form:	Solid
Autoignition temperature	<i>No Data Available</i>
Flash Point	<i>Not Applicable</i>
Flammable Limits - LEL	<i>No Data Available</i>
Flammable Limits - UEL	<i>No Data Available</i>
Boiling point	<i>Not Applicable</i>
Density	<i>Not Applicable</i>
Vapor Density	<i>No Data Available</i>
Vapor Density	<i>Not Applicable</i>
Vapor Pressure	<i>No Data Available</i>
Vapor Pressure	<i>Not Applicable</i>
Specific Gravity	0.840 [<i>Ref Std: WATER=1</i>]
pH	<i>No Data Available</i>
Melting point	>=100 °C [<i>Details: SPECIFIC METHOD: Drop Point</i>]
Solubility In Water	<=0.1 %
Solubility in Water	Negligible [<i>Details: < 0.1%</i>]
Evaporation rate	<i>No Data Available</i>
Volatile Organic Compounds	0.0 % [<i>Details: CONDITIONS: EPA Method 24</i>]
Percent volatile	Nil [<i>Details: CONDITIONS: @ 70F</i>]
VOC Less H2O & Exempt Solvents	<i>No Data Available</i>
Viscosity	<i>No Data Available</i>

SECTION 10: STABILITY AND REACTIVITY

Stability: Stable.

Materials and Conditions to Avoid: None known

Hazardous Polymerization: Hazardous polymerization will not occur.

Hazardous Decomposition or By-Products

<u>Substance</u>	<u>Condition</u>
Carbon monoxide	Not Specified
Carbon dioxide	Not Specified

SECTION 11: TOXICOLOGICAL INFORMATION

Please contact the address listed on the first page of the MSDS for Toxicological Information on this material and/or its

components.

SECTION 12: ECOLOGICAL INFORMATION

ECOTOXICOLOGICAL INFORMATION

Not determined.

CHEMICAL FATE INFORMATION

Not determined.

SECTION 13: DISPOSAL CONSIDERATIONS

Waste Disposal Method: Reclaim if feasible. If product can't be reclaimed, dispose of waste product in a sanitary landfill. Alternatively, incinerate the waste product in an industrial, commercial, or municipal incinerator. Dispose of waste product in a sanitary landfill. Incinerate in an industrial or commercial facility in the presence of a combustible material. As a disposal alternative, incinerate in an industrial or commercial facility in the presence of a combustible material.

Since regulations vary, consult applicable regulations or authorities before disposal.

SECTION 14: TRANSPORT INFORMATION

ID Number(s):

78-8135-2512-4, 80-6111-3272-3, 80-6111-3273-1, 80-6111-3274-9, 80-6111-3275-6, 80-6111-3276-4, 80-6111-3277-2, 80-6111-3278-0, 80-6111-3279-8, 80-6111-3280-6, 80-6111-3281-4, 80-6111-3282-2, 80-6111-3438-0, 80-6111-3439-8, 80-6111-3440-6, 80-6111-3441-4, 80-6111-3442-2, 80-6111-4892-7, 80-6111-4893-5, 80-6111-5056-8, 80-6111-5059-2, 80-6111-5060-0, 80-6111-5061-8, 80-6111-5062-6, 80-6111-5063-4, 80-6111-5065-9, 80-6111-5067-5, 80-6111-5069-1, 80-6111-5070-9, 80-6111-5071-7, 80-6111-5072-5, 80-6111-5162-4, 80-6111-5519-5, 80-6111-5520-3, 80-6113-1101-2, 80-6113-1162-4, 80-6113-1163-2, 80-6113-1164-0, 80-6113-1669-8, 80-6113-2153-2, 80-6113-2154-0, 80-6113-2155-7, 80-6113-2159-9, 80-6113-2354-6, 80-6113-2356-1, 80-6113-2357-9, 80-6113-2361-1, 80-6113-2362-9, 80-6113-2363-7, 80-6113-2495-7, 80-6113-2496-5, 80-6113-2497-3, 80-6113-2541-8

Please contact the emergency numbers listed on the first page of the MSDS for Transportation Information for this material.

SECTION 15: REGULATORY INFORMATION

US FEDERAL REGULATIONS

Contact 3M for more information.

311/312 Hazard Categories:

Fire Hazard - No Pressure Hazard - No Reactivity Hazard - No Immediate Hazard - Yes Delayed Hazard - No

STATE REGULATIONS

Contact 3M for more information.

CHEMICAL INVENTORIES

The components of this product are in compliance with the chemical notification requirements of TSCA.

Contact 3M for more information.

The components of this product are listed on the Australian Inventory of Chemical Substances.

All the components of this product are listed on China's Inventory of Chemical Substances.

The components of this product are in compliance with notification requirements in the Philippines.

INTERNATIONAL REGULATIONS

Contact 3M for more information.

This MSDS has been prepared to meet the U.S. OSHA Hazard Communication Standard, 29 CFR 1910.1200.

SECTION 16: OTHER INFORMATION

NFPA Hazard Classification

Health: 1 **Flammability:** 1 **Reactivity:** 0 **Special Hazards:** None

National Fire Protection Association (NFPA) hazard ratings are designed for use by emergency response personnel to address the hazards that are presented by short-term, acute exposure to a material under conditions of fire, spill, or similar emergencies. Hazard ratings are primarily based on the inherent physical and toxic properties of the material but also include the toxic properties of combustion or decomposition products that are known to be generated in significant quantities.

HMIS Hazard Classification

Health: 1 **Flammability:** 1 **Reactivity:** 0 **Protection:** A

Hazardous Material Identification System (HMIS(r)) hazard ratings are designed to inform employees of chemical hazards in the workplace. These ratings are based on the inherent properties of the material under expected conditions of normal use and are not intended for use in emergency situations. HMIS(r) ratings are to be used with a fully implemented HMIS(r) program. HMIS(r) is a registered mark of the National Paint and Coatings Association (NPCA).

Reason for Reissue: Add the following part number: 80-6113-2541-8. Mark status as Inactive for stock numbers: 80-6111-3272-3, 80-6111-3275-6, 80-6111-3279-8.

Revision Changes:

Section 16: Reason for reissue comment was modified.
Section 14: ID Number(s) was modified.

DISCLAIMER: The information in this Material Safety Data Sheet (MSDS) is believed to be correct as of the date issued. 3M MAKES NO WARRANTIES, EXPRESSED OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OR COURSE OF PERFORMANCE OR USAGE OF TRADE. User is responsible for determining whether the 3M product is fit for a particular purpose and suitable for user's method of use or application. Given the variety of factors that can affect the use and application of a 3M product, some of which are uniquely within the user's knowledge and control, it is essential that the user evaluate the 3M product to determine whether it is fit for a particular purpose and suitable for user's method of use or application.

3M provides information in electronic form as a service to its customers. Due to the remote possibility that electronic transfer may have resulted in errors, omissions or alterations in this information, 3M makes no representations as to its completeness or accuracy. In addition, information obtained from a database may not be as current as the information in the MSDS available directly from 3M.

3M MSDSs are available at www.3M.com