

# HAMLIN

www.hamlin.com

## 55110 L.E.D. Flange Mount Hall Effect Sensor Features and Benefits



### Features

- Magnetically operated position sensor
- Digital or latching types available
- Integral LED
- Medium or high sensitivities
- 3 wire (voltage output)
- Vibration 50g max. @ 50-2,000Hz
- Shock 150g max. @ 11ms 1/2 Sine
- EMC to DIN 40839 (Consult Hamlin)
- Reverse/Over Voltage Protection
- Built in temperature compensation


### Benefits

- High switching speed up to 10kHz
- Long life; up to 20 billion operations
- Visual indication of operation
- Unaffected by harsh environments
- Operates in static or dynamic magnetic field
- Customer selection of cable length and connector type


### Applications

- Position and limit sensing
- RPM measurement
- Flow metering
- Commutation of brushless dc motors
- Angle sensing
- Magnetic encoders

### DIMENSIONS (in) mm



### BLOCK DIAGRAMS



Note  
Add capacitor Cn as shown, close for the sensor, for transient suppression if required

### CUSTOMER OPTIONS - Switching Specifications


SPECIFICATIONS			Digital Switch or Digital Latch
Hall Type			3 Wire (Voltage output)
Supply Voltage (Note 1)	Absolute Ratings	Vdc	-15 to +28
	Operate	Vdc	+3.8 to +24
	Overvoltage Protection	Vdc-max	32
Output High Voltage		Vdc-min	Vdd-2 @ 0.1mA (sinking output with internal pull-up)
Output Low Voltage		Vdc-max	0.4 @ 10mA
Output Current (continuously on)		mA-max	10
Switching Speed		kHz-max	10
Temperature	Operating	°C	-40 to +100
	Storage	°C	-65 to +105

Note 1 - As long as Tj (Junction Temperature) max. is not exceeded

### CUSTOMER OPTIONS - Sensitivity, Cable Length and Termination Specification

TABLE 1 HALL OPTIONS ACTIVATE DISTANCES ARE APPROXIMATE USING NeFeB MAGNET (.827L x .276W x .185H) 21 x 7 x 4.7 HAMLIN P/N 5812334000				TABLE 2 Cable Length- (Cable type 24 AWG 7/32 PVC 105°C Double Insulated)		TABLE 3 Termination Options:-	
Select Hall Option	Hall Type	Sensitivity Gauss (Typ.)	Activate - d (in) mm	SELECT OPTION	LENGTH (in) mm	DESCRIPTION	
3M	3 Wire Switch	130	(.492) 12.5	01	(3.94) 100	Tinned leads	
3H	3 Wire Switch	59	(.709) 18.0	02	(11.81) 300	Crimped terminals	
3L	3 Wire Latch	86	(.394) 10.0	03	(19.69) 500	6.35mm fastons	
				04	(29.53) 750	AMP MTE 2.54mm pitch	
				05	(39.37) 1000	JST XHP 2.5mm pitch	

### ORDERING INFORMATION



Hamlin USA Tel: +1 920 648 3000 • Fax: +1 920 648 3001 • Email: sales.us@hamlin.com  
 Hamlin UK Tel: +44 (0)1379 649700 • Fax: +44 (0)1379 649702 • Email: sales.uk@hamlin.com  
 Hamlin Germany Tel: +49 (0) 6181 953660 • Fax: +49 (0) 6181 953666 • Email: sales.de@hamlin.com  
 Hamectrol France Tel: +33 (0) 1 4687 0202 • Fax: +33 (0) 1 4686 6786 • Email: sales.fr@hamlin.com  
 Issue No: 3 Date: 24/03/03 DCR B0063

DETAILS PROVIDED ON THIS DATA SHEET ARE PROVIDED FOR INFORMATION PURPOSES ONLY AND SHOULD NOT BE RELIED UPON AS BEING ACCURATE FOR ANY PARTICULAR PURPOSE. Product performance may be affected by the application to which the product is put. Upon request, HAMLIN will assist purchasers by providing information specific to any particular application. HAMLIN disclaims any and all liability whatsoever for any purchaser's reliance upon the information contained on this data sheet without further consultation with authorised representatives of HAMLIN.

