


CHAIN TERMINAL


SRT series <Made in Belgium>

LRT = Loose version of S (Strip) RT



Model No.	Standard	Applicable wire			Material	Finish	Dimensions mm(in.)					Q'ty / reel
		mm²	AWG #	Insulation O.D. mm(in.)			W	L	E	d (dia.)	Material thickness	
SRT-1.0T-M5S		0.5 to 1.0	20 to 18	2.0 to 3.3(.079 to .130)	Steel	Tin-plated	9.5 (.374)	21.75 (.856)	17.0 (.669)	5.3 (.209)	0.6 (.024)	4,000
SRT-2.5T-M5S		1.0 to 2.5	18 to 14	2.7 to 4.3(.106 to .169)								

SPC series (Splice) <Made in Belgium>



Model No.	Standard	Applicable wire		Material	Finish	Dimensions mm(in.)		Q'ty / reel
		mm²	AWG #			L	Material thickness	
SPC-1.0		0.5 to 1.0	20 to 18	Brass	—	6.0(.236)	0.25(.010)	30,000
SPC-1.0T					Tin-plated			
SPC-2.5		1.0 to 2.5	18 to 14		—	7.0(.276)		
SPC-2.5T					Tin-plated			

Note: The applicable wire size (total sectional area) above serves as a basic guideline. Before use, the performance of this connector must be tested with the wire that is to be used.

Applicator for the semi-automatic press AP-K2N

Contact	Crimp applicator MK-L/MK-L-PC	
	with safety cover	without safety cover
SRT-1.0T/N-M5S	APLMK SRT1.0-M5	APLNC SRT1.0-M5
SRT-2.5T/N-M5S	APLMK SRT2.5-M5	APLNC SRT2.5-M5
SPC-1.0(T)	APLMK SPC1.0	APLNC SPC1.0
SPC-2.5(T)	APLMK SPC2.5	APLNC SPC2.5