

# Crystal Clear & Crystal Blue



## DESCRIPTION

- High quality vinyl disposable glove.
- Length : 240 mm approximately.
- Thickness : 0,30 mm approximately.
- 2 available colours :
  - natural : Crystal Clear
  - blue : Crystal Blue
- 4 available sizes : 6<sup>1/2</sup>, 7<sup>1/2</sup>, 8<sup>1/2</sup> and 9<sup>1/2</sup>.

## CHARACTERISTICS

- 100% vinyl glove, ambidextrous.
- Slightly powdered for an easy donning.
- Available 100 gloves per dispenser box.
- Compliant with the European Regulations for Plastic Materials and Articles in contact with Food Regulations.



This glove is certified to comply with the essential requirements of European Directive EEC/89/686 of 21<sup>st</sup> december 1989 relative to personal protective equipment against minor hazards submitted to CE Type Examination issued by a control laboratory which certifies the conformity of this glove to the standard to which it responds.

## PERFORMANCES

- Lightweight, excellent dexterity and flexibility.
- Very good comfort in use.
- Smooth finish.
- Tear resistant beading.
- Certified in conformity with the EN 420 : 1994 standard (General requirements for protective gloves) by our control laboratory.

## APPLICATIONS

- For all types of applications requiring good dexterity.
- Crystal Blue is ideal for food environment use.
- Compliant for all types of food except fatty food.

## LIMITATIONS

- Do not use to handle chemicals or sharped objects.
- For minor risks only.

### References

	Size 6 <sup>1/2</sup>	Size 7 <sup>1/2</sup>	Size 8 <sup>1/2</sup>	Size 9 <sup>1/2</sup>
Crystal Clear	M05452	M05453	M05454	M05455
Crystal Blue	M05456	M05457	M05458	M05459

