



Sensors > Position Sensors > LVDT Sensors



Linearity Error (Full Range): $\pm.25\%$

Case Material: **Stainless Steel**

Product Shape: **Cylindrical**

Supply Voltage Range: **-15 – 15 V**

IP Rating: **IP61**

Features

Product Type Features

Product Shape	Cylindrical
---------------	-------------

Configuration Features

Electrical Connection	Shielded Cable
-----------------------	----------------

Electrical Characteristics

Supply Voltage Range	-15 – 15 V
----------------------	------------

Body Features

Case Material	Stainless Steel
Core Configuration	Separate Core

Dimensions

Product Diameter	19.05 mm[.75 in]
------------------	------------------

Operation/Application

Output Signal Type	$\pm 10\text{ V}$
--------------------	-------------------

Industry Standards

IP Rating	IP61
-----------	------

Other

Linearity Error (Full Range)	$\pm.25\%$
------------------------------	------------

Product Compliance




For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Not Yet Reviewed
EU ELV Directive 2000/53/EC	Not Yet Reviewed
China RoHS 2 Directive MIIT Order No 32, 2016	Not reviewed for China RoHS compliance
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Not Yet Reviewed
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE’s information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) ‘Guidance on requirements for substances in articles’(Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of ‘complex object’, the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA “Guidance on requirements for substances in articles” (June 2017, version 4.0) and will be updating its statements accordingly.

Also in the Series | MEAS DC



Customers Also Bought





TE Part #J05562074-000
CORE 1J50 .108OD .625LG M2X0.4



TE Part #66530072-000
R-FLEX CPLG ADP RVIT/RVDT/RSYN



TE Part #0460-010-20141
PIN, SOLID, SIZE 20, 16-18AWG, NI



TE Part #02291333-000
LDM-1000 LVDT CONDITIONER DIN



TE Part #02560408-000
LVDT MHR 050 ASSY



TE Part #CAT-RVDT0002
AC LIGHT WEIGHT RVDT



TE Part #202236-5
III+ PIN,SOLTAB,TIN,LP



TE Part #213485-1
CPC SEALING CAP ASSY SIZE 13



TE Part #5-1579007-0
TUBE

Documents

General purpose DC LVDT
English