

8442 Non-Paired - Audio Wire and Cable Cable

	<p>For more information please call 1-800-Belden1</p> <p><u>See Put-ups and Colors</u></p>
---	---

Description:

22 AWG stranded (7x30) tinned copper conductors, conductors cabled, PVC insulation, PVC jacket.

PHYSICAL CHARACTERISTICS:

CONDUCTOR:

Number of Conductors	2
Total Number of Conductors	2
AWG	22
Stranding	7x30
Conductor Material	TC - Tinned Copper

INSULATION:

Insulation Material	PVC - Polyvinyl Chloride
Nom. Insulation Wall Thickness	.015 in.

OVERALL CABLING:

Overall Cabling Lay Length	1.5 in.
Overall Cabling Color Code Chart :	

Number	Color
	Black & Red

OUTER SHIELD:

Outer Shield Material	Unshielded
-----------------------	------------

OUTER JACKET:

Outer Jacket Material	PVC - Polyvinyl Chloride
Outer Jacket Nominal Wall Thickness	.025 in.

OVERALL NOMINAL DIAMETER:

Overall Nominal Diameter	.170 in.
--------------------------	----------

MECHANICAL CHARACTERISTICS:

Operating Temperature Range	-20°C To +60°C
Bulk Cable Weight	13 lbs/1000 ft.
Max. Recommended Pulling Tension	18 lbs.
Min. Bend Radius (Install)	1.65 in.



8442 Non-Paired - Audio Wire and Cable Cable

APPLICABLE SPECIFICATIONS AND AGENCY COMPLIANCE:

APPLICABLE STANDARDS:

NEC/(UL) Specification	CMG
CEC/C(UL) Specification	CMG

FLAME TEST:

C(UL) Flame Test	FT4
------------------	-----

PLENUM/NON-PLENUM:

Plenum (Y/N)	N
Plenum Number	88442, 87442, 82442

ELECTRICAL CHARACTERISTICS:

Nom. Inductance	.2 µH/ft
Nom. Capacitance Conductor to Conductor @ 1 KHz	30 pF/ft
Nom. Conductor DC Resistance @ 20 Deg. C	15.6 Ohms/1000 ft
Max. Operating Voltage - UL	300 V RMS
Other Maximum Continuous Currents	2.9 Amps per conductor @ 25°C

PUT-UPS AND COLORS:

Item	Description	Put-Up (ft.)	Ship Weight (lbs.)	Jacket Color	Notes
8442 060100	2 #22 PVC PVC	100	2.4	CHROME	
8442 0601000	2 #22 PVC PVC	1000	15	CHROME	
8442 06010000	2 #22 PVC PVC	10000	150	CHROME	C Y
8442 060500	2 #22 PVC PVC	500	7.5	CHROME	
8442 060U1000	2 #22 PVC PVC	U1000	15	CHROME	
8442 060U500	2 #22 PVC PVC	U500	7.5	CHROME	

C = CRATE REEL PUT-UP.

Y = FINAL PUT-UP LENGTH MAY VARY -10% TO +20% FROM LENGTH SHOWN. MAY CONTAIN 2 PIECES. MINIMUM LENGTH OF ANY ONE PIECE IS 1500'.

Revision Number: 1 Revision Date: 10-07-2003



8442 Non-Paired - Audio Wire and Cable Cable

© 2003 Belden Wire & Cable Company
All Rights Reserved.

Although Belden Electronics Division ("Belden") makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.