

Amphenol

Amphenol-Tuchel Electronics GmbH

Circular Connector eco|mate^m Series



easier & quicker

|mate by Amphenol

Serie C16-1

A successful connector program now available in a new design with new technology.

3 + PE Screw termination

6 + PE Solder termination

6 + PE Crimp termination

New design



Improved technology




Male Cable Connector with Clamping Ring

Easier and quicker assembly

- New screw connection with clamping ring
- Strain relief and seal in a single element
- Ergonomically shaped handle for a better grip and safer handling
- Possibility of fastening the protective cover to the housing
- **Less logistics.** One type of housing for all cable sizes (6 to 12,5 mm)



Male Cable Connector right angled with Clamping Ring



Ø 6- 12,5 mm

The new product design is fully compatible and interchangeable with the existing C16-1 product design.

Serie C16-1




Male Cable Connector




Female Cable Connector

Male Cable Connector



Female Cable Connector



Description	No. of Cont.	Part Number	
		Cable retention with clamping ring	Cable retention with additional Cable clamp
Screw Termination	3 + PE	C016 20H003 100 10	C016 20H003 110 10
Solder Termination	6 + PE	C016 30H006 100 10	C016 30H006 110 10
Crimp Termination	6 + PE	C016 10H006 000 10	C016 10H006 010 10

Screw Termination	3 + PE	C016 20D003 100 10	C016 20D003 110 10
Solder Termination	6 + PE	C016 30D006 100 10	C016 30D006 110 10
Crimp Termination	6 + PE	C016 10D006 000 10	C016 10D006 010 10




Male Receptacle




Female Receptacle

Male Receptacle



Female Receptacle



Description	No. of Cont.	Part Number
Screw Termination	3 + PE	C016 20C003 100 12
Solder Termination	6 + PE	C016 30C006 100 12
Crimp Termination	6 + PE	C016 10C006 000 12

Screw Termination	3 + PE	C016 20G003 100 12
Solder Termination	6 + PE	C016 30G006 100 12
Crimp Termination	6 + PE	C016 10G006 000 12

Serie C16-1




Male Cable Connector, right-angled




Female Cable Connector, right-angled

Male Cable Connector, right-angled




Female Cable Connector, right-angled



Description	No. of Cont.	Part Number
Screw Termination	3 + PE	C016 20K003 100 10
Solder Termination	6 + PE	C016 30K006 100 10
Crimp Termination	6 + PE	C016 10K006 000 10



Screw Termination	3 + PE	C016 20F003 100 10
Solder Termination	6 + PE	C016 30F006 100 10
Crimp Termination	6 + PE	C016 10F006 000 10

Typ Number System




The example shown is representative of a 4 pole cable connector with screw terminals and without internal strain relief.

Serie C16-1

General Characteristics		Standard			Characteristics		
Number of contacts		3 + PE		6 + PE			
							
Electrical Characteristics		Screw		Solder	Crimp		
Rated insulation voltage	IEC 60664-1 ¹⁾	400 V		250 V	200 V		
Rated impulse withstand voltage	IEC 60664-1 ¹⁾	6000 V		4000 V			
Pollution degree	IEC 60664-1 ¹⁾	3		3			
Installation (overvoltage) category	IEC 60664-1 ¹⁾	III		III			
Material group	IEC 60664-1 ¹⁾	II		II			
Current carrying capacity	IEC 60512-5-2, Test 5b	16 A / + 55 °C		10 A / + 55 °C	13 A / + 55 °C		
Insulation resistance	IEC 60512-3-1	≥ 10 ⁸ Ω		≥ 10 ⁸ Ω			
Contact resistance	IEC 60512-2-1	≤ 5 m Ω		≤ 5 m Ω			
Climatical Characteristics							
Climatic category	DIN EN 60068-1	40 / 100 / 56			40 / 125 / 56		
Operating temperature		-40°C ... +100°C					
Mechanical Characteristics							
IP-degree of protection	DIN EN 60529	IP 65 / IP 67					
Insertion and withdrawal force	DIN EN 60512-13-2, Test 13b	≤ 15 N		≤ 30 N			
Mechanical operation	DIN EN 60512-9-1, Test 9a	≥ 500 Steckzyklen					
Materials							
Housing material		Polyamid 6.6					
Dielectric material		Polyamid 6.6					
Gasket material		Neoprene					
Contact plating		silver plated / gold plated					
Other Characteristics							
Termination technique		screw	solder	crimp			
Wire gauge mm ² / AWG		max. 2,5 mm ²	0,75 mm ²	0,14 - 1,5 mm ²			
Flammability	UL 94	VO					
Locking system		round thread DIN 405					
Fire protection	DIN 5510 Part 2 DIN 53438 Part 1-3	S1					

¹⁾ IEC 60664-1 ≙ VDE 0110-1 ≙ DIN EN 60664-1

 The stated technical values refer to the use as connector without breaking capacity (COC). If these components are used connectors with breaking capacity (CBC) a reduced current carrying capacity has to be considered.

General information

We reserve the right to change the design due to improvement in quality, development or production requirements. This catalogue must not be used in any form or manner without our prior approval in writing (Copyright Law, Fair Trading Law, Civil Code).

International

Argentina

Amphenol Argentina
Av. Callao 930
2nd Floor Office B "Plaza"
C1023 AAP Buenos Aires
Phone +54 / 11 / 4815 6886
Fax +54 / 11 / 4814 5779

Australia

Amphenol Australia Ltd.
2 Fiveways Blvd
Keysborough
Victoria 31 73
Phone +61 / 3 / 8796 / 8888
Fax +61 / 3 / 8796 / 8801

Belgium

Amphenol-Tuchel Belgium
Brusselbaan 524b
B 1600 Sint-Pieters-Leeuw
Phone +32 / 2377 / 25 49
Fax +32 / 2377 / 5303

Brasil

Amphenol do Brasil Ltda.
Rua Diogo Moreira 132, 20th Floor
CEP 05423-010 Sao Paulo SP
Phone +55 / 11 / 3815.1003
Fax +55 / 11 / 3815.1629

China

Amphenol-Tuchel Electronics GmbH
China Branch
210-1 Taishan Road
Changzhou 213022
Phone +86 / 0519 / 5110301
Fax +86 / 0519 / 5110299

Germany

Amphenol-Tuchel Electronics GmbH
August-Haeusser-Str. 10
74980 Heilbronn
Phone +49 / 71 31 / 929-0
Fax +49 / 71 31 / 929-486

Great Britain

Amphenol-Tuchel Great Britain
39 Rowlands Castle Road
Horndean
Waterlooville, Hants P08 0DF
Phone +44 / 23 92 / 57 17 91
Fax +44 / 23 92 / 57 17 91

Hong Kong

Amphenol East Asia Limited
Units 2201-02, Railway Plaza
39 Chatham Road South
Tsimshatsui, Kowloon
Phone +852 / 26 99 / 26 63
Fax +852 / 26 88 / 09 74

India

Amphetronix Limited
Plot No.105 Bhosari Industrial Area
Pune - 411 026
Phone +91 / 20 / 27121418
Fax +91 / 20 / 27120581

Italy

Amphenol Italia S.p.A.
Via Barbaiana n. 5
I-20020 Lainate (MI)
Phone +39 / 2 / 9325 41
Fax +39 / 2 / 9325 4444

Japan

Amphenol Japan, K.K.
2-3-27, Kudan Minami
Chiyoda-Ku
Tokyo 102
Phone +81 / 3 / 32 63 / 56 11
Fax +81 / 3 / 52 76 / 70 59

Korea

Amphenol DaeShin Limited
#802 Joong-Dong 1131-5
Wonmi-Ku
Bucheon-City
Kyunggi-Do
Korea 420-020
Phone +82 / 2 / 785 / 15 88
Fax +82 / 2 / 589 / 15 14

Mexico

Amphenol Mexico
Prolongacion Reforma 61 - 6 B2
Col. Paseo de las Lomas
C.P. 01330 Mexico D.F.
Phone +52 / 55 / 5258.9984
Fax +52 / 55 / 5081.6890

Sweden

Amphenol-Tuchel Scandinavia
Skogsvägen 42
SE 195 42 Märsta
Phone +46 / 85 91 / 1 75 76
Fax +46 / 85 91 / 1 75 76

Singapur

Amphenol East Asia Limited
Asia Pacific Sales Operation
Singapore Branch
300 Beach Road
#25-07 The Concourse
Singapore 199555
Phone +27 / 11 / 305-95 74
Fax +27 / 11 / 305-95 76

South Africa

Amphenol International Ltd
Chislehurst
30 Impala Road
Chislehurst
Sandton, 2146
Phone +27 / 11 / 7 83 95 17
Fax +27 / 11 / 7 83 95 19

Taiwan

Amphenol East Asia Ltd.
Taiwan Branch (H.K.)
116 Zhong Shan Road
Lane 956 Taoyuan City
Taiwan R.O.C. 330
Phone +886 / 3 / 370 / 78 55
Fax +886 / 3 / 360 72 59

Turkey

Amphenol Turkiye
Ayazaga Mah. Meydan Sk. No. 28
Beybi Giz Plaza, Kat. 26
34396 Maslak/Istanbul
Phone +90 / 0212 / 3 35 25 01
Fax +90 / 0212 / 3 35 25 00

USA

Amphenol-Tuchel Electronics
Representative Office
6900 Haggerty Road
Suite 200
Canton, Michigan 48187
Phone +1 / 734 / 451 6400
Fax +1 / 734 / 451 71 97

Amphenol Corporation

Corporate Headquarters
358 Hall Avenue
Wallingford, CT 06492
Phone +1 / 203 / 2 65 / 8900
Fax +1 / 203 / 2 65 / 86 28

Their responsible sales engineer:



Amphenol

Amphenol-Tuchel Electronics GmbH

August-Haeusser-Str. 10 · D-74080 Heilbronn · Germany · Phone. +49 (0)7131/929-0 · Fax +49 (0)7131/929-486 · www.amphenol.de