



SAFETY DATA SHEET 100 HMA BONDFLEX

1 IDENTIFICATION OF THE SUBSTANCE/PREPARATION AND OF THE COMPANY/UNDERTAKING

PRODUCT NAME 100 HMA BONDFLEX
 PRODUCT NO. 91360, 91361, 91362, 91363
 INTERNAL ID Formerly Codes - 91338, 91339, 91340, 91341
 SUPPLIER BOSTIK LIMITED
 COMMON ROAD
 STAFFORD
 STAFFORDSHIRE
 ST16 3EH
 +44 1785 255141
 +44 1785 272650 (24Hour
 Emergency)
 sds.uk@bostik.com

2 HAZARDS IDENTIFICATION

Not regarded as a health or environmental hazard under current legislation.

3 COMPOSITION/INFORMATION ON INGREDIENTS

Name	EC No.	CAS-No.	Content	Classification
METHYLTRIACTOXSILANE	224-221-9	4253-34-3	1-5%	C;R34. R14.
TRIACTOXYETHYLSILANE	241-677-4	17689-77-9	1-5%	C;R34. R14.

The Full Text for all R-Phrases are Displayed in Section 16

4 FIRST-AID MEASURES

GENERAL INFORMATION

General first aid, rest, warmth and fresh air.

INHALATION

Move the exposed person to fresh air at once. Get medical attention if any discomfort continues.

INGESTION

DO NOT induce vomiting. Get medical attention immediately.

SKIN CONTACT

Remove affected person from source of contamination. Rinse the skin immediately with lots of water. Get medical attention if irritation persists after washing.

EYE CONTACT

Rinse the eye with water immediately. Continue to rinse for at least 15 minutes and get medical attention.

5 FIRE-FIGHTING MEASURES

EXTINGUISHING MEDIA

This product is not flammable. Use fire-extinguishing media appropriate for surrounding materials.

SPECIFIC HAZARDS

Fire or high temperatures create: Toxic gases/vapours/fumes of Carbon dioxide (CO₂). Carbon monoxide (CO).

100 HMA BONDFLEX

PROTECTIVE MEASURES IN FIRE

Wear self contained breathing apparatus

6 ACCIDENTAL RELEASE MEASURES

SPILL CLEAN UP METHODS

Stop leak if possible without risk. Do not contaminate water sources or sewer. Pick up with vacuum or absorbent solid, store in closed container for disposal. Avoid generation and spreading of dust. Avoid contact with skin or inhalation of spillage, dust or vapour. Wear necessary protective equipment. Containers with collected spillage must be properly labelled with correct contents and hazard symbol.

7 HANDLING AND STORAGE

USAGE PRECAUTIONS

Avoid spilling, skin and eye contact. Do not handle broken packages without protective equipment. Use mechanical ventilation in case of handling which causes formation of dust.

STORAGE PRECAUTIONS

Store in tightly closed original container in a dry, cool and well-ventilated place. Keep in original container.

8 EXPOSURE CONTROLS/PERSONAL PROTECTION

INGREDIENT COMMENTS

WEL = Workplace Exposure Limits

PROTECTIVE EQUIPMENT



PROCESS CONDITIONS

Use engineering controls to reduce air contamination to permissible exposure level.

ENGINEERING MEASURES

All handling to take place in well-ventilated area.

RESPIRATORY EQUIPMENT

Wear respirator if there is dust formation.

HAND PROTECTION

Use suitable protective gloves if risk of skin contact. Use thin cotton gloves inside the rubber gloves if allergy risk.

EYE PROTECTION

If risk of splashing, wear safety goggles or face shield.

OTHER PROTECTION

Wear suitable protective clothing as protection against splashing or contamination.

HYGIENE MEASURES

Wash promptly if skin becomes wet or contaminated. Promptly remove any clothing that becomes contaminated. When using do not eat, drink or smoke. Wash at the end of each work shift and before eating, smoking and using the toilet. Use appropriate skin cream to prevent drying of skin. DO NOT SMOKE IN WORK AREA!

9 PHYSICAL AND CHEMICAL PROPERTIES

APPEARANCE	Paste
COLOUR	Misc. colours
RELATIVE DENSITY	1.02

10 STABILITY AND REACTIVITY

STABILITY

Stable under normal temperature conditions.

100 HMA BONDFLEX

CONDITIONS TO AVOID

Avoid excessive heat for prolonged periods of time.

HAZARDOUS POLYMERISATION

Unknown.

MATERIALS TO AVOID

No incompatible groups noted.

HAZARDOUS DECOMPOSITION PRODUCTS

Fire creates: Carbon monoxide (CO). Carbon dioxide (CO₂).

11 TOXICOLOGICAL INFORMATION

HEALTH WARNINGS

Dust may irritate respiratory system. Serious long-term effects are not known to be related to this type of product.

Particles in the eyes may cause irritation and smarting. May cause discomfort if swallowed.

12 ECOLOGICAL INFORMATION

ECOTOXICITY

Not regarded as dangerous for the environment. However, contamination of the aquatic or terrestrial environments should be avoided

13 DISPOSAL CONSIDERATIONS

DISPOSAL METHODS

Dispose of waste and residues in accordance with local authority requirements. Recover and reclaim or recycle, if practical.

14 TRANSPORT INFORMATION

GENERAL

The product is not covered by international regulation on the transport of dangerous goods (IMDG, IATA, ADR/RID).

No transport warning sign required.

MARINE POLLUTANT

No.

15 REGULATORY INFORMATION

RISK PHRASES

NC

Not classified.

SAFETY PHRASES

S36/37/39

Wear suitable protective clothing, gloves and eye/face protection.

P13

Safety data sheet available for professional user on request.

STATUTORY INSTRUMENTS

Chemicals (Hazard Information and Packaging) Regulations.

APPROVED CODE OF PRACTICE

Classification and Labelling of Substances and Preparations Dangerous for Supply.

GUIDANCE NOTES

Workplace Exposure Limits EH40. Introduction to Local Exhaust Ventilation HS(G)37. CHIP for everyone HSG(108).

16 OTHER INFORMATION

GENERAL INFORMATION

This product should be used as directed by Bostik Ltd. For further information consult the product data sheet or contact Technical Services.

INFORMATION SOURCES

This safety data sheet was compiled using current safety information supplied by distributor of raw materials.

REVISION DATE: january 2008

SDS NO.: 15696

100 HMA BONDFLEX

REVISION COMMENTS

This safety data sheet supersedes all previous issues and users are cautioned to ensure that it is current. Destroy all previous data sheets and if in doubt contact Bostik Limited.

ISSUED BY

Approved LJ

REVISION DATE january 2008

REV. NO./REPL. SDS GENERATED 2

DATE June 2006

RISK PHRASES IN FULL

R14 Reacts violently with water.

R34 Causes burns.