



**SAFETY DATA SHEET**  
**WHITE GLOSS PAINT R9010**

**1 IDENTIFICATION OF THE SUBSTANCE/PREPARATION AND OF THE COMPANY/UNDERTAKING**

**PRODUCT NAME** WHITE GLOSS PAINT R9010

**PRODUCT NO.** EPWB400

**APPLICATION** Paint

**SUPPLIER** ELECTROLUBE. A division of  
HK WENTWORTH LTD  
KINGSBURY PARK, MIDLAND  
ROAD  
SWADLINCOTE  
DERBYSHIRE, DE11 0AN  
UNITED KINGDOM  
+44(0)1283 222 111  
+44(0)1283 550 177  
info@hkw.co.uk

**EMERGENCY TELEPHONE** +44(0)1283 222 111 between 8.30 am - 5.00pm Mon - Fri

**2 HAZARDS IDENTIFICATION**

Extremely flammable.

Repeated exposure may cause skin dryness or cracking.

Vapours may cause drowsiness and dizziness.

Irritating to eyes.

Harmful to aquatic organisms, may cause long-term adverse effects in the aquatic environment.

**CLASSIFICATION** Xi;R36. F+;R12. R52/53, R66, R67.

**3 COMPOSITION/INFORMATION ON INGREDIENTS**

Name	EC No.	CAS-No.	Content	Classification
ACETONE	200-662-2	67-64-1	30-60%	F;R11 Xi;R36 R66 R67
PROPANE	200-827-9	74-98-6	10-30%	F+;R12
WHITE SPIRIT	265-151-9	64742-49-0	10-30%	Xn;R65. Xi;R38. N;R51/53.
BUTANE	203-448-7	106-97-8	5-10%	F+;R12
ISOBUTANE	200-857-2	75-28-5	1-5%	F+;R12
XYLENE	215-535-7	1330-20-7	1-5%	R10 Xn;R20/21 Xi;R38

The Full Text for all R-Phrases are Displayed in Section 16

**COMPOSITION COMMENTS**

Ingredients not listed are classified as non-hazardous or at a concentration below reportable levels

**4 FIRST-AID MEASURES**

**NOTES TO THE PHYSICIAN**

Treat symptomatically

**INHALATION**

Move the exposed person to fresh air at once. Keep the affected person warm and at rest. Get prompt medical attention.

Get medical attention.

**INGESTION**

Immediately rinse mouth and provide fresh air.

## WHITE GLOSS PAINT R9010

### SKIN CONTACT

Wash the skin immediately with soap and water. Get medical attention if any discomfort continues.

### EYE CONTACT

Make sure to remove any contact lenses from the eyes before rinsing. Promptly wash eyes with plenty of water while lifting the eye lids. Continue to rinse for at least 15 minutes. Get medical attention if any discomfort continues.

## 5 FIRE-FIGHTING MEASURES

### EXTINGUISHING MEDIA

Use: Powder. Dry chemicals, sand, dolomite etc. Water spray, fog or mist.

### SPECIAL FIRE FIGHTING PROCEDURES

Move container from fire area if it can be done without risk.

### UNUSUAL FIRE & EXPLOSION HAZARDS

Aerosol cans may explode in a fire.

## 6 ACCIDENTAL RELEASE MEASURES

### SPILL CLEAN UP METHODS

Absorb in vermiculite, dry sand or earth and place into containers. Ventilate well.

## 7 HANDLING AND STORAGE

### USAGE PRECAUTIONS

Avoid spilling, skin and eye contact. Provide good ventilation.

### STORAGE PRECAUTIONS

Store at moderate temperatures in dry, well ventilated area.

## 8 EXPOSURE CONTROLS/PERSONAL PROTECTION

Name	Std	TWA - 8 hrs		STEL - 15 min		Notes
ACETONE	WEL	500 ppm	1210 mg/m3	1500 ppm	3620 mg/m3	
BUTANE	WEL	600 ppm	1450 mg/m3	750 ppm	1810 mg/m3	
XYLENE	WEL	50 ppm(Sk)	220 mg/m3(Sk)	100 ppm(Sk)	441 mg/m3(Sk)	

WEL = Workplace Exposure Limit.

### OTHER PROTECTION

Wear appropriate clothing to prevent any possibility of liquid contact and repeated or prolonged vapour contact.

### HYGIENE MEASURES

Wash at the end of each work shift and before eating, smoking and using the toilet. Use appropriate skin cream to prevent drying of skin. When using do not eat, drink or smoke. DO NOT SMOKE IN WORK AREA!

## 9 PHYSICAL AND CHEMICAL PROPERTIES

APPEARANCE	Aerosol Liquid		
COLOUR	White		
ODOUR	Acetone, ketone.		
SOLUBILITY	Immiscible with water		
RELATIVE DENSITY	>.750 @ 20 °c	BULK DENSITY	750 kg/m3
VAPOUR PRESSURE	354 kPa @ 19 °c	FLASH POINT (°C)	<0 CC (Closed cup).
AUTO IGNITION TEMPERATURE (°C)	309	FLAMMABILITY LIMIT - LOWER(%)	0.6
FLAMMABILITY LIMIT - UPPER(%)	13		

## 10 STABILITY AND REACTIVITY

### STABILITY

Stable under normal temperature conditions.

## WHITE GLOSS PAINT R9010

### CONDITIONS TO AVOID

Avoid heat, flames and other sources of ignition. Avoid contact with acids and alkalies.

## 11 TOXICOLOGICAL INFORMATION

### INHALATION

May cause irritation to the respiratory system. Vapours may cause headache, fatigue, dizziness and nausea. High concentrations of vapours may irritate respiratory system and lead to headache, fatigue, nausea and vomiting.

### SKIN CONTACT

Product has a defatting effect on skin. Prolonged contact may cause dryness of the skin. Prolonged or repeated exposure may cause severe irritation.

### EYE CONTACT

Irritating to eyes.

### Other Health Effects

This substance has no evidence of carcinogenic properties.

### ROUTE OF ENTRY

Inhalation.

<b>Name</b>	XYLENE
<b>Toxic Dose 1 - LD 50</b>	4300 mg/kg (oral rat)
<b>Name</b>	ACETONE
<b>Toxic Dose 1 - LD 50</b>	5800 mg/kg (oral rat)
<b>Toxic Dose 2 - LD 50</b>	20,000 mg/kg (oral-rbt)
<b>Toxic Conc. - LC 50</b>	76 ppm/4h (inh-rat)
<b>Name</b>	WHITE SPIRIT
<b>Toxic Dose 1 - LD 50</b>	>5000 mg/kg (oral rat)

## 12 ECOLOGICAL INFORMATION

### ECOTOXICITY

Dangerous for the environment if discharged into watercourses.

<b>Name</b>	XYLENE
<b>LC 50, 96 Hrs, FISH mg/l</b>	2.6-8.4
<b>EC 50, 48 Hrs, DAPHNIA, mg/l</b>	1.0-4.7
<b>Name</b>	ACETONE
<b>LC 50, 96 Hrs, FISH mg/l</b>	8300
<b>EC 50, 48 Hrs, DAPHNIA, mg/l</b>	12600
<b>Degradability</b>	
The product is easily biodegradable.	
<b>Name</b>	WHITE SPIRIT

## 13 DISPOSAL CONSIDERATIONS

### DISPOSAL METHODS

Empty containers must not be burned because of explosion hazard. Dispose of waste and residues in accordance with local authority requirements.

## 14 TRANSPORT INFORMATION



<b>UK ROAD CLASS</b>	2		
<b>PROPER SHIPPING NAME</b>	AEROSOLS		
<b>UN NO. ROAD</b>	1950	<b>UK ROAD PACK GR.</b>	N/A
<b>ADR CLASS NO.</b>	2	<b>ADR CLASS</b>	Class 2: Gases

**WHITE GLOSS PAINT R9010**

<b>ADR PACK GROUP</b>	N/A	<b>ADR LABEL NO.</b>	2.1
<b>CEFIC TEC(R) NO.</b>	20G5F	<b>RID CLASS NO.</b>	2
<b>RID PACK GROUP</b>	N/A	<b>UN NO. SEA</b>	1950
<b>IMDG CLASS</b>	2.1	<b>IMDG PACK GR.</b>	N/A
<b>EMS</b>	F-D, S-U	<b>MFAG</b>	See Guide
<b>MARINE POLLUTANT</b>	No.	<b>UN NO. AIR</b>	1950
<b>AIR CLASS</b>	2.1	<b>AIR PACK GR.</b>	N/A

**15 REGULATORY INFORMATION****SYMBOLS**

Irritant



Extremely Flammable

**RISK PHRASES**

R12	Extremely flammable.
R36	Irritating to eyes.
R52/53	Harmful to aquatic organisms, may cause long-term adverse effects in the aquatic environment.
R66	Repeated exposure may cause skin dryness or cracking.
R67	Vapours may cause drowsiness and dizziness.

**SAFETY PHRASES**

A1	Pressurised container: protect from sunlight and do not expose to temperatures exceeding 50°C. Do not pierce or burn, even after use.
A2	Do not spray on a naked flame or any incandescent material.
S2	Keep out of the reach of children
S16	Keep away from sources of ignition - No smoking.
S23	Do not breathe vapour/spray.
S25	Avoid contact with eyes.
S38	In case of insufficient ventilation, wear suitable respiratory equipment.

**UK REGULATORY REFERENCES**

Chemicals (Hazard Information & Packaging) Regulations.

The Control of Substances Hazardous to Health Regulations 1988.

**ENVIRONMENTAL LISTING**

Rivers (Prevention of Pollution) Act 1961. Control of Pollution Act 1974.

**EU DIRECTIVES**

System of specific information relating to Dangerous Preparations. 2001/58/EC.

Dangerous Substance Directive 67/548/EEC.

Dangerous Preparations Directive 1999/45/EC.

Commission Directive 2000/39/EC of 8 June 2000 establishing a first list of indicative occupational exposure limit values in implementation of Council Directive 98/24/EC on the protection of the health and safety of workers from the risks related to chemical agents at work.

Regulation (EC) No 1907/2006 of the European Parliament and of the Council of 18 December 2006 concerning the Registration, Evaluation, Authorisation and Restriction of Chemicals (REACH), establishing a European Chemicals Agency, amending Directive 1999/45/EC and repealing Council Regulation (EEC) No 793/93 and Commission Regulation (EC) No 1488/94 as well as Council Directive 76/769/EEC and Commission Directives 91/155/EEC, 93/67/EEC, 93/105/EC and 2000/21/EC, including amendments.

**STATUTORY INSTRUMENTS**

Control of Substances Hazardous to Health.

## WHITE GLOSS PAINT R9010

### APPROVED CODE OF PRACTICE

Classification and Labelling of Substances and Preparations Dangerous for Supply. Safety Data Sheets for Substances and Preparations.

### GUIDANCE NOTES

Workplace Exposure Limits EH40.

## 16 OTHER INFORMATION

### REVISION COMMENTS

Revised in accordance with CHIP3 and EU Directives 1999/45/EC and 2001/58/EC

### ISSUED BY

Helen O'Reilly

**REVISION DATE** NOVEMBER 2008

**REV. NO./REPL. SDS** 3

### GENERATED

**SDS NO.** 11024

### RISK PHRASES IN FULL

R10	Flammable.
R11	Highly flammable.
R12	Extremely flammable.
R20/21	Harmful by inhalation and in contact with skin.
R36	Irritating to eyes.
R38	Irritating to skin.
R51/53	Toxic to aquatic organisms, may cause long-term adverse effects in the aquatic environment.
R65	Harmful: may cause lung damage if swallowed.
R66	Repeated exposure may cause skin dryness or cracking.
R67	Vapours may cause drowsiness and dizziness.

### DISCLAIMER

This information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process. Such information is, to the best of the company's knowledge and belief, accurate and reliable as of the date indicated. However, no warranty guarantee or representation is made to its accuracy, reliability or completeness. It is the user's responsibility to satisfy himself as to the suitability of such information for his own particular use.