

BF421, BF423

High Voltage Transistors

PNP Silicon

Features

- Pb-Free Packages are Available*

MAXIMUM RATINGS

Rating	Symbol	BF421	BF423	Unit
Collector–Emitter Voltage	V_{CEO}	-300	-250	Vdc
Collector–Base Voltage	V_{CBO}	-300	-250	Vdc
Emitter–Base Voltage	V_{EBO}	-5.0		Vdc
Collector Current – Continuous	I_C	-50		mAdc
Collector Current – Peak	I_{CM}	100		mA
Total Device Dissipation (Note 1) @ $T_A = 25^\circ\text{C}$ Derate above 25°C	P_D	830	6.6	mW mW/°C
Operating and Storage Junction Temperature Range	T_J, T_{stg}	-55 to +150		°C

THERMAL CHARACTERISTICS

Characteristic	Symbol	Max	Unit
Thermal Resistance, Junction–to–Ambient	$R_{\theta JA}$	150	°C/W
Thermal Resistance, Junction–to–Lead	$R_{\theta JL}$	68	°C/W


Maximum ratings are those values beyond which device damage can occur. Maximum ratings applied to the device are individual stress limit values (not normal operating conditions) and are not valid simultaneously. If these limits are exceeded, device functional operation is not implied, damage may occur and reliability may be affected.

- Mounted on a FR4 board with 200 mm² of 1 oz copper and lead length of 5 mm.




ON Semiconductor®


<http://onsemi.com>



MARKING DIAGRAM



TO-92
CASE 29
STYLE 14



BF42x = Device Code
x = 1 or 3

A = Assembly Location

Y = Year

WW = Work Week

▪ = Pb-Free Package

(Note: Microdot may be in either location)

ORDERING INFORMATION

Device	Package	Shipping
BF421ZL1	TO-92	2000/Ammo Pack
BF421ZL1G	TO-92 (Pb-Free)	2000/Ammo Pack
BF423	TO-92	5000 Units/Box
BF423G	TO-92 (Pb-Free)	5000 Units/Box
BF423ZL1	TO-92	2000/Ammo Pack
BF423ZL1G	TO-92 (Pb-Free)	2000/Ammo Pack

*For additional information on our Pb-Free strategy and soldering details, please download the ON Semiconductor Soldering and Mounting Techniques Reference Manual, SOLDERRM/D.

BF421, BF423

ELECTRICAL CHARACTERISTICS (T_A = 25°C unless otherwise noted)

Characteristic		Symbol	Min	Max	Unit
OFF CHARACTERISTICS					
Collector–Emitter Breakdown Voltage (Note 1) (I _C = -1.0 mA, I _B = 0)	BF421 BF423	V _{(BR)CEO}	-300 -250	- -	Vdc
Collector–Base Breakdown Voltage (I _C = -100 μA, I _E = 0)	BF421 BF423	V _{(BR)CBO}	-300 -250	- -	Vdc
Emitter–Base Breakdown Voltage (I _E = -100 μA, I _C = 0)	BF421 BF423	V _{(BR)EBO}	-5.0 -5.0	- -	Vdc
Collector Cutoff Current (V _{CB} = -200 Vdc, I _E = 0)	BF421 BF423	I _{CBO}	- -	-0.01 -	μA _{dc}
Emitter Cutoff Current (V _{EB} = -5.0 Vdc, I _C = 0)	BF421 BF423	I _{EBO}	- -	-100 -	nA _{dc}
ON CHARACTERISTICS					
DC Current Gain (I _C = -25 mA, V _{CE} = -20 Vdc)	BF421 BF423	h _{FE}	50 50	- -	-
Collector–Emitter Saturation Voltage (I _C = -20 mA, I _B = -2.0 mA)		V _{CE(sat)}	-	-0.5	Vdc
Base–Emitter Saturation Voltage (I _C = -20 mA, I _B = -2.0 mA)		V _{BE(sat)}	-	-2.0	Vdc
SMALL–SIGNAL CHARACTERISTICS					
Current–Gain – Bandwidth Product (I _C = -10 mA, V _{CE} = -10 Vdc, f = 20 MHz)		f _T	60	-	MHz
Common Emitter Feedback Capacitance (V _{CB} = -30 Vdc, I _E = 0, f = 1.0 MHz)		C _{re}	-	2.8	pF

1. Pulse Test: Pulse Width ≤ 300 μs; Duty Cycle ≤ 2.0%.

BF421, BF423




Figure 1. DC Current Gain




Figure 2. Capacitance




Figure 3. Current-Gain - Bandwidth






Figure 4. "ON" Voltages

BF421, BF423

PACKAGE DIMENSIONS

TO-92
(TO-226)
CASE 029-11
ISSUE AL



NOTES:

1. DIMENSIONING AND TOLERANCING PER ANSI Y14.5M, 1982.
2. CONTROLLING DIMENSION: INCH.
3. CONTOUR OF PACKAGE BEYOND DIMENSION R IS UNCONTROLLED.
4. LEAD DIMENSION IS UNCONTROLLED IN P AND BEYOND DIMENSION K MINIMUM.

DIM	INCHES		MILLIMETERS	
	MIN	MAX	MIN	MAX
A	0.175	0.205	4.45	5.20
B	0.170	0.210	4.32	5.33
C	0.125	0.165	3.18	4.19
D	0.016	0.021	0.407	0.533
G	0.045	0.055	1.15	1.39
H	0.095	0.105	2.42	2.66
J	0.015	0.020	0.39	0.50
K	0.500	---	12.70	---
L	0.250	---	6.35	---
N	0.080	0.105	2.04	2.66
P	---	0.100	---	2.54
R	0.115	---	2.93	---
V	0.135	---	3.43	---

STYLE 14:

1. EMITTER
2. COLLECTOR
3. BASE

ON Semiconductor and are registered trademarks of Semiconductor Components Industries, LLC (SCILLC). SCILLC reserves the right to make changes without further notice to any products herein. SCILLC makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does SCILLC assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. "Typical" parameters which may be provided in SCILLC data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. SCILLC does not convey any license under its patent rights nor the rights of others. SCILLC products are not designed, intended, or authorized for use as components in systems intended for surgical implant into the body, or other applications intended to support or sustain life, or for any other application in which the failure of the SCILLC product could create a situation where personal injury or death may occur. Should Buyer purchase or use SCILLC products for any such unintended or unauthorized application, Buyer shall indemnify and hold SCILLC and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that SCILLC was negligent regarding the design or manufacture of the part. SCILLC is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

PUBLICATION ORDERING INFORMATION

LITERATURE FULFILLMENT:
Literature Distribution Center for ON Semiconductor
P.O. Box 61312, Phoenix, Arizona 85082-1312 USA
Phone: 480-829-7710 or 800-344-3860 Toll Free USA/Canada
Fax: 480-829-7709 or 800-344-3867 Toll Free USA/Canada
Email: orderlit@onsemi.com

N. American Technical Support: 800-282-9855 Toll Free USA/Canada

Japan: ON Semiconductor, Japan Customer Focus Center
2-9-1 Kamimeguro, Meguro-ku, Tokyo, Japan 153-0051
Phone: 81-3-5773-3850

ON Semiconductor Website: <http://onsemi.com>

Order Literature: <http://www.onsemi.com/litorder>

For additional information, please contact your local Sales Representative.