



SAFETY DATA SHEET
THERMALLY CONDUCTIVE OXIME RTV

1 IDENTIFICATION OF THE SUBSTANCE/PREPARATION AND OF THE COMPANY/UNDERTAKING

PRODUCT NAME THERMALLY CONDUCTIVE OXIME RTV
PRODUCT NO. ETCOR75S
APPLICATION Manufacture of electrical equipment
SUPPLIER ELECTROLUBE. A division of
 HK WENTWORTH LTD
 KINGSBURY PARK, MIDLAND
 ROAD
 SWADLINCOTE
 DERBYSHIRE, DE11 0AN
 UNITED KINGDOM
 +44(0)1283 222 111
 +44(0)1283 550 177
 info@hkw.co.uk
EMERGENCY TELEPHONE +44(0)1283 222 111 between 8.30 am - 5.00pm Mon - Fri

2 HAZARDS IDENTIFICATION

May cause sensitisation by skin contact.

Toxic to aquatic organisms, may cause long-term adverse effects in the aquatic environment.

CLASSIFICATION R43. N;R51/53.

3 COMPOSITION/INFORMATION ON INGREDIENTS

Name	EC No.	CAS-No.	Content	Classification
Aluminium Oxide	215-691-6	1344-28-1	30-60%	-
ZINC OXIDE	215-222-5	1314-13-2	10-30%	N;R50/53
METHYLTRIS(2-BUTANONEOXIME) SILANE		22984-54-9	1-5%	Xi;R37/38,R41. R43.

The Full Text for all R-Phrases are Displayed in Section 16

COMPOSITION COMMENTS

Ingredients not listed are classified as non-hazardous or at a concentration below reportable levels

4 FIRST-AID MEASURES

INHALATION

Move the exposed person to fresh air at once. Keep the affected person warm and at rest. Get prompt medical attention.

INGESTION

DO NOT INDUCE VOMITING! Rinse mouth thoroughly. Get medical attention.

SKIN CONTACT

Promptly wash contaminated skin with soap or mild detergent and water. Promptly remove clothing if soaked through and wash as above. Get medical attention if irritation persists after washing.

EYE CONTACT

Make sure to remove any contact lenses from the eyes before rinsing. Promptly wash eyes with plenty of water while lifting the eye lids. Continue to rinse for at least 15 minutes. Get medical attention if any discomfort continues.

5 FIRE-FIGHTING MEASURES

EXTINGUISHING MEDIA

This product is not flammable. Use fire-extinguishing media appropriate for surrounding materials.

THERMALLY CONDUCTIVE OXIME RTV

6 ACCIDENTAL RELEASE MEASURES

SPILL CLEAN UP METHODS

Absorb in vermiculite, dry sand or earth and place into containers. Flush with plenty of water to clean spillage area.

7 HANDLING AND STORAGE

USAGE PRECAUTIONS

Avoid spilling, skin and eye contact.

STORAGE PRECAUTIONS

Store in tightly closed original container in a dry, cool and well-ventilated place. Keep in original container.

8 EXPOSURE CONTROLS/PERSONAL PROTECTION

Name	Std	TWA - 8 hrs		STEL - 15 min		Notes
Aluminium Oxide			10 mg/m3			

INGREDIENT COMMENTS

WEL = Workplace Exposure Limits

PROTECTIVE EQUIPMENT



ENGINEERING MEASURES

Provide sufficient ventilation during operations which cause vapour formation.

RESPIRATORY EQUIPMENT

No specific recommendation made, but respiratory protection must be used if the general level exceeds the Recommended Workplace Exposure Limit.

HAND PROTECTION

Use suitable protective gloves if risk of skin contact. The most suitable glove must be chosen in consultation with the gloves supplier, who can inform about the breakthrough time of the glove material.

EYE PROTECTION

Wear approved chemical safety goggles where eye exposure is reasonably probable.

OTHER PROTECTION

Wear appropriate clothing to prevent any possibility of liquid contact and repeated or prolonged vapour contact.

HYGIENE MEASURES

DO NOT SMOKE IN WORK AREA! Wash at the end of each work shift and before eating, smoking and using the toilet. Wash promptly with soap & water if skin becomes contaminated. When using do not eat, drink or smoke.

9 PHYSICAL AND CHEMICAL PROPERTIES

APPEARANCE	Paste
COLOUR	White
ODOUR	No characteristic odour.
SOLUBILITY	Insoluble in water
RELATIVE DENSITY	2.3 @ 20 °c

10 STABILITY AND REACTIVITY

STABILITY

Stable under normal temperature conditions.

CONDITIONS TO AVOID

Not known.

THERMALLY CONDUCTIVE OXIME RTV

11 TOXICOLOGICAL INFORMATION

INGESTION

May cause stomach pain or vomiting.

HEALTH WARNINGS

No specific health warnings noted.

No specific acute or chronic health impact noted, but this chemical may still have adverse impact on human health, either in general or on certain individuals with pre-existing or latent health problems.

Other Health Effects

This substance has no evidence of carcinogenic properties.

12 ECOLOGICAL INFORMATION

ECOTOXICITY

Dangerous for the environment if discharged into watercourses.

13 DISPOSAL CONSIDERATIONS

DISPOSAL METHODS

Dispose of waste and residues in accordance with local authority requirements.

14 TRANSPORT INFORMATION



UK ROAD CLASS	9		
PROPER SHIPPING NAME	ENVIRONMENTALLY HAZARDOUS SUBSTANCE, LIQUID, N.O.S. (ZINC OXIDE, DIBUTYLTIN DILAURATE)		
UN NO. ROAD	3082	UK ROAD PACK GR.	III
ADR CLASS NO.	9	ADR CLASS	Class 9: Miscellaneous dangerous substances and articles.
ADR PACK GROUP	III	HAZARD No. (ADR)	90
ADR LABEL NO.	9	HAZCHEM CODE	3Z
CEFIC TEC(R) NO.	90GM6-III	RID CLASS NO.	9
RID PACK GROUP	III	UN NO. SEA	3082
IMDG CLASS	9	IMDG PACK GR.	III
EMS	F-A, S-F	MARINE POLLUTANT	No.
UN NO. AIR	3082	AIR CLASS	9
AIR PACK GR.	III		

15 REGULATORY INFORMATION

SYMBOLS



Irritant



Dangerous for the environment

CONTAINS

METHYLTRIS(2-BUTANONEOXIME) SILANE

RISK PHRASES

R43 May cause sensitisation by skin contact.

THERMALLY CONDUCTIVE OXIME RTV

R51/53 Toxic to aquatic organisms, may cause long-term adverse effects in the aquatic environment.

SAFETY PHRASES

S24 Avoid contact with skin.
S37 Wear suitable gloves.
S57 Use appropriate containment to avoid environmental contamination.
S61 Avoid release to the environment. Refer to special instructions/safety data sheets.

UK REGULATORY REFERENCES

Chemicals (Hazard Information & Packaging) Regulations.

The Control of Substances Hazardous to Health Regulations 1988.

ENVIRONMENTAL LISTING

Rivers (Prevention of Pollution) Act 1961. Control of Pollution (Special Waste Regulations) Act 1980. Control of Pollution Act 1974.

EU DIRECTIVES

System of specific information relating to Dangerous Preparations. 2001/58/EC.

Dangerous Substance Directive 67/548/EEC.

Dangerous Preparations Directive 1999/45/EC.

Commission Directive 2000/39/EC of 8 June 2000 establishing a first list of indicative occupational exposure limit values in implementation of Council Directive 98/24/EC on the protection of the health and safety of workers from the risks related to chemical agents at work.

Regulation (EC) No 1907/2006 of the European Parliament and of the Council of 18 December 2006 concerning the Registration, Evaluation, Authorisation and Restriction of Chemicals (REACH), establishing a European Chemicals Agency, amending Directive 1999/45/EC and repealing Council Regulation (EEC) No 793/93 and Commission Regulation (EC) No 1488/94 as well as Council Directive 76/769/EEC and Commission Directives 91/155/EEC, 93/67/EEC, 93/105/EC and 2000/21/EC, including amendments.

APPROVED CODE OF PRACTICE

Classification and Labelling of Substances and Preparations Dangerous for Supply. Safety Data Sheets for Substances and Preparations.

GUIDANCE NOTES

Workplace Exposure Limits EH40.

16 OTHER INFORMATION**REVISION COMMENTS**

Revised in accordance with CHIP3 and EU Directives 1999/45/EC and 2001/58/EC

ISSUED BY

Helen O'Reilly

REVISION DATE

JULY 2008

REV. NO./REPL. SDS

0

GENERATED**RISK PHRASES IN FULL**

R37/38 Irritating to respiratory system and skin.
R41 Risk of serious damage to eyes.
R43 May cause sensitisation by skin contact.
R50/53 Very toxic to aquatic organisms, may cause long-term adverse effects in the aquatic environment.

DISCLAIMER

This information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process. Such information is, to the best of the company's knowledge and belief, accurate and reliable as of the date indicated. However, no warranty guarantee or representation is made to its accuracy, reliability or completeness. It is the user's responsibility to satisfy himself as to the suitability of such information for his own particular use.