

# GP Batteries

## PRODUCT SPECIFICATION

**GP PowerBank S350**  
**Model: GPPB350 (200mA)**

### Revision History

Revision	Date	Initiator	Reason for Change
00	27 Feb 2009	Con Chan	New release

Prepared By	Approved By
Con Chan	Natalie Chow
Date: 27 Feb 09	Date: 27 Feb 09



### **GPI International Limited**

Gold Peak Building, 8/F, 30 Kwai Wing Road,  
Kwai Chung, New Territories, Hong Kong.  
Tel: (852) 2484 3333 Fax: (852) 24805912  
Email: [gpii@goldpeak.com](mailto:gpii@goldpeak.com)  
Website: <http://www.gpbatteries.com>

# GP Batteries

## Product Specification

Model No.: GPPB350



NOTE : It is safe to charge GP NiMH batteries continuously with GP PowerBank S350.

Unit : mm

Product Name	:	GP PowerBank S350													
Description	:	Continuous NiMH Battery Charger (Plug-In Type)													
Input Voltage	:	230V AC 50Hz (GS/BS); 120V AC 60Hz (UL)													
Input Power	:	6W max.													
Application	:	For charging 2 or 4 pcs NiMH batteries; 2 batteries per one channel (DO NOT mix AA and AAA size batteries in the same channel.)													
Output Voltage	:	2.8V DC													
Charging Current	:	AA 200mA ± 10% AAA 100mA ± 10%													
Charging Time	:	<table border="1"> <thead> <tr> <th>GP NiMH</th> <th>Size</th> <th>Capacity (mAh / series)</th> <th>Charging Time (hours)</th> </tr> </thead> <tbody> <tr> <td rowspan="3">GP NiMH</td> <td rowspan="2">AA</td> <td>2100 ~ 2700</td> <td>12 ~ 15.5</td> </tr> <tr> <td>1300 ~ 1800</td> <td>8 ~ 11</td> </tr> <tr> <td>AAA</td> <td>600 ~ 1000</td> <td>7 ~ 11.5</td> </tr> </tbody> </table>	GP NiMH	Size	Capacity (mAh / series)	Charging Time (hours)	GP NiMH	AA	2100 ~ 2700	12 ~ 15.5	1300 ~ 1800	8 ~ 11	AAA	600 ~ 1000	7 ~ 11.5
GP NiMH	Size	Capacity (mAh / series)	Charging Time (hours)												
GP NiMH	AA	2100 ~ 2700	12 ~ 15.5												
		1300 ~ 1800	8 ~ 11												
	AAA	600 ~ 1000	7 ~ 11.5												
MTBF	:	30000 hours (at ambient temperature 25°C)													
Operating Temperature	:	0°C to 45°C													
Storage Temperature	:	-25°C to 60°C													
Charge Indicator	:	2 red LED for two channels, left LED for front channel and right LED for back channel													
Dimensions	:	105(L) X 44(W) X 46(T)mm													
Approval	:	GS, CE, CQC, FCC, C-UL													
Warranty Period	:	12 months from ex-factory date													