


**RoHS
Compliant**



Specifications

Waterproof Rate	: IP68
Recommend Cable Diameter	: 3.5mm to 4mm
Recommend Cover Torque	: 2.5 to 3 Kgf-cm
Recommend Gland Nut Torque	: 6.5 to 7 Kgf-cm

Diagram



Item	Part Name	Material / Finish
1	Housing	Thermoplastic Colour Black
2	Screw Nut	Thermoplastic Colour Black
3	DC Plug	Housing Thermoplastics Colour: Black
		Neg. Terminal Copper Alloy, Finish: Ni Plated
		Pos. Terminal Copper Alloy: Finish Ni Plated
4	O-Ring	Silicone Colour Red
5	Glue	Epoxy Colour: Black
6	Gasket	EPDM Colour: Black
7	Cover	Thermoplastic Colour Black
8	Gland	NBR Colour: Black
9	Gland Nut	Thermoplastic Colour Black
10	C-Ring	SWB Finish: Zn Plated

Part Number Table

Description	Part Number
DC Power Connector, Jack, 2mm	MP015831

Dimensions : Millimetres

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro
Farnell.com/multicomp-pro
sg.element14.com/b/multicomp-pro

multicomp^{PRO}