## 23160

# residual current circuit breaker RCCB ID clic 2 poles 40 A class AC 30 mA



#### Main

DuoLine
ID' clic RCCB
2P
Left
40 A
AC
50/60 Hz
230 V AC 50/60 Hz conforming to IEC 61008
30 mA
Instantaneous
Class AC
Im 500 A

### Complementary

Device location in system	Group incomer
Residual current tripping technology	Electromechanical
Rated conditional short-circuit current	3 kA 40 A
Control type	Toggle
Mounting mode	Fixed
Mounting support	35 mm symmetrical DIN rail
Comb busbar distribution block compatibility	Upside: Bar'clic
Height	92 mm
Width	36 mm
Depth	73 mm
Product weight	0.18 kg
Mechanical durability	10000 cycles
Connections - terminals	Tunnel type terminals 16 mm²
Wire stripping length	13 mm
Tightening torque	3.5 N.m

#### **Environment**

Standards	IEC 61008	
Quality labels	NF	
Tropicalisation	2 conforming to IEC 61008	
Relative humidity	95 % ( 55 °C )	
Operating altitude	2000 m	
Ambient air temperature for operation	-540 °C	
Ambient air temperature for storage	-4060 °C	
RoHS EUR conformity date	0722	
RoHS EUR status	Compliant	