

# DATA SHEET

## THICK FILM CHIP RESISTORS

Automotive Precision grade

AE series

0.1%, 0.5%, 1%, TC 25/50

Sizes 0402/0603/0805/1206

RoHS compliant & Halogen Free



**YAGEO**

Product specification – January 20, 2025 V.1



## SCOPE

This specification describes AE0402 to AE1206 ultra precision chip resistors with lead-free terminations made by thick film process.

## APPLICATIONS

- All general purpose applications
- Car electronics
- Industrial applications

## FEATURES

- AEC-Q200 qualified
- Halogen Free Epoxy
- RoHS compliant
- Reducing environmentally hazardous wastes
- High component and equipment reliability
- Moisture sensitivity level: MSL 1

## ORDERING INFORMATION - GLOBAL PART NUMBER & 12NC

Both part numbers are identified by the series, size, tolerance, packing type, temperature coefficient, taping reel and resistance value.

### YAGEO BRAND ordering code

### GLOBAL PART NUMBER (PREFERRED)

AE XXXX X X X XX XXXX L  
(1) (2) (3) (4) (5) (6) (7)

#### (1) SIZE

0402 / 0603 / 0805 / 1206

#### (2) TOLERANCE

B =  $\pm 0.1\%$

D =  $\pm 0.5\%$

F =  $\pm 1\%$

#### (3) PACKAGING TYPE

R = Paper/PE taping reel

#### (4) TEMPERATURE COEFFICIENT OF RESISTANCE

- = Base on spec

E =  $\pm 50$  ppm/ $^{\circ}\text{C}$

#### (5) TAPING REEL

07 = 7 inch dia. Reel

13 = 13 inch dia. Reel

#### (6) RESISTANCE VALUE

There are 2~4 digits indicated the resistor value. Letter R/K/M is decimal point, no need to mention the last zero after R/K/M, e.g. 1K2, not 1K20.

Detailed resistance rules show in table of "Resistance rule of global part number".

#### (7) DEFAULT CODE

Letter L is system default code for order only (Note)

### Resistance rule of global part number


Resistance code rule	Example
XXRX (10 to 97.6 $\Omega$ )	10R = 10 $\Omega$ 97R6 = 97.6 $\Omega$
XXXR (100 to 976 $\Omega$ )	100R = 100 $\Omega$
XXXX (1 to 9.76 K $\Omega$ )	1K = 1,000 $\Omega$ 9K76 = 9760 $\Omega$
XXXX (1 M $\Omega$ )	1M = 1,000,000 $\Omega$

### ORDERING EXAMPLE

The ordering code of a AE0603 chip resistor, TC 25 value 56 $\Omega$  with  $\pm 0.5\%$  tolerance, supplied in 7-inch tape reel is: AE0603DR-0756RL.

### NOTE

1. All our R-Chip products meet RoHS compliant and Halogen Free. "LFP" of the internal 2D reel label mentions "Lead Free Process"
2. On customized label, "LFP" or specific symbol can be printed

**MARKING****AE0402**

No marking


**AE0603 / AE0805 / AE1206**

Fig. 2 Value = 10 kΩ

E-24 series: 3 digits,  $\pm 5\%$   
First two digits for significant figure and 3rd digit for number of zeros

**AE0603**

Fig. 3 Value = 24 Ω

E-24 series: 3 digits,  $\pm 1\%$  &  $\pm 0.5\%$   
One short bar under marking letter




Fig. 4 Value = 12.4 kΩ

E-96 series: 3 digits,  $\pm 1\%$  &  $\pm 0.5\%$   
First two digits for E-96 marking rule and 3rd letter for number of zeros


**AE1206**

Fig. 5 Value = 10 kΩ

Either resistance in E-24 or E-96: 4 digits  
First three digits for significant figure and 4th digit for number of zeros


For further marking information, please see special data sheet "Chip resistors marking".

**CONSTRUCTION**

The resistors are constructed out of a high-grade ceramic body. Internal metal electrodes are added at each end and connected by a resistive layer. The resistive layer is adjusted to give the approximate required resistance and laser cutting of this resistive layer that achieves tolerance trims the value. The resistive layer is covered with a protective coat and printed with the resistance value. Finally, the two external terminations (matte tin) are added. See fig. 6.

Table I For outlines see fig. 6

TYPE	L (mm)	W (mm)	H (mm)	I <sub>1</sub> (mm)	I <sub>2</sub> (mm)
AE0402	1.00 ±0.05	0.50 ±0.05	0.32 ±0.05	0.16 <sup>+0.14/-0.06</sup>	0.29 ±0.10
AE0603	1.60 ±0.10	0.80 ±0.10	0.45 ±0.10	0.20 <sup>+0.20/-0.10</sup>	0.45 ±0.15
AE0805	2.00 ±0.10	1.25 ±0.10	0.50 ±0.10	0.25 <sup>+0.25/-0.15</sup>	0.50 <sup>+0.10/-0.30</sup>
AE1206	3.10 ±0.20	1.60 ±0.10	0.60 ±0.10	0.35 ±0.20	0.50 ±0.20

**OUTLINES**

## ELECTRICAL CHARACTERISTICS

Table 2

TYPE	RESISTANCE RANGE (E24/E96)	OPERATING TEMPERATURE RANGE	POWER RATING	MAXIMUM WORKING VOLTAGE	DIELECTRIC WITHSTAND VOLTAGE	MAXIMUM OVERLOAD VOLTAGE	TEMPERATURE COEFFICIENT OF RESISTANCE
AE0402	100Ω to 1MΩ	-55 °C to +155 °C	1/8 W	75 V	100 V	100 V	- : Hot : ±25ppm/°C Cold : -50~+25ppm/°C E : ±50ppm/°C
AE0603	100Ω to 1MΩ		1/5 W	100 V	150 V	150 V	
AE0805	100Ω to 1MΩ		1/4 W	150 V	300 V	300 V	
AE1206	100KΩ to 1MΩ		1/3 W	200 V	500 V	400 V	

## NOTE

The maximum working voltage that may be continuously applied to the resistor element, see “IEC publication 60115-8”

## FOOTPRINT AND SOLDERING PROFILES

For recommended footprint and soldering profiles, please see the special data sheet “Chip resistors mounting”

## PACKING STYLE AND PACKAGING QUANTITY

Table 3 Packing style and packaging quantity

PACKING STYLE	REEL DIMENSION	AE0402	AE0603	AE0805	AE1206
Paper/PE taping reel (R)	7" (178 mm)	10,000	5,000	5,000	5,000
	13" (330 mm)	50,000	20,000	20,000	20,000

## NOTE

1. For Paper/PE tape and reel specification/dimensions, please see the special data sheet “Chip resistors packing”

## FUNCTIONAL DESCRIPTION

## POWER RATING

Each type rated power at 70°C:

AE0402=1/8W

AE0603=1/5W

AE0805=1/4W

AE1206=1/3W

## RATED VOLTAGE

The DC or AC (rms) continuous working voltage corresponding to the rated power is determined by the following formula:

$$V = \sqrt{P \times R}$$

or max. working voltage whichever is less

Where

V=Continuous rated DC or  
AC (rms) working voltage (V)

P=Rated power (W)

R=Resistance value (Ω)




Fig. 7 Maximum dissipation (P) in percentage of rated power as a function of the operating ambient temperature ( $T_{amb}$ )

## TESTS AND REQUIREMENTS

Table 4 Test condition, procedure and requirements

TEST	TEST METHOD	PROCEDURE	REQUIREMENTS
High Temperature Exposure	AEC-Q200 Test 3 MIL-STD-202 Method 108	1,000 hours at $T_A = 155\text{ }^{\circ}\text{C}$ , unpowered	$\pm(0.5\%+0.05\Omega)$
Moisture Resistance	AEC-Q200 Test 6 MIL-STD-202 Method 106	Each temperature / humidity cycle is defined at 8 hours (method 106F), 3 cycles / 24 hours for 10d. with $25\text{ }^{\circ}\text{C}$ / $65\text{ }^{\circ}\text{C}$ 95% R.H, without steps 7a & 7b, unpowered Parts mounted on test-boards, without condensation on parts	$\pm(0.5\%+0.05\Omega)$
Biased Humidity	AEC-Q200 Test 7 MIL-STD-202 Method 103	1,000 hours; $85\text{ }^{\circ}\text{C}$ / 85% RH 10% of operating power Measurement at $24\pm 4$ hours after test conclusion.	$\pm(1.0\%+0.05\Omega)$
Operational Life	AEC-Q200 Test 8 MIL-STD-202 Method 108	1,000 hours at $125\text{ }^{\circ}\text{C}$ , derated voltage applied for 1.5 hours on, 0.5 hour off, still-air required	$\pm(1.0\%+0.05\Omega)$
Resistance to Soldering Heat	AEC-Q200 Test 15 MIL-STD-202 Method 210	Condition B, no pre-heat of samples Lead-free solder, $260\pm 5\text{ }^{\circ}\text{C}$ , $10\pm 1$ seconds immersion time Procedure 2 for SMD: devices fluxed and cleaned with isopropanol	$\pm(0.2\%+0.05\Omega)$ No visible damage
Thermal Shock	AEC-Q200 Test 16 MIL-STD-202 Method 107	$-55/+125\text{ }^{\circ}\text{C}$ Number of cycles is 300. Devices mounted Maximum transfer time is 20 seconds. Dwell time is 15 minutes. Air – Air	$\pm(0.5\%+0.05\Omega)$
ESD	AEC-Q200 Test 17 AEC-Q200-002	Human Body Model, $I_{\text{pos.}} + I_{\text{neg.}}$ discharges 0402/0603: 1KV 0805 and above: 2KV	$\pm(3.0\%+0.05\Omega)$

TEST	TEST METHOD	PROCEDURE	REQUIREMENTS
Solderability - Wetting	AEC-Q200 Test 18 J-STD-002	Electrical Test not required Magnification 50X SMD conditions: (a) Method B, aging 4 hours at 155 °C dry heat, dipping at 235±3 °C for 5±0.5 seconds. (b) Method B, steam aging 8 hours, dipping at 215±3 °C for 5±0.5 seconds. (c) Method D, steam aging 8 hours, dipping at 260±3 °C for 30±0.5 seconds.	Well tinned (≥95% covered) No visible damage
Board Flex	AEC-Q200 Test 21 AEC-Q200-005	Chips mounted on a 90mm glass epoxy resin PCB (FR4) Bending for 0402: 5 mm 0603/0805: 3 mm 1206 and above: 2 mm Holding time: minimum 60 seconds	±(1.0%+0.05Ω)
Temperature Coefficient of Resistance (T.C.R.)	MIL-STD-202 Method 304	At +25/-55 °C and +25/+125 °C  <b>Formula:</b> $T.C.R. = \frac{R_2 - R_1}{R_1(t_2 - t_1)} \times 10^6 \text{ (ppm/°C)}$  Where t <sub>1</sub> =+25 °C or specified room temperature t <sub>2</sub> =-55 °C or +125 °C test temperature R <sub>1</sub> =resistance at reference temperature in ohms R <sub>2</sub> =resistance at test temperature in ohms	Refer to table 2
Short Time Overload	IEC60115-1 4.13	2.5 times of rated voltage or maximum overload voltage whichever is less for 5 sec at room temperature	±(0.5%+0.05Ω)
FOS	ASTM-B-809-95	Sulfur (saturated vapor) 500 hours, 60±2°C, unpowered	±(1.0%+0.05Ω)

REVISION HISTORY

REVISION	DATE	CHANGE NOTIFICATION	DESCRIPTION
Version I	Jan. 20, 2025		- Add size 0402, 0603, 0805
Version 0	Jul. 18, 2023		- New datasheet for Automotive thick film ultra precision chip resistors sizes of 0402/0603/0805/1206, 0.1%, 0.5%, 1%, TC25

## LEGAL DISCLAIMER

YAGEO, its distributors and agents (collectively, "YAGEO"), hereby disclaims any and all liabilities for any errors, inaccuracies or incompleteness contained in any product related information, including but not limited to product specifications, datasheets, pictures and/or graphics. YAGEO may make changes, modifications and/or improvements to product related information at any time and without notice.

YAGEO makes no representation, warranty, and/or guarantee about the fitness of its products for any particular purpose or the continuing production of any of its products. To the maximum extent permitted by law, YAGEO disclaims (i) any and all liability arising out of the application or use of any YAGEO product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for a particular purpose, non-infringement and merchantability.

YAGEO products are designed for general purpose applications under normal operation and usage conditions. Please contact YAGEO for the applications listed below which require especially high reliability for the prevention of defects which might directly cause damage to the third party's life, body or property: Aerospace equipment (artificial satellite, rocket, etc.), Atomic energy-related equipment, Aviation equipment, Disaster prevention equipment, crime prevention equipment, Electric heating apparatus, burning equipment, Highly public information network equipment, data-processing equipment, Medical devices, Military equipment, Power generation control equipment, Safety equipment, Traffic signal equipment, Transportation equipment and Undersea equipment, or for any other application or use in which the failure of YAGEO products could result in personal injury or death, or serious property damage. Particularly **YAGEO Corporation and its affiliates do not recommend the use of commercial, automotive, and/or COTS grade products for high reliability applications or manned space flight.**

Information provided here is intended to indicate product specifications only. YAGEO reserves all the rights for revising this content without further notification, as long as products are unchanged. Any product change will be announced by PCN.