

Multilayer Ceramic Capacitor

Radial-Leaded Type Capacitor

multicompPRO

**RoHS
Compliant**



Description


Its specification applies to Radial Series Ceramic Capacitor.

Part Number Explanation

RD21	B				102	K	500	B	5	C	07	B
Product Type	Dielectric Code				Capacitance Code	Tolerance Code	Rated Voltage	Packaging Code	Chip Size	Termination	Lead length	Lead length Tolerance
	Code	T.C.	Operating Temperature	Capacitance Change(Δ°C)								
RD20 RD21	N	NPO	-55 ~ +125°C	0±30(PPM/°C)	100=10 pF 102=1000 pF 103=10000pF 1R5=1.5 pF 101=100 pF 472=4700 pF 104=100000pF	C=±0.25pF D=±0.5pF J=±5% K=±10% M=±20% Z=±80% /-20%	100=10V 250=25V 500=50V 101=100V 201=200V 251=250V 501=500V 631=630V 102=1000V 202=2000V 302=3000V	B=Bulk A=Ammo	5=0805 6=1206 0=1210 2=1812	L=Ag/Ni/Sn C=Cu/Ni/Sn A=Ag/Ni/Sn Halogen free H=Cu/Ni/Sn Halogen free	Tapping: AN=Ammo Bulk (ex): 07=7mm	D=Tapping A=±0.5mm B=±1mm C=Min
	B	X7R	-55 ~ +125°C	±15%								
	F	Y5V	-25 ~ +85°C	+30% ~ -80%								

Remark about tolerance code: NPO: all tolerance, X7R: K M, Y5V: M Z

Lead Configuration and Size



Type Code	Chip Size	Width (W) Max.	Height (Max.)		Thickness (T)Max.	Lead length (L)	Lead Spacing for Taping (F)	Lead Spacing for Bulk (F)	Lead Diameter (d)
			h	h1					
RD20	0805	5	4.5	6	3.5	Refer to the item "2.2 SAP Part Number"	2.5 ±0.8	2.54 ±1	0.5 ±0.05
RD21	0805	5	4.5	6.5	3.5		5 ±0.8	5.08 ±1	
	1206	6.5	5	7	4				
	1210 (Special size)	6.5	5.5	7.5	5				
	1812	8	6.5	8.5	5.5				

Dimensions : Millimetres

Newark.com/multicomp-pro
Farnell.com/multicomp-pro
sg.element14.com/b/multicomp-pro

multicompPRO


Multilayer Ceramic Capacitor

Radial-Leaded Type Capacitor

multicompPRO

Product Structure

Radial capacitor



No.	Part Name	Material	
1.	MLCC Capacitor	Ceramic Dielectric	
		Internal Electrode	Ag-Pd or Ni (BME)
		End Termination	Ag or Cu (BME) layer
			Ni layer
			Sn layer
2.	Solder	Tin-silver	
3.	Radial Lead Wire	Tined CP wire	
4.	Coating	Epoxy resin (Blue)	

Test conditions:

Tests shall, unless otherwise specified, be carried out at 15 to 35°C and RH 45 to 75%.

If any doubt and argument has been encounter in judgement, the final test shall be done at 25±2°C, RH45 to 55% and 860~1060mbar. (Based on JIS standard)

Handle procedure:

To avoid unexpected testing results from occurring, the tested capacitor must be kept at room temperature for at least 30 minutes and completely discharged.

Multilayer Ceramic Capacitor

Radial-Leaded Type Capacitor

multicompPRO

Specification and test method

Item	Performance	Test or inspection method																																																					
Appearance structure size	No defects which may affect performance.	As section 3																																																					
Withstand Voltage	Withstand test voltage without Insulation breakdown or other damage.	DC Tested voltage shall be applied for 1~ 5sec. Charge/discharge current shall not exceed 50mA. <table><tr><th>Rated Voltage</th><th>Tested Voltage</th></tr><tr><td><100V</td><td>2.5Ra</td></tr><tr><td>100V</td><td>3Ra</td></tr><tr><td>200~300V</td><td>2Ra</td></tr><tr><td>500~999V</td><td>1.5 Ra</td></tr><tr><td>1000~3000V</td><td>1.2 Ra</td></tr></table>	Rated Voltage	Tested Voltage	<100V	2.5Ra	100V	3Ra	200~300V	2Ra	500~999V	1.5 Ra	1000~3000V	1.2 Ra																																									
Rated Voltage	Tested Voltage																																																						
<100V	2.5Ra																																																						
100V	3Ra																																																						
200~300V	2Ra																																																						
500~999V	1.5 Ra																																																						
1000~3000V	1.2 Ra																																																						
Insulation Resistance	NPO: 10,000MΩ Min. or 500Ω×F Min X7R-Y5V: 10GΩ Min or R·C ≥ 500Ω·F (Whichever is smaller)	Insulation resistance shall be measured at 120±5 seconds after rated voltage applied. <table><tr><th>Rated Voltage</th><th>Tested Voltage</th></tr><tr><td><500V</td><td>1 Ra</td></tr><tr><td>≥500V</td><td>500V</td></tr></table>	Rated Voltage	Tested Voltage	<500V	1 Ra	≥500V	500V																																															
Rated Voltage	Tested Voltage																																																						
<500V	1 Ra																																																						
≥500V	500V																																																						
Capacitance	Within the specified tolerance.	Measuring frequency & voltage: NPO: >1000pF: 1kHz±10% 1.0±0.2 Vrms ≤1000pF: 1MHz±10% 1±0.2 Vrms X7R, Y5V: C ≤10uF 1 ±0.2 Vrms 1kHz±10% C>10μF 0.5 ±0.2Vrms 120Hz ±20%																																																					
Dissipation Factor	<table><tr><td rowspan="2">NPO</td><td colspan="3">More than 30pF: Q≥1000</td></tr><tr><td colspan="3">Less than 30pF: Q≥400+20C</td></tr><tr><td rowspan="8">X7R</td><td>Rated vol.</td><td>DF≤</td><td>Special chip size and capacitance</td></tr><tr><td rowspan="3">≥100V</td><td>≤2.5%</td><td></td></tr><tr><td>≤3%</td><td>1206≥0.47uF</td></tr><tr><td>≤5%</td><td>0805>0.1μF,1206>1μF</td></tr><tr><td rowspan="4">50V</td><td>≤2.5%</td><td></td></tr><tr><td>≤3%</td><td>0805≥0.18μF, 1206≥0.47μF</td></tr><tr><td>≤5%</td><td>1210≥4.7μF</td></tr><tr><td>≤10%</td><td>0805≥1μF, 1206≥2.2μF, 1210≥10μF</td></tr><tr><td rowspan="10">Y5V</td><td>Rated vol.</td><td>DF≤</td><td>Special chip size and capacitance</td></tr><tr><td rowspan="2">≥50V</td><td>≤5%</td><td></td></tr><tr><td>≤7%</td><td>0805≥0.47μF, 1206≥ 4.7μF</td></tr><tr><td rowspan="3">25V</td><td>≤5%</td><td></td></tr><tr><td>≤7%</td><td>0805≥0.33μF, 1206≥1μF, 1210≥4.7μF</td></tr><tr><td>≤9%</td><td>1206≥4.7μF, 1210≥22μF</td></tr><tr><td>16V (C<1μF)</td><td>≤7%</td><td></td></tr><tr><td rowspan="2">16V C≥1μF)</td><td>≤9%</td><td></td></tr><tr><td>≤12.5%</td><td>0805≥3.3μF;1206≥10μF; 1210≥22μF; 1812≥47μF</td></tr><tr><td>10V</td><td>≤12.5%</td><td></td></tr></table>		NPO	More than 30pF: Q≥1000			Less than 30pF: Q≥400+20C			X7R	Rated vol.	DF≤	Special chip size and capacitance	≥100V	≤2.5%		≤3%	1206≥0.47uF	≤5%	0805>0.1μF,1206>1μF	50V	≤2.5%		≤3%	0805≥0.18μF, 1206≥0.47μF	≤5%	1210≥4.7μF	≤10%	0805≥1μF, 1206≥2.2μF, 1210≥10μF	Y5V	Rated vol.	DF≤	Special chip size and capacitance	≥50V	≤5%		≤7%	0805≥0.47μF, 1206≥ 4.7μF	25V	≤5%		≤7%	0805≥0.33μF, 1206≥1μF, 1210≥4.7μF	≤9%	1206≥4.7μF, 1210≥22μF	16V (C<1μF)	≤7%		16V C≥1μF)	≤9%		≤12.5%	0805≥3.3μF;1206≥10μF; 1210≥22μF; 1812≥47μF	10V	≤12.5%
NPO	More than 30pF: Q≥1000																																																						
	Less than 30pF: Q≥400+20C																																																						
X7R	Rated vol.	DF≤	Special chip size and capacitance																																																				
	≥100V	≤2.5%																																																					
		≤3%	1206≥0.47uF																																																				
		≤5%	0805>0.1μF,1206>1μF																																																				
	50V	≤2.5%																																																					
		≤3%	0805≥0.18μF, 1206≥0.47μF																																																				
		≤5%	1210≥4.7μF																																																				
		≤10%	0805≥1μF, 1206≥2.2μF, 1210≥10μF																																																				
Y5V	Rated vol.	DF≤	Special chip size and capacitance																																																				
	≥50V	≤5%																																																					
		≤7%	0805≥0.47μF, 1206≥ 4.7μF																																																				
	25V	≤5%																																																					
		≤7%	0805≥0.33μF, 1206≥1μF, 1210≥4.7μF																																																				
		≤9%	1206≥4.7μF, 1210≥22μF																																																				
	16V (C<1μF)	≤7%																																																					
	16V C≥1μF)	≤9%																																																					
		≤12.5%	0805≥3.3μF;1206≥10μF; 1210≥22μF; 1812≥47μF																																																				
	10V	≤12.5%																																																					

Multilayer Ceramic Capacitor

Radial-Leaded Type Capacitor

multicompPRO

Item	Performance	Test or inspection method																											
Temperature Characteristic of Capacitance	<table><tr><th colspan="3">Temperatures Coefficient</th></tr><tr><th>T.C</th><th>Operating Temperature</th><th>Capacitance Change(ΔC)</th></tr><tr><td>NPO</td><td>-55 ~ +125°C</td><td>0±30 (ppm/°C)</td></tr><tr><td>X7R</td><td>-55 ~ +125°C</td><td>±15%</td></tr><tr><td>Y5V</td><td>-25 ~ +85°C</td><td>+30% ~ -80%</td></tr></table>	Temperatures Coefficient			T.C	Operating Temperature	Capacitance Change(ΔC)	NPO	-55 ~ +125°C	0±30 (ppm/°C)	X7R	-55 ~ +125°C	±15%	Y5V	-25 ~ +85°C	+30% ~ -80%	The temperature coefficient is determined using the capacitance measured at base temperature as a reference. Test the specimen in a range of maximum and minimum operation temperature that shown as left table. * Base Temp 25±2°C * Base Temp for Y5V: 20±2°C <table><tr><th>Step</th><th>Temperature (°C)</th></tr><tr><td>1</td><td>Base Temp.(25°C) ±2°C</td></tr><tr><td>2</td><td>Min. Operation Temp. ±2°C</td></tr><tr><td>3</td><td>Base Temp.(25°C) ±2°C</td></tr><tr><td>4</td><td>Max. Operation Temp. ±2°C</td></tr><tr><td>5</td><td>Base Temp.(25°C) ±2°C</td></tr></table>	Step	Temperature (°C)	1	Base Temp.(25°C) ±2°C	2	Min. Operation Temp. ±2°C	3	Base Temp.(25°C) ±2°C	4	Max. Operation Temp. ±2°C	5	Base Temp.(25°C) ±2°C
Temperatures Coefficient																													
T.C	Operating Temperature	Capacitance Change(ΔC)																											
NPO	-55 ~ +125°C	0±30 (ppm/°C)																											
X7R	-55 ~ +125°C	±15%																											
Y5V	-25 ~ +85°C	+30% ~ -80%																											
Step	Temperature (°C)																												
1	Base Temp.(25°C) ±2°C																												
2	Min. Operation Temp. ±2°C																												
3	Base Temp.(25°C) ±2°C																												
4	Max. Operation Temp. ±2°C																												
5	Base Temp.(25°C) ±2°C																												
Terminal strength	Tensile strength: No breakdown	Loading weight 0.5 Kgs is applied for 10±1 seconds																											
	Bending strength: No breakdown	Loading weight 0.25 Kgs is applied Bending back and forth 90 degrees twice																											
Soldering heat resistance	<table><tr><th>External appearance</th><th colspan="2">No mechanical damage.</th></tr><tr><td rowspan="3">Cap. change (ΔC/C)</td><td>NPO</td><td>±2.5% or ±0.25 pF max. Whichever is larger</td></tr><tr><td>X7R</td><td>±7.5%</td></tr><tr><td>Y5V</td><td>±20%</td></tr><tr><td>D.F.</td><td colspan="2">To meet initial standard value</td></tr><tr><td>I.R.</td><td colspan="2">To meet initial standard value</td></tr></table>	External appearance	No mechanical damage.		Cap. change (ΔC/C)	NPO	±2.5% or ±0.25 pF max. Whichever is larger	X7R	±7.5%	Y5V	±20%	D.F.	To meet initial standard value		I.R.	To meet initial standard value		Lead wire or terminals shall be immersed (A) up to 2mm from body (B) into the Molten solder of which temperature is 260+5 -0°C for 3±0.5 sec. Then leave at standard test conditions for 24±2 hours, then measured. *Preconditioning: (only for Class 2): Perform a heat treatment at 150 +0/-10°C for one hour and then let sit for 48 ± 4 hours at room temperature.											
External appearance	No mechanical damage.																												
Cap. change (ΔC/C)	NPO	±2.5% or ±0.25 pF max. Whichever is larger																											
	X7R	±7.5%																											
	Y5V	±20%																											
D.F.	To meet initial standard value																												
I.R.	To meet initial standard value																												
Solderability	Lead wire shall be soldered over 75% of the circumfluent direction	To comply with JIS-C-5102 8.4, the soldering temperature is 245±5°C and dipping time is 5±0.5 seconds. Flux: weight ratio of Rosin 25%																											
Humidity (Steady state)	<table><tr><th>External appearance</th><th>No mechanical damage.</th></tr><tr><td>Cap. change (ΔC/C)</td><td>NPO: ± 5% or ±0.5 pFmax. (Whichever is larger) X7R: ±12.5% Y5V: ±30%</td></tr></table> D.F.: NPO: C≥30pF: D.F. ≤ $\frac{1}{350}$ 10pF≤C<30pF: D.F. ≤ $\frac{1}{275 + 2.5^{\circ}\text{C}}$ C<10pF: D.F. ≤ $\frac{1}{200 + 10^{\circ}\text{C}}$ PS: C: Nominal Capacitance (pF)	External appearance	No mechanical damage.	Cap. change (ΔC/C)	NPO: ± 5% or ±0.5 pFmax. (Whichever is larger) X7R: ±12.5% Y5V: ±30%	Humidity (Steady state): At temperature 40 ±2°C and humidity 90 to 95%RH for 500 +24/-0 hours. Leave the capacitors in ambient condition for the following time before measurement. Class 1: 24±2 hours. Class 2: 48±4 hours. *Charge / discharge current shall. not exceed 50mA. * Preconditioning: (only for Class 2): Apply the rated DC voltage for 1hour at 150 ±5°C. Remove and let sit for 48±4 hours at room temperature. Perform initial measurement.																							
External appearance	No mechanical damage.																												
Cap. change (ΔC/C)	NPO: ± 5% or ±0.5 pFmax. (Whichever is larger) X7R: ±12.5% Y5V: ±30%																												

Multilayer Ceramic Capacitor

Radial-Leaded Type Capacitor

multicompPRO

Item	Performance				Test or inspection method
	X7R	Rated vol.	DF≤	Special chip size and capacitance	
		≥100V	≤3%		
			≤6%	1206≥0.47uF	
			≤7.5%	0805>0.1μF,1206>1μF	
		50V	≤3%		
			≤6%	0805≥0.18μF, 1206≥0.47μF	
			≤10%	1210≥4.7μF	
			≤20%	0805≥1μF, 1206≥2.2μF, 1210≥10μF	
	Y5V	Rated vol.	DF≤	Special chip size and capacitance	
		≥50V	≤7.5%		
			≤10%	0805≥0.47μF, 1206≥ 4.7μF	
		25V	≤7.5%		
			≤10%	0805≥0.33μF, 1206≥1μF, 1210≥4.7μF	
			≤15%	1206≥4.7μF, 1210≥22μF	
		16V (C<1μF)	≤10%		
		16V C≥1μF)	≤12.5%		
			≤20%	0805≥3.3μF;1206≥10μF; 1210≥22μF; 1812≥47μF	
		10V	≤20%		
	I.R.	1GΩ min. or 50Ω*F (Whichecker is smaller)			
	Humidity load	External appearance		No mechanical damage.	
Cap. change (ΔC/C)		NPO: ±5% or ±0.5pFmax. (Whichecker is larger) X7R: ±12.5% Y5V: ±30%			
D.F.: NPO: C≥30pF: D.F. ≤ $\frac{1}{350}$ 10pF≤C<30pF: D.F. ≤ $\frac{1}{275 + 2.5^{\circ}\text{C}}$ C<10pF: D.F. ≤ $\frac{1}{200 + 10^{\circ}\text{C}}$ PS: C: Nominal Capacitance (pF)					
Humidity load: (apply for the product with rated voltage 500V-Max): Apply the rated voltage at temperature 40±2°C and humidity 90 to 95%RH for 500 +24/-0 hours. Leave the capacitors in ambient condition for the following time before measurement. Class 1: 24±2 hours. Class 2: 48±4 hours. * Charge / discharge current shall. not exceed 50mA. * Preconditioning : (only for Class 2): Apply the rated DC voltage for 1 hour at 150 ±5°C. Remove and let sit for 48±4 hours at room temperature. Perform initial measurement.					

Multilayer Ceramic Capacitor

Radial-Leaded Type Capacitor

multicompPRO

Item	Performance				Test or inspection method																
	X7R	Rated vol.	DF≤	Special chip size and capacitance																	
			≤3%																		
		≥100V	≤6%	1206≥0.47uF																	
			≤7.5%	0805>0.1μF,1206>1μF																	
			≤3%																		
		50V	≤6%	0805≥0.18μF, 1206≥0.47μF																	
			≤10%	1210≥4.7μF																	
			≤20%	0805≥1μF, 1206≥2.2μF, 1210≥10μF																	
		Y5V	Rated vol.	DF≤			Special chip size and capacitance														
	≤7.5%																				
	≥50V		≤10%	0805≥0.47μF, 1206≥ 4.7μF																	
			≤7.5%																		
	25V		≤10%	0805≥0.33μF, 1206≥1μF, 1210≥4.7μF																	
			≤15%	1206≥4.7μF, 1210≥22μF																	
			16V (C<1μF)	≤10%																	
	16V C≥1μF)		≤12.5%																		
			≤20%	0805≥3.3μF;1206≥10μF; 1210≥22μF; 1812≥47μF																	
10V			≤20%																		
I.R.	500MΩ min. or 25Ω*F (Whichever is smaller)																				
Temperature Load	External appearance		No mechanical damage.		<table><tr><th>Rated Voltage</th><th>Tested Voltage</th></tr><tr><td>< 500V</td><td>2Ra</td></tr><tr><td>500V</td><td>1.5Ra</td></tr><tr><td>≥ 630V</td><td>1.2Ra</td></tr><tr><td>≥ 1000V</td><td>1.2Ra</td></tr></table>		Rated Voltage	Tested Voltage	< 500V	2Ra	500V	1.5Ra	≥ 630V	1.2Ra	≥ 1000V	1.2Ra					
	Rated Voltage	Tested Voltage																			
	< 500V	2Ra																			
	500V	1.5Ra																			
	≥ 630V	1.2Ra																			
	≥ 1000V	1.2Ra																			
	Cap. change (ΔC/C)		NPO: ±3% or ±0.3pFmax. (Whichever is larger) X7R: ≥10V, ±12.5% Y5V: ≥10V, ±30%		PS: The test voltage is 150% of rated voltage for below range.																
	D.F.:				<table><tr><th>Size</th><th>Rated Voltage</th><th>Capacitance</th></tr><tr><td>0805</td><td>50V (X7R)</td><td>C≥2.2μF</td></tr><tr><td></td><td>100V (X7R)</td><td>C≥0.47μF</td></tr><tr><td></td><td>16V (Y5V)</td><td>C≥0.47μF</td></tr><tr><td>1206</td><td>100V (X7R)</td><td>C≥1μF</td></tr></table>		Size	Rated Voltage	Capacitance	0805	50V (X7R)	C≥2.2μF		100V (X7R)	C≥0.47μF		16V (Y5V)	C≥0.47μF	1206	100V (X7R)	C≥1μF
	Size	Rated Voltage	Capacitance																		
	0805	50V (X7R)	C≥2.2μF																		
	100V (X7R)	C≥0.47μF																			
	16V (Y5V)	C≥0.47μF																			
1206	100V (X7R)	C≥1μF																			
NPO:				at maximum operating temperature ±2°C for 1000+48/-0 hours.																	
C≥30pF: D.F. ≤ $\frac{1}{350}$				Leave the capacitors in ambient condition for the following time before measurement.																	
10pF≤C<30pF: D.F. ≤ $\frac{1}{275 + 2.5^{\circ}\text{C}}$				Class I: 24±2 hours																	
C<10pF: D.F. ≤ $\frac{1}{200 + 10^{\circ}\text{C}}$				Class II: 48±4 hours																	
PS: C: Nominal Capacitance (pF)				* Charge / discharge current shall not exceed 50 mA.																	

Multilayer Ceramic Capacitor

Radial-Leaded Type Capacitor

multicompPRO

Item	Performance				Test or inspection method															
	X7R	Rated vol.	DF≤	Special chip size and capacitance	* Preconditioning: (only for Class 2): Apply 200% of the rated DC voltage for 1 hour at the maximum operating temperature ±3°C. Remove and let sit for 48±4 hours at room temperature. Perform initial measurement.															
			≤3%																	
		≥100V	≤6%	1206≥0.47μF																
			≤7.5%	0805>0.1μF,1206>1μF																
			≤3%																	
		50V	≤6%	0805≥0.18μF, 1206≥0.47μF																
			≤10%	1210≥4.7μF																
			≤20%	0805≥1μF, 1206≥2.2μF, 1210≥10μF																
	Y5V		Rated vol.	DF≤		Special chip size and capacitance														
		≥50V		≤7.5%																
		≤10%	0805≥0.47μF, 1206≥ 4.7μF																	
		25V	≤7.5%																	
			≤10%	0805≥0.33μF, 1206≥1μF, 1210≥4.7μF																
			≤15%	1206≥4.7μF, 1210≥22μF																
		16V (C<1μF)	≤10%																	
		16V (C≥1μF)	≤12.5%																	
			≤20%	0805≥3.3μF;1206≥10μF; 1210≥22μF; 1812≥47μF																
		10V	≤20%																	
		I.R.	1000MΩ min. or 50Ω*F (Whichever is smaller)																	
Temperature cycle	External appearance		No mechanical damage.		The capacitor shall be subject 5 cycles according to four heat treatments listed in the following table. Then Leave the capacitors in ambient condition for the following time before measurement. Class I: 24±2 hours Class II: 48±4 hours <table><tr><th>Step</th><th>Temperature (°C)</th><th>Duration (min.)</th></tr><tr><td>1</td><td>Min. Operation Temp.±3</td><td>30±3</td></tr><tr><td>2</td><td>Room Temp. (25°C)</td><td>2 ~ 3</td></tr><tr><td>3</td><td>Max. Operation Temp.±3</td><td>30±2</td></tr><tr><td>4</td><td>Room Temp. (25°C)</td><td>2 ~ 3</td></tr></table> Preconditioning: (only for Class 2): Perform a heat treatment at 150 +0-10°C for one hour and then let sit for 48±4 hours at room	Step	Temperature (°C)	Duration (min.)	1	Min. Operation Temp.±3	30±3	2	Room Temp. (25°C)	2 ~ 3	3	Max. Operation Temp.±3	30±2	4	Room Temp. (25°C)	2 ~ 3
	Step	Temperature (°C)	Duration (min.)																	
	1	Min. Operation Temp.±3	30±3																	
	2	Room Temp. (25°C)	2 ~ 3																	
	3	Max. Operation Temp.±3	30±2																	
	4	Room Temp. (25°C)	2 ~ 3																	
Cap. change (ΔC/C)		NPO: ±2.5% or ±0.25pFmax. (Whichever is larger) X7R: ±7.5% Y5V: ±20%																		
D.F.		To meet initial standard value																		
I.R.		10000MΩ min. or 500Ω*F (Whichever is smaller)																		

Multilayer Ceramic Capacitor

Radial-Leaded Type Capacitor

multicompPRO

Operating and storage environment

The insulating coating of capacitors does not form a perfect seal; therefore, do not use or store capacitors in a corrosive atmosphere, especially where chloride gas, sulfide gas, acid, alkali, salt or the like are present. Also avoid exposure to moisture. Before cleaning, bonding or molding this product, verify that these processes do not affect product quality by testing the performance of a cleaned, bonded or molded product in the intended equipment. Store the capacitors where the temperature and relative humidity do not exceed 5 to 40 degrees centigrade and 20 to 70%. Use capacitors within 6 months after delivery.

Radial-Leaded, Epoxy-Dipped Multilayer ceramic capacitors are built by superior moisture and shock resistant Epoxy coating, can be supplied in both bulk or tape package for automatic insertion in printed circuit board. But must to avoid effect of external force when the capacitors are used automatic insertion because the inner chips are very weak and easy broken.


RD series capacitors have wide application in computer, data Processor, telecom communication, industrial control, and instrumentation equipment, etc.

(Epoxy coated: Flame resistance for UL94 V-0 Approved)

Features

- Enhanced environmental protection coating.
- COG (NPO), X7R, Y5V characteristic.
- Variety of Lead configuration.

Taping Figure and Specification: (RD21)



Description	Symbol	Dimension (mm)	Remarks
Pitch of Component	P	12.7 ±1	
Feed Hold Pitch	P0	12.7 ±0.3	Cumulative Pitch Error: ±1mm/20 Pitches
Feed Hold Centre to Lead	P1	3.85 ±0.7	
Feed Hold Centre to Component Centre	P2	6.35 ±1.3	
Lead diameter	d	0.5 ±0.05	
Lead to Lead Spacing	F	5 ±0.8	To Lead Tip within Tolerance
Component Alignment, F-R	Δh	2 Max	The Alignment from the Centre of the Lead is ±1mm
Tape Width	W	18 +1.0/-0.5	
Adhesive Tape Width	W0	11 Min.	
Hole Position	W1	9 ±0.5	
Adhesive Tape Position	W2	3 max.	
Height of Bottom Body from Tape Centre	H	18 +2.0/-0	H+12.5mm≤H1

Newark.com/multicomp-pro
Farnell.com/multicomp-pro
sg.element14.com/b/multicomp-pro

multicompPRO


Multilayer Ceramic Capacitor

Radial-Leaded Type Capacitor

multicompPRO

Description	Symbol	Dimension (mm)	Remarks
Lead-Wire Clinch Height	H0	16 ±0.5	6.5≤H0-W1
Component Height	H1	32.25 Max.	
Feed Hole Diameter	D0	4 ±0.2	
Tape Thickness	t	0.6 ±0.3	

Taping Figure and Specification: (RD20)



Description	Symbol	Dimension (mm)	Remarks
Pitch Of Component	P	12.7 ±1	
Feed Hold Pitch	P0	12.7 ±0.3	Cumulative Pitch Error: ±1mm/20 Pitches
Feed Hold Centre to Lead	P1	5.1 ±0.7	
Feed Hold Centre to Component Centre	P2	6.35 ±1.3	
Lead diameter	d	0.5 ±0.05	
Lead To Lead Spacing	F	2.5 ±0.8	To Lead Tip within Tolerance
Component Alignment, F-R	Δh	2 Max	The Alignment from the Centre of the Lead is±1mm
Tape Width	W	18 +1 /-0.5	
Adhesive Tape Width	W0	11 Min.	
Hole Position	W1	9 ±0.5	
Adhesive Tape Position	W2	3 max.	
Lead-Wire Clinch Height from bottom of capacitor to the hold centre	H	18 ±0.5	
Component Height	H1	32.25 Max.	
Feed Hole Diameter	D0	4 ±0.2	
Tape Thickness	t	0.6 ±0.3	

Packing quantity

Chip Size	Taping type		Bulk type
	Quantity per reel	Quantity per box	Quantity per bag
0805	2,000	2,000	1,000
1206,1210,1812	1,500	1,500	1,000

Newark.com/multicomp-pro
Farnell.com/multicomp-pro
sg.element14.com/b/multicomp-pro

multicompPRO

Multilayer Ceramic Capacitor

Radial-Leaded Type Capacitor

multicompPRO

Size code and capacitance (pF) available

Dielectric		NPO										
Size		0805				1206						
Voltage (VDC)		50	100	200	250	50	100	200	250	500	630	1000
Capacitance	1.0pF (010)	B	B	B	B							
	1.2pF (1R2)	B	B	B	B	B	B					
	1.5pF (1R5)	B	B	B	B	B	B	B	B	B	B	B
	1.8pF (1R8)	B	B	B	B	B	B	B	B	B	B	B
	2.2pF (2R2)	B	B	B	B	B	B	B	B	B	B	B
	2.7pF (2R7)	B	B	B	B	B	B	B	B	B	B	B
	3.3pF (3R3)	B	B	B	B	B	B	B	B	B	B	B
	3.9pF (3R9)	B	B	B	B	B	B	B	B	B	B	B
	4.7pF (4R7)	B	B	B	B	B	B	B	B	B	B	B
	5.6pF (5R6)	B	B	B	B	B	B	B	B	B	B	B
	6.8pF (6R8)	B	B	B	B	B	B	B	B	B	B	B
	8.2pF (8R2)	B	B	B	B	B	B	B	B	B	B	B
	10pF (100)	B	B	B	B	B	B	B	B	B	B	B
	12pF (120)	B	B	B	B	B	B	B	B	B	B	B
	15pF (150)	B	B	B	B	B	B	B	B	B	B	B
	18pF (180)	B	B	B	B	B	B	B	B	B	B	B
	22pF (220)	B	B	B	B	B	B	B	B	B	B	B
	27pF (270)	B	B	B	B	B	B	B	B	B	B	B
	33pF (330)	B	B	B	B	B	B	B	B	B	B	B
	39pF (390)	B	B	B	B	B	B	B	B	B	B	B
	47pF (470)	B	B	B	B	B	B	B	B	B	B	B
	56pF (560)	B	B	B	B	B	B	B	B	B	B	B
	68pF (680)	B	B	B	B	B	B	B	B	B	B	B
	82pF (820)	B	B	B	B	B	B	B	B	B	B	B
	100pF (101)	B	B	B	B	B	B	B	B	B	B	B
	120pF (121)	B	B	B	B	B	B	B	B	B	B	B
	150pF (151)	B	B	B	B	B	B	B	B	B	B	B
	180pF (181)	B	B	B	B	B	B	B	B	B	B	B
	220pF (221)	B	B	B	B	B	B	B	B	B	B	B
	270pF (271)	B	B	B	B	B	B	B	B	B	B	B
	330pF (331)	B	B	B	B	B	B	B	B	B	B	B
	390pF (391)	B	B	B	B	B	B	B	B	B	B	B
	470pF (471)	B	B	B	B	B	B	B	B	B	B	B
	560pF (561)	B	B	B	B	B	B	B	B	B		
	680pF (681)	B	B	B	B	B	B	B	B	B		
	820pF (821)	B	B	B	B	B	B	B	B	B		
	1000pF (102)	B	B	B		B	B	B	B	B		
	1200pF (122)	B	B			B	B	B	B	B		
	1500pF (152)	B	B			B	B	B	B	B		
	1800pF (182)	B	B			B	B	B	B	B		
	2200pF (222)	B	B			B	B	B	B	B		
	2700pF (272)	B	B			B	B					

Newark.com/multicomp-pro
Farnell.com/multicomp-pro
sg.element14.com/b/multicomp-pro

multicompPRO

Multilayer Ceramic Capacitor

Radial-Leaded Type Capacitor

multicompPRO

Dielectric		NPO										
Size		0805				1206						
Voltage (VDC)		50	100	200	250	50	100	200	250	500	630	1000
Capacitance	3300pF (332)	B	B			B	B					
	3900pF (392)	B	B			B	B					
	4700pF (472)	B	B			B	B					
	5600pF (562)	B				B	B					
	6800pF (682)	B				B	B					
	8200pF (822)	B				B	B					
	0.01uF (103)	B				B						

Dielectric		X7R										
Size		0805				1206						
Voltage (VDC)		50	100	200	250	50	100	200	250	500	630	1000
Capacitance	100pF (101)	B	B	B	B							
	120pF (121)	B	B	B	B							
	150pF (151)	B	B	B	B	B	B	B	B	B	B	B
	180pF (181)	B	B	B	B	B	B	B	B	B	B	B
	220pF (221)	B	B	B	B	B	B	B	B	B	B	B
	270pF (271)	B	B	B	B	B	B	B	B	B	B	B
	330pF (331)	B	B	B	B	B	B	B	B	B	B	B
	390pF (391)	B	B	B	B	B	B	B	B	B	B	B
	470pF (471)	B	B	B	B	B	B	B	B	B	B	B
	560pF (561)	B	B	B	B	B	B	B	B	B	B	B
	680pF (681)	B	B	B	B	B	B	B	B	B	B	B
	820pF (821)	B	B	B	B	B	B	B	B	B	B	B
	1000pF (102)	B	B	B	B	B	B	B	B	B	B	B
	1200pF (122)	B	B	B	B	B	B	B	B	B	B	B
	1500pF (152)	B	B	B	B	B	B	B	B	B	B	B
	1800pF (182)	B	B	B	B	B	B	B	B	B	B	B
	2200pF (222)	B	B	B	B	B	B	B	B	B	B	B
	2700pF (272)	B	B	B	B	B	B	B	B	B	B	B
	3300pF (332)	B	B	B	B	B	B	B	B	B	B	B
	3900pF (392)	B	B	B	B	B	B	B	B	B	B	B
	4700pF (472)	B	B	B	B	B	B	B	B	B	B	B
	5600pF (562)	B	B	B	B	B	B	B	B	B	B	B
	6800pF (682)	B	B	B	B	B	B	B	B	B	B	B
	8200pF (822)	B	B	B	B	B	B	B	B	B	B	B
	0.01uF (103)	B	B	B	B	B	B	B	B	B	B	B
	0.012uF (123)	B	B	B	B	B	B	B	B	B	B	
	0.015uF (153)	B	B	B	B	B	B	B	B	B	B	
	0.018uF (183)	B	B	B	B	B	B	B	B	B	B	
	0.022uF (223)	B	B	B	B	B	B	B	B	B	B	
	0.027uF (273)	B	B			B	B	B	B	B	B	
	0.033uF (333)	B	B			B	B	B	B	B	B	

Newark.com/multicomp-pro
Farnell.com/multicomp-pro
sg.element14.com/b/multicomp-pro

multicompPRO

Multilayer Ceramic Capacitor

Radial-Leaded Type Capacitor

multicompPRO

Dielectric		X7R										
Size		0805				1206						
Voltage (VDC)		50	100	200	250	50	100	200	250	500	630	1000
Capacitance	0.039uF (393)	B	B			B	B	B	B			
	0.047uF (473)	B	B			B	B	B	B			
	0.056uF (563)	B	B			B	B	B	B			
	0.068uF (683)	B	B			B	B	B	B			
	0.082uF (823)	B	B			B	B	B	B			
	0.1uF (104)	B	B			B	B	B	B			
	0.12uF (124)	B				B	B					
	0.15uF (154)	B				B	B					
	0.18uF (184)	B				B	B					
	0.22uF (224)	B				B	B					
	0.27uF (274)	B				B						
	0.33uF (334)	B				B						
	0.39uF (394)	B				B						
	0.47uF (474)	B				B						
	0.56uF (564)					B						
	0.68uF (684)					B						
	0.82uF (824)					B						
	1.0uF (105)					B						

The letter in cell is expressed the symbol of product terminations. B: (Cu/Ni/Sn)
RD21 type can use Mlcc size 0805 and 1206, but RD20 type can only use Mlcc size 0805.

Dielectric		Y5V													
Size		0805							1206						
Voltage (VDC)		10	16	25	50	100	200	250	10	16	25	50	100	200	250
Capacitance	0.01uF (103)	B	B	B	B	B	B	B	B	B	B	B	B	B	B
	0.015uF (153)	B	B	B	B	B	B	B	B	B	B	B	B	B	B
	0.022uF (223)	B	B	B	B	B	B	B	B	B	B	B	B	B	B
	0.033uF (333)	B	B	B	B	B	B	B	B	B	B	B	B	B	B
	0.047uF (473)	B	B	B	B	B	B	B	B	B	B	B	B	B	B
	0.068uF (683)	B	B	B	B	B	B	B	B	B	B	B	B	B	B
	0.1uF (104)	B	B	B	B	B			B	B	B	B	B	B	B
	0.15uF (154)	B	B	B	B				B	B	B	B	B	B	B
	0.22uF (224)	B	B	B	B				B	B	B	B	B		
	0.33uF (334)	B	B	B	B				B	B	B	B			
	0.47uF (474)	B	B	B	B				B	B	B	B			
	0.68uF (684)	B	B	B	B				B	B	B	B			
	1.0uF (105)	B	B	B	B				B	B	B	B			
	1.5uF (155)	B	B						B	B	B				
	2.2uF (225)	B	B	B					B	B	B	B			
	3.3uF (335)	B	B						B	B	B				
	4.7uF (475)	B	B	B					B	B	B				
	6.8uF (685)	B							B	B					
	10uF (106)	B							B	B	B				
	22uF (226)								B						

Newark.com/multicomp-pro
Farnell.com/multicomp-pro
sg.element14.com/b/multicomp-pro

multicompPRO

Multilayer Ceramic Capacitor


Radial-Leaded Type Capacitor

multicompPRO

The letter in cell is expressed the symbol of product terminations. B: (Cu/Ni/Sn)
RD21 type can use Mlcc size 0805 and 1206, but RD20 type can only use Mlcc size 0805.

Marking:

Rated voltage (V DC)	10	16	25	50	100	200	250	500	630	1000	2000	3000
Marking	$\overline{104}$	$10\overline{4}$	$\overline{\overline{104}}$	104	<u>104</u>	<u>104</u>	104	<u>104</u>	$\overline{104}$	$\widetilde{104}$	$\overset{104}{\sim}$	$\overset{\wedge}{104}$



- (1) Rated capacitance: Identified by 3-figure code.
(2) Halogen and Pb free: There is a "." beside the capacitance code when the coating resin is Halogen and Pb free Epoxy.

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro
Farnell.com/multicomp-pro
sg.element14.com/b/multicomp-pro

multicompPRO