

## M23660 Gas Tap Lubricant

**Effective lubrication and sealing of gas taps and taper plug cocks.**

**Developed in conjunction with cooker and tap manufacturers for the lubrication of taper gas taps operating with 1<sup>st</sup>, 2<sup>nd</sup> and 3<sup>rd</sup> family gases. Its use enables compliance with British Standard 5494, 1978, service No.6 (30,000 operations).**

**ROCOL M23660 Gas Tap Lubricant has been used by British Gas PLC for over 30 years, and demonstrated to be acceptable for continuous use at 120°C in a wide range of gas equipment applications including gas taps, cocks etc...**

### Features

- Suitable for high temperature applications up to 120°C
- Good lubricating and sealing properties
- Excellent anti-wear and anti-seize properties

### Directions for Use

- ROCOL M23660 Gas Tap Lubricant can be applied manually or by a suitable applicator capable of handling an NLGI No.2 grease.
- For best results equipment should be cleaned or purged of previous lubricant prior to application of ROCOL M23660.

T +44 (0) 113 232 2600  
F +44 (0) 113 232 2740  
E [customer-service@rocol.com](mailto:customer-service@rocol.com)  
[www.rocol.com](http://www.rocol.com)

ROCOL House, Swinton, Leeds LS26 8BS

Registered Company No. 339489 - VAT No. 794 0547 85  
Registered Office: 200-202, Farnley Road, Farnley, Leeds LS28 3JF

ROCOL A division of **ITW** Ltd



BSI  
2014 30 3001  
Lubricants - Greases



BSI  
2014 12 1401  
Lubricants - Greases



BSI  
2014 13 01  
Lubricants - Greases



INVESTOR IN PEOPLE

The information in this publication is based on our experience and reports from customers. There are many factors outside our control or knowledge which affect the use and performance of our products, for which reason it is given without responsibility.

# Technical Data



Performance you can trust

## M23660 Gas Tap Lubricant

<b>Appearance</b>	Smooth, blue-black grease
<b>NLGI No. (IP 50)(ASTM D217)</b>	NLGI No. 1/2
<b>Base type</b>	Severely refined mineral oil
<b>Thickener</b>	Organically modified clay
<b>Solids</b>	Molybdenum disulphide
<b>Operating temperature of applied film</b>	-20 <sup>0</sup> C to +120 <sup>0</sup> C
<b>Drop point (IP132)</b>	Non-melting
<b>Storage</b>	Storage temperature should be controlled to between 1 and 40 °C.
<b>Pack sizes</b>	50g

T +44 (0) 113 232 2600  
F +44 (0) 113 232 2740  
E [customer-service@rocol.com](mailto:customer-service@rocol.com)  
[www.rocol.com](http://www.rocol.com)

ROCOL House, Sw. Jington, Leeds LS26 8BS

Registered Company No. 389589 VAT No. 762 0547 89  
Registered Office: Admin House, 51, Great St. Road, Wetherby, West Yorkshire LS23 7BQ

ROCOL A division of **ITW** Ltd



2024 ISO 9001  
CERTIFICATE NO. 1411244



2024 ISO 14001  
CERTIFICATE NO. 1411244



2024 ISO 45001  
CERTIFICATE NO. 1411244



INVESTOR IN THE PEOPLE

The information in this publication is based on our experience and reports from customers. There are many factors outside our control or knowledge which affect the use and performance of our products, for which reason it is given without responsibility.