

TECHNICAL DATA

Fluke i800 AC Current Clamp Probe



Key features

- Measures AC current from 100 mA to 800 A rms
- 30 Hz to 10 kHz frequency range
- CAT III 600 V rating
- Accepts up to 54 mm (2.1 in) diameter conductor size
- 1000:1 conversion factor for easy calculation
- Rugged positive action design

Product overview: Fluke i800 AC Current Clamp Probe

The Fluke i800 AC Current Clamp is designed for use with multimeters, recorders, safety testers, etc., for accurate non-intrusive AC current measurement. It extends the current measuring capability of a digital multimeter to 800 A AC. It is compatible with digital multimeters that accept shrouded 4 mm (0.16) banana plugs and has an AC milliamp range.

Specifications: Fluke i800 AC Current Clamp Probe

Ordering information



Fluke-i800

AC Current Clamp Probe

Fluke. *Keeping your world up and running.®*

Fluke Corporation
PO Box 9090, Everett, WA 98206 U.S.A.

For more information call:
In the U.S.A. (800) 443-5853
In Canada (800) 36-FLUKE
From other countries +1 (425) 446-5500
www.fluke.com

©2025 Fluke Corporation.
Specifications subject to change without notice.
08/2025

**Modification of this document is not permitted
without written permission from Fluke
Corporation.**