











- Higher Capacitance, Low ESR, High ripple current.
- Load life of 2000 hours at 105°C.
- SMD type: Lead free reflow soldering condition at 260°C peak correspondence.
- Adapted to the RoHS directive (2002/95/EC).






■Specifications

| Item | Performance Characteristics | | | | | |
|---|---|--|--|--|--|--|
| Category Temperature Range | −55 to +105°C | | | | | |
| Rated Voltage Range | 2.5 to 16V | | | | | |
| Rated Capacitance Range | 47 to 3300μF | | | | | |
| Capacitance Tolerance | ±20% at 120Hz, 20°C | | | | | |
| tan δ | Not more than value of Standard ratings at 120Hz, 20°C | | | | | |
| ESR (* 1) | Not more than value of Standard ratings at 100kHz, 20°C | | | | | |
| Leakage Current (* 2) | Not more than value of Standard ratings. After 2 minutes' application of rated voltage. 20°C | | | | | |
| Characteristics of Temperature Impedance Ratio | Z+105°C / Z+20°C ≤ 1.25 (100kHz) Z-55°C / Z+20°C ≤ 1.25 | | | | | |
| Endurance | After 2000 hours' application of rated voltage at 105°C, capacitors meet the specified value for life characteristics listed at right. | Capacitance change tan δ ESR (* 1) Leakage current (* 2) | Within ± 20% of initial value (* 3) 150% or less of the initial specified value 150% or less of the initial specified value Initial specified value or less | | | |
| Damp Heat | After 1000 hours' application of rated voltage at 60°C 90%RH, capacitors meet the specified value for life characteristics listed at right. | Capacitance change tan δ ESR (** 1) Leakage current (** 2) | Within ± 20% of initial value (* 3) 150% or less of the initial specified value 150% or less of the initial specified value Initial specified value or less | | | |
| Resistance to Soldering Heat | To comply with recommended conditions for reflow soldering. Pre-heating shall be done at 150 to 200°C and for 60 to 180 sec. The duration for over +230°C temperature at capacitor surface shall not exceed 60 seconds. In the case of peak temp, less than 250°C, reflow soldering shall be within two times. In the case of peak temp, less than 260°C, reflow soldering shall be once. Measurement for solder temperature profile shall be made at the capacitor top and the terminal. | Capacitance change tan δ ESR (* 1) Leakage current (* 2) | Within ± 10% of initial value (* 3) 130% or less of the initial specified value 130% or less of the initial specified value Initial specified value or less | | | |
| Marking | Navy blue print on the case top | | | | | |


- * 1 ESR measurements should be made at a point on the terminal nearest where the terminals protrude through the plastic platform.
- * 2 Conditioning: If there is doubt about the measured result, measurement should be made again after the rated voltage is applied for 120 minutes at the temperature of 105°C.
- * 3 Initial value: The value before test of examination of resistance to soldering.

■ Dimensions



| | | | | | | (mm) |
|------|------------|------------|------------|------------|----------------------|-------------|
| Size | φ5×6L | φ6.3×6L | φ8×7L | φ10 × 8L | $\phi 10 \times 10L$ | φ10 × 12.7L |
| φD | 5.0 | 6.3 | 8.0 | 10.0 | 10.0 | 10.0 |
| L | 5.9 | 5.9 | 6.9 | 7.9 | 9.9 | 12.6 |
| Α | 6.0 | 7.3 | 9.0 | 11.0 | 11.0 | 11.0 |
| В | 5.3 | 6.6 | 8.3 | 10.3 | 10.3 | 10.3 |
| С | 5.3 | 6.6 | 8.3 | 10.3 | 10.3 | 10.3 |
| Е | 1.4 | 2.1 | 3.2 | 4.6 | 4.6 | 4.6 |
| Н | 0.5 to 0.8 | 0.5 to 0.8 | 0.8 to 1.1 | 0.8 to 1.1 | 0.8 to 1.1 | 0.8 to 1.1 |

Type numbering system (Example: 6.3V 470µF)



Voltage

| romago | | | | | |
|--------|-----|---|-----|----|----|
| V | 2.5 | 4 | 6.3 | 10 | 16 |
| Code | е | g | j | Α | С |



■Standard ratings

| Rated Voltage (V)(code) | Surge Voltage (V) | Rated Capacitance (μF) | Case Size φD × L (mm) | tan δ | Leakage Current (μΑ) | ESR (mΩ) (at 100kHz 20°C) | Rated ripple (mArms) | Part Number |
|----------------------------|----------------------|------------------------|--------------------------|-------|----------------------|------------------------------|-------------------------|----------------|
| 2.5 (0E) | 2.8 | 220 | 5 × 6 | 0.12 | 110 | 30 | 2100 | PCG0E221MCL1GS |
| | | 470 | 6.3 × 6 | 0.12 | 235 | 20 | 2900 | PCG0E471MCL1GS |
| | | 560 | 6.3 × 6 | 0.12 | 280 | 20 | 3000 | PCG0E561MCL1GS |
| | | 820 | 8×7 | 0.12 | 410 | 20 | 3300 | PCG0E821MCL1GS |
| | | 1500 | 10 × 8 | 0.12 | 750 | 17 | 4100 | PCG0E152MCL1GS |
| | | 2700 | 10 × 10 | 0.12 | 1350 | 12 | 4700 | PCG0E272MCL1GS |
| | | 3300 | 10×12.7 | 0.12 | 1650 | 10 | 5500 | PCG0E332MCL1GS |
| | | 180 | 5×6 | 0.12 | 144 | 32 | 1900 | PCG0G181MCL1GS |
| | | 390 | 6.3×6 | 0.12 | 312 | 22 | 2700 | PCG0G391MCL1GS |
| 4 | 4.6 | 680 | 8 × 7 | 0.12 | 544 | 21 | 3200 | PCG0G681MCL1GS |
| (0G) | 4.0 | 1200 | 10 × 8 | 0.12 | 960 | 17 | 4000 | PCG0G122MCL1GS |
| | | 2200 | 10 × 10 | 0.12 | 1760 | 13 | 4600 | PCG0G222MCL1GS |
| | | 2700 | 10 × 12.7 | 0.12 | 2160 | 11 | 5300 | PCG0G272MCL1GS |
| | 7.2 | 150 | 5 × 6 | 0.12 | 189 | 33 | 1800 | PCG0J151MCL1GS |
| | | 270 | 6.3×6 | 0.12 | 340 | 23 | 2600 | PCG0J271MCL1GS |
| | | 330 | 6.3×6 | 0.12 | 416 | 23 | 2700 | PCG0J331MCL1GS |
| 6.3 (0J) | | 470 | 8 × 7 | 0.12 | 592 | 22 | 3100 | PCG0J471MCL1GS |
| , , | | 1000 | 10 × 8 | 0.12 | 1260 | 18 | 3800 | PCG0J102MCL1GS |
| | | 1800 | 10 × 10 | 0.12 | 2268 | 14 | 4400 | PCG0J182MCL1GS |
| | | 2200 | 10×12.7 | 0.12 | 2772 | 12 | 5000 | PCG0J222MCL1GS |
| | 11.5 | 82 | 5 × 6 | 0.12 | 164 | 35 | 1700 | PCG1A820MCL1GS |
| | | 150 | 6.3 × 6 | 0.12 | 300 | 25 | 2500 | PCG1A151MCL1GS |
| 10 | | 330 | 8 × 7 | 0.12 | 660 | 23 | 3100 | PCG1A331MCL1GS |
| (1A) | | 560 | 10 × 8 | 0.12 | 1120 | 20 | 3600 | PCG1A561MCL1GS |
| | | 820 | 10 × 10 | 0.12 | 1640 | 15 | 4300 | PCG1A821MCL1GS |
| | | 1000 | 10×12.7 | 0.12 | 2000 | 13 | 4800 | PCG1A102MCL1GS |
| | 18.4 | 47 | 5×6 | 0.12 | 150 | 40 | 1500 | PCG1C470MCL1GS |
| 16 (1C) | | 82 | 6.3×6 | 0.12 | 262 | 30 | 2300 | PCG1C820MCL1GS |
| | | 150 | 8×7 | 0.12 | 480 | 28 | 2800 | PCG1C151MCL1GS |
| | | 270 | 10×8 | 0.12 | 864 | 25 | 3300 | PCG1C271MCL1GS |
| | | 470 | 10×10 | 0.12 | 1504 | 20 | 3700 | PCG1C471MCL1GS |
| | | 680 | 10 × 12.7 | 0.12 | 2176 | 18 | 4100 | PCG1C681MCL1GS |

Rated Ripple (mArms) at 105°C 100kHz

[•] Taping specifications are given in page 23.

[•] Recommended land size, soldering by reflow are given in page 18, 19.

• Please refer to page 3 for the minimum order quantity.