

**RoHS
Compliant**



Specifications

Applications	Product	: Telecom and wide variety of electronic equipment
Features	Operation	: Low hold current, Solid state, Radial leaded product ideal for up to 90V
Current Maximum		: 100mA to 550mA
Voltage	Temperature	: up to 90V
Range		: -40°C to +85°C
Approval		: UL Approved

Electrical Characteristics (23°C)

Hold Current	Trip Current	Max. Time to trip	Max. Current	Rated Voltage	Typical Power	Resistance		Part Number
						R Min.	R1 Max.	
I_H , A	I_T , A	at $5x I_H$	$I_{Max.}$, A	$V_{Max.}$, V DC	P_d , W	ohms	ohms	
0.1	0.2	4	40	72/90	0.38	2.5	7.5	MC36184
0.15	0.35	10			0.7	2.4	7	MC36185
0.17	0.34	3			0.48	2	8	MC36186
0.55	1.2	10			1.5	0.4	1.5	MC36193

I_H	= Hold current-maximum current at which the device will not trip at 23°C still air
I_T	= Trip current-minimum current at which the device will always trip at 23°C still air
V_{MAX}	= Maximum voltage device can withstand without damage at its rated current
I_{MAX}	= Maximum fault current device can withstand without damage at rated voltage (V maximum)
P_d	= Typical power dissipated from device when in the tripped state in 23°C still air environment
R_{MIN}	= Minimum device resistance at 23°C
$R1_{MAX}$	= Maximum device resistance at 23°C 1 hour after tripping


Physical specifications

Lead Material	: Tin plated copper, 24AWG
Soldering Characteristics	: MIL-STD-202, Method 208E
Insulating Coating	: Flame retardant epoxy

Resettable Fuse

multicompPRO

Production Dimensions




A	B	C	D	E	F	Part Number
Max.	Max.	Typical	Min.	Max.	Typical	
7.4	12.7	5.1	7.6	3.1	1.1	MC36184
						MC36185
						MC36186
9.7	14					MC36193

Lead Size : 24 AWG
Ø0.51mm Diameter


Dimensions : Millimetres

Thermal Derating Curve

Thermal Derating Curve-FRX 90V Series



Typical Time-To-Trip at 23°C



Part Number Table

Description	Part Number
Radial Leaded PTC Resettable Fuse	MC36184
	MC36185
	MC36186
	MC36193

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro
Farnell.com/multicomp-pro
sg.element14.com/b/multicomp-pro

multicompPRO