



NOTES: FINISH (PLATING THICKNESS IN MICRO-INCHES)  
 1. BRASS PER QQ-B-626  
 2. BRASS PER QQ-B-613  
 3. NICKEL PL. 100 MIN. THICK OVER COPPER STRIKE  
 4. NICKEL PL. 200 MIN. THICK OVER COPPER STRIKE  
 5. GOLD PL. 3 MIN. THICK OVER NICKEL PL. 100 MIN. THICK OVER COPPER STRIKE

11	NUT	NOTE 1	NOTE 3	1	B5291-14
10	FERRULE	COPPER	NOTE 3	1	FR-648/533X127C
9	WASHER	NOTE 2	NOTE 3	1	WS-128/9X08
8	SPRING	SK5	NOTE 4	2	B50000-6
7	RETAINER RING	NOTE 1	NOTE 3	1	B50000-5
6	GASKET	RUBBER	RED	1	GS-115/8X15
5	CONTACT PIN	NOTE 1	NOTE 5	1	B5091-6-50
4	INSULATOR	DELTRIN	NATURAL	1	B50002-3-50
3	BARREL	NOTE 1	NOTE 3	1	B5091-3-46/31
2	HOUSING	NOTE 1	NOTE 3	1	B5091-2
1	SHELL	NOTE 1	NOTE 3	1	B50000-1-B
NO.	DESCRIPTION	MATERIAL	FINISH	Q'TY	DRAWING NO.

DIMENSIONS ARE IN MILLIMETERS			PART NO. B1112A1-ND3G-1-50	
UNLESS OTHERWISE SPECIFIED TOLERANCES 0.5-6 = ±0.2 6-30 = ±0.4 30-120 = ±0.6 120-315 = ±1 315-1000 = ±1.6 1000-2000 = ±2.4			APPROVED	DATE 10-11-01'
			CHECKED	DATE 10-11-01'
			DRAWN	DATE 10-11-01'
			FILE NO.	
SCALE	3/1	ISSUE	A	

1. CRIMPED FERRULE  
 HEX CRIMP SIZE .213"  
 2. CONTACT PIN TO SOLDER

# Amphenol

TITLE BNC R/A CRIMP PLUG  
 (FOR RG-58/U,58C/U)

DRAWING NO.  
 KJ-B1112A1-ND3G-58U-50

ITEM NO.