

Vishay Semiconductors

Small Signal Switching Diodes, High Voltage

Features

- Silicon Epitaxial Planar Diodes
- Lead (Pb)-free component
- Component in accordance to RoHS 2002/95/EC and WEEE 2002/96/EC



Applications

· General purposes

Mechanical Data

Case: MiniMELF Glass case (SOD80)

Weight: approx. 31 mg
Cathode Band Color: Black
Packaging Codes/Options:

GS18/10 k per 13" reel (8 mm tape), 10 k/box GS08/2.5 k per 7" reel (8 mm tape), 12.5 k/box

Parts Table

Part	Type differentiation	Ordering code	Type Marking	Remarks	
BAV100	V _{RRM} = 60 V	BAV100-GS18 or BAV100-GS08	-	Tape and Reel	
BAV101	V _{RRM} = 120 V	BAV101-GS18 or BAV101-GS08	-	Tape and Reel	
BAV102	V _{RRM} = 200 V	BAV102-GS18 or BAV102-GS08	-	Tape and Reel	
BAV103	V _{RRM} = 250 V	BAV103-GS18 or BAV103-GS08	-	Tape and Reel	

Absolute Maximum Ratings

T_{amb} = 25 °C, unless otherwise specified

Parameter	Test condition	Part	Symbol	Value	Unit
Repetitive peak reverse voltage		BAV100	V _{RRM}	60	V
		BAV101	V _{RRM}	120	V
		BAV102	V _{RRM}	200	V
		BAV103	V _{RRM}	250	V
Reverse voltage		BAV100	V _R	50	V
		BAV101	V _R	100	V
		BAV102	V _R	150	V
		BAV103	V _R	200	V
Peak forward surge current	t _p = 1 s		I _{FSM}	1	Α
Repetitive peak forward current			I _{FRM}	625	mA
Forward continuous current			I _F	250	mA
Power dissipation			P _{tot}	500	mW

Document Number 85542 www.vishay.com

BAV100/101/102/103

Vishay Semiconductors



Thermal Characteristics

T_{amb} = 25 °C, unless otherwise specified

Parameter	Test condition Symbol		Value	Unit	
Junction lead		R _{thJL}	350	K/W	
Thermal resistance junction to ambient air	on PC board 50 mm x 50 mm x 1.6 mm	R _{thJA}	500	K/W	
Junction temperature		Tj	175	°C	
Storage temperature range		T _{stg}	- 65 to + 175	°C	

Electrical Characteristics

 T_{amb} = 25 °C, unless otherwise specified

Parameter	Test condition	Part	Symbol	Min	Тур.	Max	Unit
Forward voltage	I _F = 100 mA		V _F			1000	mV
Reverse current	V _R = 50 V	BAV100	I _R			100	nA
	V _R = 100 V	BAV101	I _R			100	nA
	V _R = 150 V	BAV102	I _R			100	nA
	V _R = 200 V	BAV103	I _R			100	nA
	$T_j = 100 ^{\circ}\text{C}, V_R = 50 ^{\circ}\text{V}$	BAV100	I _R			15	μΑ
	T _j = 100 °C, V _R = 100 V	BAV101	I _R			15	μΑ
	T _j = 100 °C, V _R = 150 V	BAV102	I _R			15	μΑ
	T _j = 100 °C, V _R = 200 V	BAV103	I _R			15	μΑ
Breakdown voltage	$I_R = 100 \ \mu\text{A}, \ t_p/T = 0.01, \ t_p = 0.3 \ \text{ms}$	BAV100	V _(BR)	60			V
	I_R =100 μ A, t_p /T = 0.01, t_p = 0.3 ms	BAV101	V _(BR)	120			V
	$I_R = 100 \mu A, t_p/T = 0.01,$ $t_p = 0.3 \text{ ms}$	BAV102	V _(BR)	200			V
		BAV103	V _(BR)	250			V
Diode capacitance	V _R = 0, f = 1 MHz		C _D		1.5		pF
Differential forward resistance	I _F = 10 mA		r _f		5		Ω
Reverse recovery time	$I_F = I_R = 30 \text{ mA}, i_R = 3 \text{ mA},$ $R_L = 100 \Omega$		t _{rr}			50	ns

Typical Characteristics

T_{amb} = 25 °C, unless otherwise specified




Figure 1. Reverse Current vs. Junction Temperature




Figure 2. Forward Current vs. Forward Voltage

Vishay Semiconductors






Figure 3. Differential Forward Resistance vs. Forward Current

Package Dimensions in millimeters (inches): SOD80



★ The gap between plug and glass can be either on cathode or anode side



Rev. 8 - Date: 07.June.2006 Document no.:6.560-5005.01-4 96 12070

BAV100/101/102/103

Vishay Semiconductors



Ozone Depleting Substances Policy Statement

It is the policy of Vishay Semiconductor GmbH to

- 1. Meet all present and future national and international statutory requirements.
- 2. Regularly and continuously improve the performance of our products, processes, distribution and operating systems with respect to their impact on the health and safety of our employees and the public, as well as their impact on the environment.

It is particular concern to control or eliminate releases of those substances into the atmosphere which are known as ozone depleting substances (ODSs).

The Montreal Protocol (1987) and its London Amendments (1990) intend to severely restrict the use of ODSs and forbid their use within the next ten years. Various national and international initiatives are pressing for an earlier ban on these substances.

Vishay Semiconductor GmbH has been able to use its policy of continuous improvements to eliminate the use of ODSs listed in the following documents.

- 1. Annex A, B and list of transitional substances of the Montreal Protocol and the London Amendments respectively
- 2. Class I and II ozone depleting substances in the Clean Air Act Amendments of 1990 by the Environmental Protection Agency (EPA) in the USA
- 3. Council Decision 88/540/EEC and 91/690/EEC Annex A, B and C (transitional substances) respectively.

Vishay Semiconductor GmbH can certify that our semiconductors are not manufactured with ozone depleting substances and do not contain such substances.

> We reserve the right to make changes to improve technical design and may do so without further notice.

Parameters can vary in different applications. All operating parameters must be validated for each customer application by the customer. Should the buyer use Vishay Semiconductors products for any unintended or unauthorized application, the buyer shall indemnify Vishay Semiconductors against all claims, costs, damages, and expenses, arising out of, directly or indirectly, any claim of personal damage, injury or death associated with such unintended or unauthorized use.

Vishay Semiconductor GmbH, P.O.B. 3535, D-74025 Heilbronn, Germany

www.vishay.com Document Number 85542 Rev. 1.6, 13-Feb-07

Legal Disclaimer Notice



Vishay

Notice

Specifications of the products displayed herein are subject to change without notice. Vishay Intertechnology, Inc., or anyone on its behalf, assumes no responsibility or liability for any errors or inaccuracies.

Information contained herein is intended to provide a product description only. No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document. Except as provided in Vishay's terms and conditions of sale for such products, Vishay assumes no liability whatsoever, and disclaims any express or implied warranty, relating to sale and/or use of Vishay products including liability or warranties relating to fitness for a particular purpose, merchantability, or infringement of any patent, copyright, or other intellectual property right.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications. Customers using or selling these products for use in such applications do so at their own risk and agree to fully indemnify Vishay for any damages resulting from such improper use or sale.

www.vishay.com Revision: 08-Apr-05