

6000 SP Splashproof Rocker Switches 16A 250Vac



European 16(4)A 250Vac T125, 10A 400Vac T125




UL CSA 20A+ 277Vac, 250Vac 1 1/2hp, 125Vac 1hp
UL 100°C, file E45221, CSA file LR10990



Inrush 150A* to EN61058-1 (On - Off only)
20A 28Vdc


+ * applies to non-momentary types

6000 Switches feature "Arcshield" to hide visible switching arc
3mm contact gap with Positive Break switching
Call factory for IP details
Technical data on pages 4 & 5 (switches), 66 (indicators)
Patent app.



TERMINAL	FUNCTION	ROCKER
<p>C</p> <p>6.3 x 0.8</p>	<p>Approvals & ratings vary with function On Off Switches - ON when pressed over terminal 3</p>	<p>A Softline Matt</p>
	<p>6000 ON - OFF</p>	
	<p>6001 ON - OFF (momentary ON)</p>	<p>A Softline Matt</p> <p>Lit</p>
	<p>6002 ON - OFF (momentary OFF)</p>	
	<p>6003 ON - OFF Lit</p>	<p>P Lit window Matt</p>
	<p>6008 ON - OFF Lit (Unswitched neutral)</p>	
	<p>6009 ON - OFF (momentary ON) Lit (Unswitched neutral)</p>	
	<p>6010 ON - ON</p>	<p>A Lens Matt (6030 indicator only)</p>
	<p>6011 ON - ON (momentary 1 side)</p>	
	<p>6030 Indicator</p>	
<p>H</p> <p>4.8 x 0.8</p>		
<p>S</p> <p>Screw & Clamp N/A for assemblies with 3 terminals</p>		
<p>For twin switches and double pole circuits see pages 24 & 25</p>		

For IP65 see "options" below



Integral Splashproofing

Current carrying parts are protected from moisture. Droplets which may enter the switch are channelled out through ports in the switch body



C6000AL ---



C6000AL ---



C6010AL ---



C6003AL ---



C6003PL ---




C6030AL ---



BODY

Panel cut-out ** Flange
Cut-outs must be punched in the direction of insertion

L



OPTIONS


Finish Matt is standard

Colour Call factory for custom colours
A full range is available for large orders

Legend printing Select from the examples
or call factory for custom legends

Lamp voltage Call factory for details

Protective cover (designed to IP65)
The 6000 series is a water thru design.
For a higher level of sealing, a snap on cover
is available (add G after body code). This
reduces panel thickness by 1mm.




Panel sealing washer W46 is available but
reduces panel thickness by a further 0.8mm.
Covers are not suitable for momentary types.

Mounting orientation may affect splashproofing

For all options call the factory

DIMENSIONS (mm)




Panel thickness
L 0.75 to 2.5mm

** For cut-out details
on momentary switches
call the factory

Examples of printing



EN1224



EN1223