
Data Sheet


# Chip Common Mode Choke Coils Wire Wound Type

## DLW21H Series (0805 Size)

Dimension



### Equivalent Circuit



### ■ Rated Value (□: packaging code)

#### Common Mode Impedance Operating Part Number Rated Current Rated Voltage Insulation Resistance (min.) Withstand Voltage DC Resistance Number of Circuit (at 100MHz/20°C) Temperature Range DLW21HN670SQ2 67ohm±25% 330mA 50Vdc 10M ohm 125Vdc 0.35ohmmax. -40°C to 85°C 1 DLW21HN900SQ2 90ohm±25% 330mA 50Vdc 10M ohm 125Vdc 0.35ohmmax. -40°C to 85°C 1 DLW21HN121SQ2 120ohm±25% 280mA 50Vdc 10M ohm 125Vdc 0.45ohmmax. -40°C to 85°C 1 DLW21HN181SQ2 180ohm±25% 250mA 50Vdc 10M ohm 125Vdc 0.50ohmmax. -40°C to 85°C 1

#### ■ ①Caution/Notice

#### Notice

Solderability of Tin plating termination chip might be deteriorated when low temperature soldering profile where peak solder temperature is below the Tin melting point is used. Please confirm the solderability of Tin plating termination chip before use.

• This data sheet is applied for CHIP COMMON MODE CHOKE COIL used for General Electronics equipment for your design.


#### A Note:

1. This datasheet is downloaded from the website of Murata Manufacturing co., ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2. This datasheet has only typical specifications because there is no space for detailed specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.



#### ■ Impedance-Frequency Characteristics



#### Packaging

Code	Packaging	Minimum Quantity
L	180mm Embossed Tape	3000
В	Bulk(Bag)	500