


PAC

PTFE TYPE A Cable (26 AWG) Specification

7/0.15 SPC

Part No.:PTFE26A100

Cross Section	Performance														
	<p>Electrical Characteristics:</p> <p>Spark Test: AC-1.5KV Dielectric Strength : AC-300V/60sec Conductor Resistance: 180 OHM/KM At 20°C Insulation Resistance: DC-500V 10 Mohm/KM At 20°C</p>														
<p>Packing</p> <p>100M/reel</p>															
<p>Description</p> <table border="0"> <tr> <td>Rated Temperature (°C)</td> <td>-75~190</td> </tr> <tr> <td>Rated Voltage(V)</td> <td>300</td> </tr> <tr> <td>Product Standard Certification</td> <td></td> </tr> <tr> <td>Flammability Test</td> <td>FT1</td> </tr> </table>	Rated Temperature (°C)	-75~190	Rated Voltage(V)	300	Product Standard Certification		Flammability Test	FT1							
Rated Temperature (°C)	-75~190														
Rated Voltage(V)	300														
Product Standard Certification															
Flammability Test	FT1														
<p>Construction</p> <table border="0"> <tr> <td>Conductor</td> <td>Silver plated copper</td> </tr> <tr> <td>AWG</td> <td>26</td> </tr> <tr> <td>Conductor Dia. (±0.005mm)</td> <td>7/0.15</td> </tr> <tr> <td>Jacket</td> <td>PTFE</td> </tr> <tr> <td>Average Thickness(mm)</td> <td>0.14</td> </tr> <tr> <td>Outer Dia.(±0.05mm)</td> <td>0.75</td> </tr> </table>	Conductor	Silver plated copper	AWG	26	Conductor Dia. (±0.005mm)	7/0.15	Jacket	PTFE	Average Thickness(mm)	0.14	Outer Dia.(±0.05mm)	0.75			
Conductor	Silver plated copper														
AWG	26														
Conductor Dia. (±0.005mm)	7/0.15														
Jacket	PTFE														
Average Thickness(mm)	0.14														
Outer Dia.(±0.05mm)	0.75														
<p>Color</p> <p>As request</p>	<p>Mechanical Characteristics:</p> <table border="0"> <tr> <td>Test Object</td> <td>Jacket</td> </tr> <tr> <td>Test Material</td> <td>PTFE</td> </tr> <tr> <td>Before Tensile Strength (kgf/mm²)</td> <td>>=0.5</td> </tr> <tr> <td>Aging Elongation (%)</td> <td>>=100</td> </tr> <tr> <td>Aging Condition ()</td> <td></td> </tr> <tr> <td>After Tensile Strength (%)</td> <td>>=60</td> </tr> <tr> <td>Aging Elongation (%)</td> <td>>=60</td> </tr> </table>	Test Object	Jacket	Test Material	PTFE	Before Tensile Strength (kgf/mm ²)	>=0.5	Aging Elongation (%)	>=100	Aging Condition ()		After Tensile Strength (%)	>=60	Aging Elongation (%)	>=60
Test Object	Jacket														
Test Material	PTFE														
Before Tensile Strength (kgf/mm ²)	>=0.5														
Aging Elongation (%)	>=100														
Aging Condition ()															
After Tensile Strength (%)	>=60														
Aging Elongation (%)	>=60														
<p>Marking</p> <p>No</p>															
<p>Revision History</p>															