

GLOSS PAINTS

Product Code: PWB, PBB, PJB, PNB, PRB, PVB

PRODUCT DESCRIPTION

A range of quick drying, high quality, universal spray paints based on alkyd resins. They exhibit excellent coverage and hardness characteristics and are ideally suited for use in manufacturing, repair and for home and workshop use. These paints use the International RAL classification system. Available in white, blue, yellow, black, red and green.

CHARACTERISTICS

- * 100% Ozone Friendly
- * Excellent coverage & flow
- * Fast drying with high opacity
- * Excellent hardness
- * Very good resistance to water and other and chemicals
- * Excellent adhesion to bare metal

PREPARATION & APPLICATION

- * Ensure that surface is dry, smooth and free from dust and grease.
- * To test, paint a sample panel in advance. Check synthetic and plastic substrates for adhesion and compatibility. For plastics such as PP and EPDM, a primer coat should be applied first.
- * Shake the spray-can well for at least 2 minutes and at intervals during use.
- * Spray, (holding the aerosol vertically), at a distance of 25-30 cm from the object to be painted. Best results are obtained by applying several thin coats rather than one single thick coat. Wait a few minutes, with a maximum of 30 minutes, between the application of each layer.
- * After use, clear the valve by spraying with the can inverted
- * If repainting is necessary, this should be after 24 hours. Drying of the synthetic paint depends on the thickness of the layer and the ambient temperature.

TECHNICAL
DATA
SHEET



**Copyright
Electrolube
2003**

All information is given in good faith but without warranty. Properties are given as a guide only and should not be taken as a specification. Electrolube cannot be held responsible for the performance of its products within any application determined by the customer, who must satisfy themselves as to the suitability of the product.



GLOSS PAINTS – Page 2

TYPICAL PROPERTIES

Gloss:	Gloss 90 angle of 60°
Satin:	25 angle of 60°
Coverage:	1.0-1.5 m ² (layer 20µ - depends on colour)
Drying time:	15 minutes (surface) 3 hours (touch dry) 24 hours (fully dry)
Maximum Temperature:	110°C

PACKAGING

400 ml net aerosol - White Gloss RAL 9010
400 ml net aerosol - Blue Gloss RAL 5010
400 ml net aerosol - Yellow Gloss RAL1021
400 ml net aerosol - Black Gloss RAL 9005
400 ml net aerosol - Red Gloss RAL 3000
400 ml net aerosol - Green Gloss RAL 6002

ORDER CODE

PWB400
PBB400
PJB400
PNB400
PRB400
PVB400

TECHNICAL
DATA
SHEET



**Copyright
Electrolube
2003**

All information is given in good faith but without warranty. Properties are given as a guide only and should not be taken as a specification. Electrolube cannot be held responsible for the performance of its products within any application determined by the customer, who must satisfy themselves as to the suitability of the product.

