




Automotive Parts > Automotive Connectors > Automotive Headers > PicoMQS, 2-22 POS HDR ASSY, Unsealed



PCB Mount Orientation: **Vertical**

Contact Current Rating (Max): **2 A**

Termination Method to PCB: **Surface Mount**

Sealable: **No**

Centerline (Pitch): **1.27 mm [.05 in]**

[All PicoMQS, 2-22 POS HDR ASSY, Unsealed \(10\)](#)

Features

Product Type Features

Connector Product Type	Connector Assembly
Mixed & Hybrid Header	No
Header Type	Fully Shrouded
Connector Shape	Rectangular
Sealable	No
Connector System	Wire-to-Board
Connector & Contact Terminates To	Printed Circuit Board

Configuration Features

Number of Signal Positions	6
Number of Sections	1
PCB Mount Orientation	Vertical
Number of Positions	6
Number of Rows	1



Electrical Characteristics		
Operating Voltage		12 VDC
Voltage Rating (Max)		12 VDC
Body Features		
Connector & Keying Code		A
Primary Product Color		Black
Contact Features		
Mating Tab Width		.5 mm[.019 in]
Mating Tab Thickness		.4 mm[.015 in]
Contact Type		Tab
Contact Current Rating (Max)		2 A
Contact Mating Area Plating Material		Tin (Sn)
Termination Features		
Termination Method to PCB		Surface Mount
Mechanical Attachment		
Mating Alignment Type		Polarization
Mating Alignment		With
Connector Mounting Type		Board Mount
Housing Features		
Centerline (Pitch)		1.27 mm[.05 in]
Dimensions		
Connector Width		14.6 mm[.57 in]
Connector Length		11 mm[.43 in]
Profile Height from PCB		5.98 mm[.23 in]
Usage Conditions		
Operating Temperature (Max)		130 °C[266 °F]
Operating Temperature Range		-40 – 130 °C[-40 – 266 °F]
Operation/Application		
Solder Process		Reflow Solder Capable
Shielded		No
Circuit Application		Signal



Industry Standards

UL Flammability Rating	UL 94HB
------------------------	---------

Packaging Features

Packaging Quantity	620
Packaging Method	Reel

Other

Interface Number	208-18038
------------------	-----------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	有害物质含量符合标准要求 No Restricted Substance(s) Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JUNE 2025 (250) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer



This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts







Also in the Series

Nano MQS



Customers Also Bought



Documents

Product Drawings

6POS,TAB0.5X0.4,HDR ASSY,90 DEG,COD A

English

CAD Files

3D PDF

3D



Customer View Model

[ENG_CVM_CVM_2339206-6_A.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2339206-6_A.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2339206-6_A.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

[Product Specification](#)

English