TOSHIBA Photocoupler GaAs IRED & Photo-Triac

TLP3082(S)

Office Machine Household Use Equipment Triac Driver Solid State Relay

The TOSHIBA TLP3082(S) consists of a zero voltage crossing turn-on photo-triac optically coupled to a GaAs infrared emitting diode in a six lead plastic DIP package.

Features

• Peak off-state voltage: 800V (Min.)

• Trigger LED current: 10mA (Max.)

• On-state current: 100mA (Max.)

• Isolation voltage: 5000Vrms (Min.)

• UL recognized: UL1577, file No. E67349

Option(D4) type

VDE approved: DIN EN 60747-5-2

Certificate No. 40009302

Maximum operating insulation voltage : 890Vpk Highest permissible over voltage : 8000Vpk

(Note) When an EN60747-5-2 approved type is needed, please designate the "Option(D4)".


Construction mechanical rating

	7.62 mm pitch standard type	10.16 mm pitch TLPXXXF type
Creepage distance	7.0 mm (Min.)	8.0 mm (Min.)
Clearance	7.0 mm (Min.)	8.0 mm (Min.)
Insulation thickness	0.4 mm (Min.)	0.4 mm (Min.)

Unit: mm 3 2 1 7.12 ± 0.25 98 0.25 ± 0.11 1.2 ± 0.15 NW 2.54 ± 0.25 2.54 ± 0.25 JEDEC JEITA TOSHIBA 11-7A9

Weight: 0.39 g (Typ.)

Pin configuration (top view)



1: Anode

2: Cathode

3: N.C.

4:Terminal 1

6:Terminal 2

ZC:Zero-cross Circuit

(Note) When specifying the application type name for certification testing, be sure to use the standard product type name, e.g.,

TLP3082

Absolute Maximum Ratings (Ta = 25°C)

	Characteristic	Symbol	Rating	Unit		
	Forward current		l _F	50	mA	
	Forward current derating (Ta≥53°C)	ΔI _F /°C	-0.7	mA /°C		
LED	Peak forward current (100µs pulse, 100pps)		I _{FP}	1	Α	
	Reverse voltage			5	V	
	Junction temperature	Tj	125	°C		
	Off-state output terminal voltage	V_{DRM}	800	V		
	On-state RMS current	Ta=25°C	I _{T(RMS)}	100	mA	
'n	On-State (Wild Current	Ta=70°C	TI(KIVIS)	50		
Detector	On-state current derating (Ta≥25°C)	ΔI _T / °C	-1.1	mA /°C		
Δ	Peak on-state current (100µs pulse, 120pps)	I _{TP}	2	Α		
	Peak nonrepetitive surge current (Pw=10ms,DC=10%	I _{TSM}	1.2	Α		
	Junction temperature	Tj	115	°C		
Stor	rage temperature range	T _{stg}	-55~125	°C		
Оре	erating temperature range	T _{opr}	-40~100	°C		
Lea	d soldering temperature (10s)	T _{sol}	T _{sol} 260			
Isola	ation voltage (AC,1min. , R.H. ≤60%)	BVS	5000	Vrms		

(Note 1) Device considered a two terminal device: Pins1,2 and 3 shorted together and pin4 and pin6 shorted together.

Recommended Operating Conditions

Characteristic	Symbol	Min.	Тур.	Max.	Unit
Supply voltage	V _{AC}	_	_	240	Vac
Forward current	lF	15	20	25	mA
Peak on-state current	I _{TP}	_	_	1	Α
Operating temperature	T _{opr}	-25	_	85	°C

Recommended operating conditions are given as a design guideline to obtain expected performance of the device. Additionally, each item is an independent guideline respectively. In developing designs using this product, please confirm specified characteristics shown in this document.

2

Electrical Characteristics (Ta = 25°C)


	Characteristic	Symbol	Test Condition	Min.	Тур.	Max.	Unit
	Forward voltage	VF	I _F = 10 mA	1.0	1.15	1.3	V
LED	Reverse current	I _R	V _R = 5 V	_	_	10	μA
	Capacitance	C _T	V = 0, f = 1MHz	_	30	_	pF
	Peak off-state current	I _{DRM}	V _{DRM} = 800V	_	10	1000	nA
<u>_</u>	Peak on-state voltage	V _{TM}	I _{TM} = 100mA	_	1.7	3.0	V
Detector	Holding current	lΗ	_	_	0.6	_	mA
Det	Critical rate of rise of off-state voltage	dv/dt	Vin = 240 Vrms , Ta = 85°C (Note 2)	200	500	_	V/µs
	Critical rate of rise of commutating voltage	dv/dt(c)	Vin = 60 Vrms , I _T = 15 mA (Note 2)	_	0.2	_	V/µs


Coupled Electrical Characteristics (Ta = 25°C)


Characteristic	Symbol	Test Condition	Min.	Тур.	Max.	Unit	
Trigger LED current	I _{FT}	V _T = 3V	_	5	10	mA	
Inhibit voltage	V _{IH}	I _F =Rated I _{FT}	_	_	50	V	
Leakage in inhibited state	l _{IH}	I _F =Rated I _{FT} , V _T = Rated V _{DRM}	_	200	600	μA	
Capacitance (input to output)	Cs	V _S = 0 , f = 1MHz	_	0.8	_	pF	
Isolation resistance	Rs	V _S = 500 V, R.H.≦60%	1×10 ¹²	10 ¹⁴	_	Ω	
Isolation voltage	BVs	AC , 1minute	5000	_	_	Vrms	
		AC , 1second,in oil	_	10000	_	VIIIIS	
		DC , 1minute,in oil	_	10000	_	Vdc	


3


(Note 2) dv / dt test circuit
























4 2006-12-11


^{*} The above graphs show typical characteristics.














^{*} The above graphs show typical characteristics.

RESTRICTIONS ON PRODUCT USE

20070701-EN

- The information contained herein is subject to change without notice.
- TOSHIBA is continually working to improve the quality and reliability of its products. Nevertheless, semiconductor devices in general can malfunction or fail due to their inherent electrical sensitivity and vulnerability to physical stress. It is the responsibility of the buyer, when utilizing TOSHIBA products, to comply with the standards of safety in making a safe design for the entire system, and to avoid situations in which a malfunction or failure of such TOSHIBA products could cause loss of human life, bodily injury or damage to property.
 In developing your designs, please ensure that TOSHIBA products are used within specified operating ranges as set forth in the most recent TOSHIBA products specifications. Also, please keep in mind the precautions and conditions set forth in the "Handling Guide for Semiconductor Devices," or "TOSHIBA Semiconductor Reliability Handbook" etc.
- The TOSHIBA products listed in this document are intended for usage in general electronics applications (computer, personal equipment, office equipment, measuring equipment, industrial robotics, domestic appliances, etc.). These TOSHIBA products are neither intended nor warranted for usage in equipment that requires extraordinarily high quality and/or reliability or a malfunction or failure of which may cause loss of human life or bodily injury ("Unintended Usage"). Unintended Usage include atomic energy control instruments, airplane or spaceship instruments, transportation instruments, traffic signal instruments, combustion control instruments, medical instruments, all types of safety devices, etc.. Unintended Usage of TOSHIBA products listed in his document shall be made at the customer's own risk.
- The products described in this document shall not be used or embedded to any downstream products of which manufacture, use and/or sale are prohibited under any applicable laws and regulations.
- GaAs(Gallium Arsenide) is used in this product. The dust or vapor is harmful to the human body. Do not break, cut, crush or dissolve chemically.
- Please contact your sales representative for product-by-product details in this document regarding RoHS
 compatibility. Please use these products in this document in compliance with all applicable laws and regulations
 that regulate the inclusion or use of controlled substances. Toshiba assumes no liability for damage or losses
 occurring as a result of noncompliance with applicable laws and regulations.