


SPECIFICATIONS


[1. General Specifications]

Model	SZW-301
Compatible models	CLA□-02□N-□
Mounting Location	Indoor
Mass (Tolerance ±10%)	0.01kg (0.005kg×2)
Quantity	2
Remarks	No restricted substances exceeding the thresholds of the RoHS Directive are contained.

[2. Outer Dimension]




(Unit : mm)





No.	Name	Material	Quantity
1	Bracket	PC	2

[3. Mounting Dimensional Drawing]



(Unit : mm)

Model	A Dim Mounting Pitch	B Dim	Number of Brackets used
CLA1-02□N-C	74	-	2
CLA2-02□N-C	174	-	
CLA3-02□N-□	274	-	
CLA6-02□N-□	574	-	
CLA9-02□N-C	874	290	4



Screw / Nut	Recommended Torque
M4	0.7 N·m