


SIDE VIEWS DO NOT DETAIL SCREW CHANNELS SEE "A - A" FOR CHANNEL DETAIL

THIS DRAWING IS PROPRIETARY INFORMATION OF HAMMOND MFG.CO.LTD. NOT TO BE USED WITHOUT EXPRESSED WRITTEN PERMISSION OF HAMMOND MFG.CO.LTD.

△	N/A	RELEASE	----	10/01/02	MJM
Rev	ECN	Description		Date	By

NOTES

DESIGNED TO MEET THE REQUIREMENTS OF IP65, & NEMA 4X TONGUE & GROOVE CONSTRUCTION WITH A MOLDED ONE PIECE SILICON GASKET. COMES WITH 4 STAINLESS STEEL MACHINE LID SCREWS, CAPTIVATED WITH 4 RUBBER O-RINGS. COMES WITH 4 GROUNDING SCREWS AND WASHERS. FINISH: NONE OR SUFFIX "BK" BLACK, OR SUFFIX "GY" GRAY (RAL 7001) POLYESTER POWDER



For the best fit print on legal size paper.

Unless otherwise spec'd dimensions are in millimeters Tolerances are:		Dwn	M. MERCER	HAMMOND MANUFACTURING CO. LTD. Electronics Group, Waterloo, Ont. - Cheektowaga, NY
.X	±2.5	Date	10/01/02	
.XX	±1.50	Chk	---	HAMMOND 1590Z SERIES CASTED AL ENCLOSURES
.XXX	±.500	Mat'l	CAST ALUMINUM	
.XXXX	±.100	Sheet	1 of 1	Part # 1590Z150
Holes	±.100			
Angles	±.5°			