



#### General ordering data

Order No.	0376860000
Short text for material	ASK 1/15
EAN	4008190141202
Qty	100

#### Additional technical data

Type of connection	screwed
No. of identical terminals	1
Version	Fuse terminal
Type of mouting	clipped
UL 94 flammability rating of insulation material	V2
Installation advice	TS 15
Colour of insulating material	beige
Insulating material	PA 66
Open sides	right
Operating temperature range	- 50 °C, + 100 °C
Connection direction	on side
Product range	SAK Series
No. of levels	1
Levels cross-connected internally	No
No. of terminal strips per level	2
End plate required	Yes

#### CSA rating data

Min. cross-section (CSA)	AWG 26
Voltage CSA	300 V
CSA current	6,3 A
Max. cross-section (CSA)	AWG 12

**Conductors for clamping (rated connection)**

AWG conductor size, min.	AWG 26
Flexible, min.	0,5 mm <sup>2</sup>
2nd type of connection	screwed
Solid, min.	0,5 mm <sup>2</sup>
Twin wire-end ferrule, min.	0,50 mm <sup>2</sup>
Twin wire end ferrule, max.	1,50 mm <sup>2</sup>
Stripping length	9 mm
Type of connection	Screw connection
No. of connections	2
Torque level with DMS electric screwdriver	2
Tightening torque range	0.5...1.0 Nm
Solid, max.	4 mm <sup>2</sup>
Flexible, max.	4 mm <sup>2</sup>
flexible w. ferrule AEH, max. DIN 46228-1	4 mm <sup>2</sup>
Flexible, max., ferrule with plastic collar (DIN 46228 pt 4)	4 mm <sup>2</sup>
flexible w. ferrule AEH, min. DIN 46228-1	0,5 mm <sup>2</sup>
Flexible, min., ferrule with plastic collar (DIN 46228 pt 4)	0,5 mm <sup>2</sup>
Clamping range, max.	4 mm <sup>2</sup>
Clamping range, min.	0,13 mm <sup>2</sup>
Clamping screw	M3
Blade size	0.6 x 3.5 mm
Gauge to IEC 60947-1	A3
AWG conductor size, max.	3,31 mm <sup>2</sup>
AWG conductor size, max.	AWG 12
Stranded, max.	4 mm <sup>2</sup>
Stranded, min.	1,5 mm <sup>2</sup>
AWG conductor size, min.	0,13 mm <sup>2</sup>
Connection direction	on side

**Dimensions**

Height of lowest version	34 mm
TS 15 offset	20 mm
Length	58 mm
Width	8 mm

**Disconnect terminals**

Torque level with DMS electric screwdriver	2
--	---

**Display element**

Type of voltage for indicator	AC/DC
Operating voltage for indicator, max.	500 V

**Fuse terminals**

Fuse holder (cartridge holder)	detachable
Display	without LED
Operating voltage, max.	400 V
Type of voltage for indicator	AC/DC
Cartridge fuse	G-Si. 5 x 20

**Rating data**

Rated cross-section	4 mm <sup>2</sup>
Rated voltage	500 V
Rated impulse withstand voltage	6 kV
Rated current	6,3 A
Current with max. conductor	6,3 A
Pollution severity	3

**UL rating data**

Current (UL)	10 A
Voltage UL	300 V
Min. cross-section (UL)	AWG 22
Max. cross-section (UL)	AWG 12

**Approvals**

Approvals

**Approvals**

Approvals

**Classifications**

ETIM 2.0	EC000899
ETIM 3.0	EC000899
eClass 4.1	27-14-11-16
eClass 5.0	27-14-11-16
eClass 5.1	27-14-11-16

**Related products**