

Inductors for power circuits

Wound metal

SPM-VC-D series (for automotive)



AEC-Q200

## SPM6545VC-D type



### FEATURES

- Metal composite type wound inductor for power circuits using a metallic magnetic material.
- Compared to ferrite wound type inductors, low Rdc and miniaturization can be realized due to superior DC superimposition characteristics of metallic magnetic materials.
- Vibration resistance of 30 G due to vibration resistance structure
- Operating temperature range: -55 to +155°C(including self-heating)
- Compliant with AEC-Q200

### APPLICATION

- Automotive-related equipment (LED, ECM, ADAS, BCM etc.)

### PART NUMBER CONSTRUCTION

SPM6545VC	-	1R0	M	-	D
Series name	Inductance (μH)	Inductance tolerance	Internal code		

### CHARACTERISTICS SPECIFICATION TABLE

L (μH)	Tolerance (±20%)	Measuring frequency (kHz)	DC resistance (mΩ)typ.	Isat (A)typ. (ΔL=-20%)	Itemp (A)typ. (ΔT=40deg.C)	Part No.
1.0	±20%	100	5.5	±15% 15.1	21.6	13.5 <a href="#">SPM6545VC-1R0M-D</a>
1.5	±20%	100	7.2	±15% 14.2	19.4	12.1 <a href="#">SPM6545VC-1R5M-D</a>
2.2	±20%	100	9.4	±15% 11.8	16.9	10.3 <a href="#">SPM6545VC-2R2M-D</a>
3.3	±20%	100	13.8	±15% 10.0	14.8	8.5 <a href="#">SPM6545VC-3R3M-D</a>
4.7	±20%	100	20.4	±15% 10.6	14.5	6.9 <a href="#">SPM6545VC-4R7M-D</a>
6.8	±20%	100	31.5	±15% 7.5	10.6	5.8 <a href="#">SPM6545VC-6R8M-D</a>
10	±20%	100	49.2	±15% 6.6	9.0	4.4 <a href="#">SPM6545VC-100M-D</a>
15	±20%	100	66.9	±15% 4.0	5.4	3.9 <a href="#">SPM6545VC-150M-D</a>
22	±20%	100	91.7	±15% 3.7	5.0	3.4 <a href="#">SPM6545VC-220M-D</a>
33	±20%	100	126.3	±15% 3.2	4.3	2.8 <a href="#">SPM6545VC-330M-D</a>
47	±20%	100	208.0	±15% 3.1	4.2	2.2 <a href="#">SPM6545VC-470M-D</a>
68	±20%	100	306.3	±15% 2.5	3.4	1.8 <a href="#">SPM6545VC-680M-D</a>

Isat: Based on the rate of change from the initial value of the inductance with DC current

Itemp: Based on self-heating due to DC current (rated current)

#### Measurement equipment


Measurement item	Product No. *	Manufacturer
L	4285A	Keysight Technologies
DC resistance	3541	HIOKI

\* Equivalent measurement equipment may be used.



# SPM6545VC-D type


## ■ L FREQUENCY CHARACTERISTICS



### Measurement equipment

Product No. *	Manufacturer
4294A	Keysight Technologies

## ■ L VS. DC BIAS CHARACTERISTICS




### Measurement equipment

Product No. *	Manufacturer
4284A+42841A	Keysight Technologies

\* Equivalent measurement equipment may be used.


# SPM6545VC-D type

## ■ SHAPE & DIMENSIONS




## ■ PACKAGING STYLE


### □ REEL DIMENSIONS



### □ TAPE DIMENSIONS



## ■ RECOMMENDED LAND PATTERN




Type	A	B	K
SPM6545VC-D	6.85	7.35	5.1

### □ PACKAGE QUANTITY

Package quantity	1000 pcs/reel
------------------	---------------

## ■ RECOMMENDED REFLOW PROFILE



## ■ TEMPERATURE RANGE, INDIVIDUAL WEIGHT

Operating temperature range *	Storage temperature range **	Individual weight
-55 to +155 °C	-55 to +155 °C	1.0 g

\* Operating temperature range includes self-heating.

\*\* The storage temperature range is for after the assembly.

## REMINDERS FOR USING THESE PRODUCTS

Before using these products, be sure to request the delivery specifications.

### SAFETY REMINDERS

Please pay sufficient attention to the warnings for safe designing when using this products

### REMINDERS

- The storage period is within 12 months. Be sure to follow the storage conditions (temperature: 5 to 40°C, humidity: 20 to 75% RH or less).  
If the storage period elapses, the soldering of the terminal electrodes may deteriorate.
- Do not use or store in locations where there are conditions such as gas corrosion (salt, acid, alkali, etc.).
- Soldering corrections after mounting should be within the range of the conditions determined in the specifications.  
If overheated, a short circuit, performance deterioration, or lifespan shortening may occur.
- Do not use products that have received any excessive mechanical shock such as by being dropped.
- When embedding a printed circuit board where a chip is mounted to a set, be sure that residual stress is not given to the chip due to the overall distortion of the printed circuit board and partial distortion such as at screw tightening portions.
- Self heating (temperature increase) occurs when the power is turned ON, so the tolerance should be sufficient for the set thermal design.
- Do not expose the products to magnets or magnetic fields.
- The performance of the product may deteriorate if coating materials are used, thus please assess the situation beforehand by taking this factor into consideration.
- Do not use for a purpose outside of the contents regulated in the delivery specifications.
- The products described in this catalog are intended to be installed in automobiles or automotive electronic equipment (AV equipment, telecommunications equipment, home appliances, amusement equipment, computer equipment, personal equipment, office equipment, measurement equipment, industrial robots) and to be used in automobiles (including the case where the said automotive product is mounted in a vehicle) or standard applications as general electronic equipment in automotive applications or standard applications as general electronic equipment in automotive applications in accordance with the scope and conditions described in this specification, while the said automotive or general electronic equipment including the said product is intended to be used in the usual operation and usage methods, respectively. Other than automotive or automotive products are not designed or warranted to meet the requirements of the applications listed below, whose performance and/or quality requires a more stringent level of safety or reliability, or whose failure, malfunction or defect could cause serious damage to society, person or property.

Please understand that we are not responsible for any damage or liability caused by use of the products in any of the applications below or for any other use exceeding the range or conditions set forth in this specification sheet.

If you intend to use the products in the applications listed below or if you have special requirements exceeding the range or conditions set forth in this specification, please contact us.

(1) Aerospace/aviation equipment	(7) Transportation control equipment
(2) Transportation equipment (electric trains, ships, etc.)	(8) Public information-processing equipment
(3) Medical equipment	(9) Military equipment
(4) Power-generation control equipment	(10) Electric heating apparatus, burning equipment
(5) Atomic energy-related equipment	(11) Disaster prevention/crime prevention equipment
(6) Seabed equipment	(12) Safety equipment
	(13) Other applications that are not considered general-purpose applications

When designing your equipment even for general-purpose applications, you are kindly requested to take into consideration securing protection circuit/device or providing backup circuits in your equipment.