


12CWQ06FN

SCHOTTKY RECTIFIER

12 Amp




Major Ratings and Characteristics

| Characteristics | 12CWQ06FN | Units |
|--|------------|------------|
| $I_{F(AV)}$ Rectangular waveform | 12 | A |
| V_{RRM} | 60 | V |
| I_{FSM} @ $t_p = 5 \mu s$ sine | 320 | A |
| V_F @ 6 Apk, $T_J = 125^\circ C$ (per leg) | 0.57 | V |
| T_J range | -40 to 150 | $^\circ C$ |

Description/Features

The 12CWQ06FN surface mount, center tap, Schottky rectifier series has been designed for applications requiring low forward drop and small footprints on PC board. Typical applications are in disk drives, switching power supplies, converters, free-wheeling diodes, battery charging, and reverse battery protection.

- Popular D-PAK outline
- Center tap configuration
- Small foot print, surface mountable
- Low forward voltage drop
- High frequency operation
- Guard ring for enhanced ruggedness and long term reliability



Voltage Ratings

| Part number | 12CWQ06FN |
|---|-----------|
| V_R Max. DC Reverse Voltage (V) | 60 |
| V_{RWM} Max. Working Peak Reverse Voltage (V) | |

Absolute Maximum Ratings

| Parameters | 12CWQ... | Units | Conditions | |
|---|----------|-------|---|---|
| $I_{F(AV)}$ Max. Average Forward Current (Per Leg) * See Fig. 5 (Per Device) | 6 | A | 50% duty cycle @ $T_C = 131^\circ\text{C}$, rectangular waveform | |
| | 12 | | | |
| I_{FSM} Max. Peak One Cycle Non-Repetitive Surge Current (Per Leg) * See Fig. 7 | 320 | A | 5 μs Sine or 3 μs Rect. pulse | Following any rated load condition and with rated V_{RRM} applied |
| | 105 | | 10ms Sine or 6ms Rect. pulse | |

Electrical Specifications

| Parameters | 12CWQ... | Units | Conditions | |
|--|----------|------------|---|---------------------------|
| V_{FM} Max. Forward Voltage Drop (Per Leg) * See Fig. 1 (1) | 0.61 | V | @ 6A | $T_J = 25^\circ\text{C}$ |
| | 0.79 | V | @ 12A | |
| | 0.57 | V | @ 6A | $T_J = 125^\circ\text{C}$ |
| | 0.72 | V | @ 12A | |
| I_{RM} Max. Reverse Leakage Current (Per Leg) * See Fig. 2 (1) | 3 | mA | $T_J = 25^\circ\text{C}$ | $V_R = \text{rated } V_R$ |
| | 35 | mA | $T_J = 125^\circ\text{C}$ | |
| $V_{F(TO)}$ Threshold Voltage | 0.36 | V | $T_J = T_J \text{ max.}$ | |
| r_t Forward Slope Resistance | 24.14 | m Ω | | |
| C_T Typ. Junction Capacitance (Per Leg) | 360 | pF | $V_R = 5V_{DC}$, (test signal range 100Khz to 1Mhz) 25°C | |
| L_S Typical Series Inductance (Per Leg) | 5.0 | nH | Measured lead to lead 5mm from package body | |

(1) Pulse Width < 300 μs , Duty Cycle <2%

Thermal-Mechanical Specifications

| Parameters | 12CWQ... | Units | Conditions | |
|--|------------|--------------------|---------------------|--------------|
| T_J Max. Junction Temperature Range | -40 to 150 | $^\circ\text{C}$ | | |
| T_{stg} Max. Storage Temperature Range | -40 to 150 | $^\circ\text{C}$ | | |
| R_{thJC} Max. Thermal Resistance (Per Leg) Junction to Case (Per Device) | 3.0 | $^\circ\text{C/W}$ | DC operation | * See Fig. 4 |
| | 1.5 | | | |
| wt Approximate Weight | 0.3(0.01) | g(oz.) | | |
| Case Style | D-Pak | | Similar to TO-252AA | |




Fig. 1 - Max. Forward Voltage Drop Characteristics (Per Leg)




Fig. 2 - Typical Values Of Reverse Current Vs. Reverse Voltage (Per Leg)




Fig. 3 - Typical Junction Capacitance Vs. Reverse Voltage (Per Leg)




Fig. 4 - Max. Thermal Impedance Z_{thJC} Characteristics (Per Leg)




Fig. 5 - Max. Allowable Case Temperature Vs. Average Forward Current (Per Leg)




Fig. 6 - Forward Power Loss Characteristics (Per Leg)





Fig. 7 - Max. Non-Repetitive Surge Current (Per Leg)

(2) Formula used: $T_c = T_j - (Pd + Pd_{REV}) \times R_{thJC}$;


Pd = Forward Power Loss = $I_{F(AV)} \times V_{FM} @ (I_{F(AV)} / D)$ (see Fig. 6);

Pd_{REV} = Inverse Power Loss = $V_{R1} \times I_R (1 - D)$; $I_R @ V_{R1} = 80\%$ rated V_R

Marking Information



Tape & Reel Information



International
IOR Rectifier

WORLDHEADQUARTERS: 233 Kansas St., El Segundo, California 90245 U.S.A. Tel: (310) 322 3331. Fax: (310) 322 3332.
EUROPEANHEADQUARTERS: Hurst Green, Oxted, Surrey RH8 9BB, U.K. Tel: ++ 44 1883 732020. Fax: ++ 44 1883 733408.
IR CANADA: 15 Lincoln Court, Brampton, Markham, Ontario L6T3Z2. Tel: (905) 453 2200. Fax: (905) 475 8801.
IR GERMANY: Saalburgstrasse 157, 61350 Bad Homburg. Tel: ++ 49 6172 96590. Fax: ++ 49 6172 965933.
IR ITALY: Via Liguria 49, 10071 Borgaro, Torino. Tel: ++ 39 11 4510111. Fax: ++ 39 11 4510220.
IR FAR EAST: K&H Bldg., 2F, 30-4 Nishi-Ikebukuro 3-Chome, Toshima-Ku, Tokyo, Japan 171. Tel: 81 3 3983 0086.
IR SOUTHEAST ASIA: 1 Kim Seng Promenade, Great World City West Tower,13-11, Singapore 237994. Tel: ++ 65 838 4630.
IR TAIWAN: 16 Fl. Suite D.207, Sec. 2, Tun Haw South Road, Taipei, 10673, Taiwan. Tel: 886 2 2377 9936.

<http://www.irf.com>

Fax-On-Demand: +44 1883 733420

Data and specifications subject to change without notice.