

Safety Data Sheet

According to Annex II to REACH - Regulation (EU) 2020/878 and to Annex II to UK REACH

SECTION 1. Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

Product name **SGM494**

1.2. Relevant identified uses of the substance or mixture and uses advised against

Intended use **Silicone grease.**

1.3. Details of the supplier of the safety data sheet

Name **CHT UK BRIDGWATER LTD**
Full address **Amber House Showground Road**
District and Country **TA6 6AJ Bridgwater (Somerset)**
England
Tel. **+44(0)1278411400**
Fax **+44(0)1278411444**

e-mail address of the competent person responsible for the Safety Data Sheet **info.uk@cht.com**Supplier: **CHT Germany GmbH**
Bismarckstraße 102
72072 Tübingen
Germany

1.4. Emergency telephone number

For urgent inquiries refer to **Transport: +1-703-527-3887 CHEMTREC (International, 24 hours) (CCN 1014369)**
+44 20 3807 3798 CHEMTREC (United Kingdom, 24 hours)
+353 1 901 4670 CHEMTREC (Ireland, 24 hours)
+61 2 9037 2994 CHEMTREC (Australia, 24 hours)
+64 9-801 0034 CHEMTREC (New Zealand, 24 hours)

SECTION 2. Hazards identification

2.1. Classification of the substance or mixture

The product is not classified as hazardous pursuant to the provisions set forth in EC Regulation 1272/2008 (CLP). However, since the product contains hazardous substances in concentrations such as to be declared in section no. 3, it requires a safety data sheet with appropriate information, compliant to (EU) Regulation 2020/878.

Hazard classification and indication: --

2.2. Label elements

Hazard labelling pursuant to EC Regulation 1272/2008 (CLP) and subsequent amendments and supplements.

Hazard pictograms: --

Signal words: --

Hazard statements:
EUH210 Safety data sheet available on request.

Precautionary statements: --

SECTION 2. Hazards identification ... / >>

2.3. Other hazards

On the basis of available data, the product does not contain any PBT or vPvB in percentage \geq than 0,1%.

The product does not contain substances with endocrine disrupting properties in concentration \geq 0.1%.

SECTION 3. Composition/information on ingredients

3.1. Substances

Information not relevant

3.2. Mixtures

Contains:

Identification	x = Conc. %	Classification (EC) 1272/2008 (CLP)
TRIMETHYL BORATE		
INDEX 005-005-00-1	$0.2 \leq x < 0.3$	Flam. Liq. 3 H226, Repr. 1B H360, Acute Tox. 3 H301, Acute Tox. 3 H311, Acute Tox. 3 H331, STOT SE 1 H370, Eye Irrit. 2 H319
EC 204-468-9		LD50 Oral: 100.1 mg/kg, LD50 Dermal: 300.1 mg/kg, LC50 Inhalation vapours: 3.1 mg/l/4h
CAS 121-43-7		
REACH Reg. 01-2119906953-33		

The full wording of hazard (H) phrases is given in section 16 of the sheet.

SECTION 4. First aid measures

4.1. Description of first aid measures

No effects requiring implementation of special first aid measures are expected. The following information represents practical indications of correct behaviour in the event of contact with a chemical product, even if not hazardous.

In case of doubt or in the presence of symptoms contact a doctor and show him this document.

In case of more severe symptoms, ask for immediate medical aid.

EYES: Remove, if present, contact lenses if the situation allows you to do so easily. Wash immediately with plenty of water for at least 15 minutes, opening the eyelids fully. Get medical advice/attention.

SKIN: Take off contaminated clothing. Wash immediately and thoroughly with running water (and soap if possible). Get medical advice.

Avoid further contact with contaminated clothing.

INGESTION: Do not induce vomiting unless explicitly authorised by a doctor. Do not give anything by mouth to an unconscious person. Get medical advice/attention.

INHALATION: Remove victim to fresh air, away from the accident scene. Get medical advice/attention.

Rescuer protection

It is good practice for rescuers lending support to a person who has been exposed to a chemical substance or to a mixture to wear personal protective equipment. The nature of such protection depends on the hazard level of the substance or mixture, on the type of exposure and on the extent of the contamination. In the absence of other more specific indications, use of disposable gloves in the event of possible contact with body fluids is recommended. For the type of PPE suitable for the characteristics of the substance or mixture, see section 8.

4.2. Most important symptoms and effects, both acute and delayed

Specific information on symptoms and effects caused by the product are unknown.

DELAYED EFFECTS: Based on the information currently available, there are no known cases of delayed effects following exposure to this product.

4.3. Indication of any immediate medical attention and special treatment needed

If symptoms occur, whether acute or delayed, consult a doctor.

Means to have available in the workplace for specific and immediate treatment

Running water for skin and eye wash.

SECTION 5. Firefighting measures

5.1. Extinguishing media

SUITABLE EXTINGUISHING EQUIPMENT

The extinguishing equipment should be of the conventional kind: carbon dioxide, foam, powder and water spray.

UNSUITABLE EXTINGUISHING EQUIPMENT

None in particular.

5.2. Special hazards arising from the substance or mixture

HAZARDS CAUSED BY EXPOSURE IN THE EVENT OF FIRE

Do not breathe combustion products.

5.3. Advice for firefighters

GENERAL INFORMATION

Use jets of water to cool the containers to prevent product decomposition and the development of substances potentially hazardous for health. Always wear full fire prevention gear. Collect extinguishing water to prevent it from draining into the sewer system. Dispose of contaminated water used for extinction and the remains of the fire according to applicable regulations.

SPECIAL PROTECTIVE EQUIPMENT FOR FIRE-FIGHTERS

Normal fire fighting clothing i.e. fire kit (BS EN 469), gloves (BS EN 659) and boots (HO specification A29 and A30) in combination with self-contained open circuit positive pressure compressed air breathing apparatus (BS EN 137).

SECTION 6. Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

Block the leakage if there is no hazard.

Wear suitable protective equipment (including personal protective equipment referred to under Section 8 of the safety data sheet) to prevent any contamination of skin, eyes and personal clothing. These indications apply for both processing staff and those involved in emergency procedures.

6.2. Environmental precautions

The product must not penetrate into the sewer system or come into contact with surface water or ground water.

6.3. Methods and material for containment and cleaning up

Collect the leaked product into a suitable container. Evaluate the compatibility of the container to be used, by checking section 10. Absorb the remainder with inert absorbent material.

Make sure the leakage site is well aired. Contaminated material should be disposed of in compliance with the provisions set forth in point 13.

6.4. Reference to other sections

Any information on personal protection and disposal is given in sections 8 and 13.

SECTION 7. Handling and storage

7.1. Precautions for safe handling

Keep away from heat, sparks and naked flames; do not smoke or use matches or lighters. Without adequate ventilation, vapours may accumulate at ground level and, if ignited, catch fire even at a distance, with the danger of backfire. Avoid bunching of electrostatic charges. Do not eat, drink or smoke during use. Remove any contaminated clothes and personal protective equipment before entering places in which people eat. Avoid leakage of the product into the environment.

7.2. Conditions for safe storage, including any incompatibilities

Store only in the original container. Store in a cool and well ventilated place, keep far away from sources of heat, naked flames and sparks and other sources of ignition. Keep containers away from any incompatible materials, see section 10 for details.

7.3. Specific end use(s)

Information not available

SECTION 8. Exposure controls/personal protection

8.1. Control parameters

Information not available

8.2. Exposure controls

As the use of adequate technical equipment must always take priority over personal protective equipment, make sure that the workplace is well aired through effective local aspiration.

HAND PROTECTION

Protect hands with category III work gloves.

The following should be considered when choosing work glove material (see standard EN 374): compatibility, degradation, permeability time.

The work gloves' resistance to chemical agents should be checked before use, as it can be unpredictable. The gloves' wear time depends on the duration and type of use.

Protect your hands with gloves of the following type:

Material: Nitrile rubber (NBR)

The choice of an appropriate glove does not only depend on its material but also on other quality features and is different from one producer to the other.

Thickness: 0.35 mm

The obtained break through times according to EN 374 Part III are not measured under normal operating conditions.

Breakthrough time: 480 min

Therefore a maximum usage time of 50% of the break through time is recommended.

SKIN PROTECTION

Wear category I professional long-sleeved overalls and safety footwear (see Regulation 2016/425 and standard EN ISO 20344). Wash body with soap and water after removing protective clothing.

EYE PROTECTION

Wear airtight protective goggles (see standard EN ISO 16321).

RESPIRATORY PROTECTION

Respiratory protection devices must be used if the technical measures adopted are not suitable for restricting the worker's exposure to the threshold values considered. Use a mask with a type A filter whose class (1, 2 or 3) must be chosen according to the limit of use concentration. (see standard EN 14387).

If the substance considered is odourless or its olfactory threshold is higher than the corresponding TLV-TWA and in the case of an emergency, wear open-circuit compressed air breathing apparatus (in compliance with standard EN 137) or external air-intake breathing apparatus (in compliance with standard EN 138). For a correct choice of respiratory protection device, see standard EN 529.

ENVIRONMENTAL EXPOSURE CONTROLS

The emissions generated by manufacturing processes, including those generated by ventilation equipment, should be checked to ensure compliance with environmental standards.

SECTION 9. Physical and chemical properties

9.1. Information on basic physical and chemical properties

Properties	Value	Information
Appearance	paste	
Colour	colourless	
Odour	characteristic	
Melting point / freezing point	not available	
Initial boiling point	not available	
Flammability	not available	
Lower explosive limit	not available	
Upper explosive limit	not available	
Flash point	> 150 °C	
Auto-ignition temperature	> 400 °C	
Decomposition temperature	not available	
pH	not available	
Kinematic viscosity	paste	
Solubility	immiscible with water	
Partition coefficient: n-octanol/water	not available	
Vapour pressure	not available	
Density and/or relative density	1	
Relative vapour density	not available	
Particle characteristics	not applicable	

SECTION 9. Physical and chemical properties ... / >>**9.2. Other information**

9.2.1. Information with regard to physical hazard classes

Information not available

9.2.2. Other safety characteristics

VOC (Directive 2010/75/EU)	0.51 % - 5.10	g/litre
VOC (volatile carbon)	0.17 % - 1.71	g/litre

SECTION 10. Stability and reactivity**10.1. Reactivity**

There are no particular risks of reaction with other substances in normal conditions of use.

10.2. Chemical stability

The product is stable in normal conditions of use and storage.

10.3. Possibility of hazardous reactions

No hazardous reactions are foreseeable in normal conditions of use and storage.

10.4. Conditions to avoid

None in particular. However the usual precautions used for chemical products should be respected.

10.5. Incompatible materials

Information not available

10.6. Hazardous decomposition products

Information not available

SECTION 11. Toxicological information

In the absence of experimental data for the product itself, health hazards are evaluated according to the properties of the substances it contains, using the criteria specified in the applicable regulation for classification.

It is therefore necessary to take into account the concentration of the individual hazardous substances indicated in section 3, to evaluate the toxicological effects of exposure to the product.

11.1. Information on hazard classes as defined in Regulation (EC) No 1272/2008Metabolism, toxicokinetics, mechanism of action and other information

Information not available

Information on likely routes of exposure

Information not available

Delayed and immediate effects as well as chronic effects from short and long-term exposure

Information not available

Interactive effects

Information not available

ACUTE TOXICITY

ATE (Inhalation - vapours) of the mixture:	> 20 mg/l
ATE (Oral) of the mixture:	>2000 mg/kg
ATE (Dermal) of the mixture:	>2000 mg/kg

SECTION 11. Toxicological information ... / >>

TRIMETHYL BORATE

LD50 (Dermal):	300.1 mg/kg (Expert judgment)
LD50 (Oral):	100.1 mg/kg (Expert judgment)
LC50 (Inhalation vapours):	3.1 mg/l/4h (Expert judgment)

SKIN CORROSION / IRRITATION

Does not meet the classification criteria for this hazard class

SERIOUS EYE DAMAGE / IRRITATION

Does not meet the classification criteria for this hazard class

RESPIRATORY OR SKIN SENSITISATION

Does not meet the classification criteria for this hazard class

GERM CELL MUTAGENICITY

Does not meet the classification criteria for this hazard class

CARCINOGENICITY

Does not meet the classification criteria for this hazard class

REPRODUCTIVE TOXICITY

Does not meet the classification criteria for this hazard class

STOT - SINGLE EXPOSURE

Does not meet the classification criteria for this hazard class

STOT - REPEATED EXPOSURE

Does not meet the classification criteria for this hazard class

ASPIRATION HAZARD

Does not meet the classification criteria for this hazard class

11.2. Information on other hazards

Based on the available data, the product does not contain substances listed in the main European lists of potential or suspected endocrine disruptors with human health effects under evaluation.

SECTION 12. Ecological information

Use this product according to good working practices. Avoid littering. Inform the competent authorities, should the product reach waterways or contaminate soil or vegetation.

12.1. Toxicity

Information not available

12.2. Persistence and degradability

Information not available

12.3. Bioaccumulative potential

Information not available

12.4. Mobility in soil

Information not available

SECTION 12. Ecological information ... / >>**12.5. Results of PBT and vPvB assessment**

On the basis of available data, the product does not contain any PBT or vPvB in percentage \geq than 0,1%.

12.6. Endocrine disrupting properties

Based on the available data, the product does not contain substances listed in the main European lists of potential or suspected endocrine disruptors with environmental effects under evaluation.

12.7. Other adverse effects

Information not available

SECTION 13. Disposal considerations**13.1. Waste treatment methods**

Reuse, when possible. Neat product residues should be considered special non-hazardous waste.
Disposal must be performed through an authorised waste management firm, in compliance with national and local regulations.

CONTAMINATED PACKAGING

Contaminated packaging must be recovered or disposed of in compliance with national waste management regulations.

Waste Code: 70 02 16*

SECTION 14. Transport information

The product is not dangerous under current provisions of the Code of International Carriage of Dangerous Goods by Road (ADR) and by Rail (RID), of the International Maritime Dangerous Goods Code (IMDG), and of the International Air Transport Association (IATA) regulations.

14.1. UN number or ID number

not applicable

14.2. UN proper shipping name

not applicable

14.3. Transport hazard class(es)

not applicable

14.4. Packing group

not applicable

14.5. Environmental hazards

not applicable

14.6. Special precautions for user

not applicable

14.7. Maritime transport in bulk according to IMO instruments

Information not relevant

SECTION 15. Regulatory information

Australia AICS: On or in compliance with the inventory.
Canada DSL Inventory List: On or in compliance with the inventory.

SECTION 15. Regulatory information ... / >>

EINECS, ELINCS or NLP: On or in compliance with the inventory.
Japan (ENCS) List: On or in compliance with the inventory.
China Inv. Existing Chemical Substances: On or in compliance with the inventory.
Korea Existing Chemicals Inv. (KECI): On or in compliance with the inventory.
Philippines PICCS: On or in compliance with the inventory.
US TSCA Inventory: On or in compliance with the inventory.
New Zealand Inventory of Chemicals: On or in compliance with the inventory.
Taiwan Chemical Substance Inventory: On or in compliance with the inventory.

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

Seveso Category - Directive 2012/18/EU: None

Restrictions relating to the product or contained substances pursuant to Annex XVII to EC Regulation 1907/2006

<u>Product</u>	
Point	40
<u>Contained substance</u>	
Point	75

Regulation (EU) 2019/1148 - on the marketing and use of explosives precursors
not applicable

Substances in Candidate List (Art. 59 REACH)

On the basis of available data, the product does not contain any SVHC in percentage \geq than 0,1%.

Substances subject to authorisation (Annex XIV REACH)

None

Substances subject to exportation reporting pursuant to Regulation (EU) 649/2012:

None

Substances subject to the Rotterdam Convention:

None

Substances subject to the Stockholm Convention:

None

Healthcare controls

Information not available

German regulation on the classification of substances hazardous to water (AwSV, vom 18. April 2017)

WGK 1: Low hazard to waters

15.2. Chemical safety assessment

A chemical safety assessment has not been performed for the preparation/for the substances indicated in section 3.

SECTION 16. Other information

Text of hazard (H) indications mentioned in section 2-3 of the sheet:

Flam. Liq. 3	Flammable liquid, category 3
Repr. 1B	Reproductive toxicity, category 1B
Acute Tox. 3	Acute toxicity, category 3
STOT SE 1	Specific target organ toxicity - single exposure, category 1
Eye Irrit. 2	Eye irritation, category 2
H226	Flammable liquid and vapour.
H360	May damage fertility or the unborn child.
H301	Toxic if swallowed.
H311	Toxic in contact with skin.
H331	Toxic if inhaled.
H370	Causes damage to organs.
H319	Causes serious eye irritation.
EUH210	Safety data sheet available on request.

LEGEND:

- ADR: European Agreement concerning the carriage of Dangerous goods by Road

SECTION 16. Other information ... / >>

- ATE: Acute Toxicity Estimate
- CAS: Chemical Abstract Service Number
- CE50: Effective concentration (required to induce a 50% effect)
- CE: Identifier in ESIS (European archive of existing substances)
- CLP: Regulation (EC) 1272/2008
- DNEL: Derived No Effect Level
- EmS: Emergency Schedule
- GHS: Globally Harmonized System of classification and labeling of chemicals
- IATA DGR: International Air Transport Association Dangerous Goods Regulation
- IC50: Immobilization Concentration 50%
- IMDG: International Maritime Code for dangerous goods
- IMO: International Maritime Organization
- INDEX: Identifier in Annex VI of CLP
- LC50: Lethal Concentration 50%
- LD50: Lethal dose 50%
- OEL: Occupational Exposure Level
- PBT: Persistent, bioaccumulative and toxic
- PEC: Predicted environmental Concentration
- PEL: Predicted exposure level
- PMT: Persistent, mobile and toxic
- PNEC: Predicted no effect concentration
- REACH: Regulation (EC) 1907/2006
- RID: Regulation concerning the international transport of dangerous goods by train
- TLV: Threshold Limit Value
- TLV CEILING: Concentration that should not be exceeded during any time of occupational exposure.
- TWA: Time-weighted average exposure limit
- TWA STEL: Short-term exposure limit
- VOC: Volatile organic Compounds
- vPvB: Very persistent and very bioaccumulative
- vPvM: Very persistent and very mobile
- WGK: Water hazard classes (German).

GENERAL BIBLIOGRAPHY

1. Regulation (EC) 1907/2006 (REACH) of the European Parliament
 2. Regulation (EC) 1272/2008 (CLP) of the European Parliament
 3. Regulation (EU) 2020/878 (II Annex of REACH Regulation)
 4. Regulation (EC) 790/2009 (I Atp. CLP) of the European Parliament
 5. Regulation (EU) 286/2011 (II Atp. CLP) of the European Parliament
 6. Regulation (EU) 618/2012 (III Atp. CLP) of the European Parliament
 7. Regulation (EU) 487/2013 (IV Atp. CLP) of the European Parliament
 8. Regulation (EU) 944/2013 (V Atp. CLP) of the European Parliament
 9. Regulation (EU) 605/2014 (VI Atp. CLP) of the European Parliament
 10. Regulation (EU) 2015/1221 (VII Atp. CLP) of the European Parliament
 11. Regulation (EU) 2016/918 (VIII Atp. CLP) of the European Parliament
 12. Regulation (EU) 2016/1179 (IX Atp. CLP)
 13. Regulation (EU) 2017/776 (X Atp. CLP)
 14. Regulation (EU) 2018/669 (XI Atp. CLP)
 15. Regulation (EU) 2019/521 (XII Atp. CLP)
 16. Delegated Regulation (UE) 2018/1480 (XIII Atp. CLP)
 17. Regulation (EU) 2019/1148
 18. Delegated Regulation (UE) 2020/217 (XIV Atp. CLP)
 19. Delegated Regulation (UE) 2020/1182 (XV Atp. CLP)
 20. Delegated Regulation (UE) 2021/643 (XVI Atp. CLP)
 21. Delegated Regulation (UE) 2021/849 (XVII Atp. CLP)
 22. Delegated Regulation (UE) 2022/692 (XVIII Atp. CLP)
 23. Delegated Regulation (UE) 2023/707
 24. Delegated Regulation (UE) 2023/1434 (XIX Atp. CLP)
 24. Delegated Regulation (UE) 2023/1435 (XX Atp. CLP)
- The Merck Index. - 10th Edition
 - Handling Chemical Safety
 - INRS - Fiche Toxicologique (toxicological sheet)
 - Patty - Industrial Hygiene and Toxicology
 - N.I. Sax - Dangerous properties of Industrial Materials-7, 1989 Edition
 - IFA GESTIS website
 - ECHA website
 - Database of SDS models for chemicals - Ministry of Health and ISS (Istituto Superiore di Sanità) - Italy

SECTION 16. Other information ... / >>**Note for users:**

The information contained in the present sheet are based on our own knowledge on the date of the last version. Users must verify the suitability and thoroughness of provided information according to each specific use of the product.

This document must not be regarded as a guarantee on any specific product property.

The use of this product is not subject to our direct control; therefore, users must, under their own responsibility, comply with the current health and safety laws and regulations. The producer is relieved from any liability arising from improper uses.

Provide appointed staff with adequate training on how to use chemical products.

CALCULATION METHODS FOR CLASSIFICATION

Chemical and physical hazards: Product classification derives from criteria established by the CLP Regulation, Annex I, Part 2. The data for evaluation of chemical-physical properties are reported in section 9.

Health hazards: Product classification is based on calculation methods as per Annex I of CLP, Part 3, unless determined otherwise in Section 11.

Environmental hazards: Product classification is based on calculation methods as per Annex I of CLP, Part 4, unless determined otherwise in Section 12.

Changes to previous review:

The following sections were modified:

03 / 04 / 08 / 09 / 11 / 13.